


D

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
2. 温度范围(Temperature range):  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ .
3. 额定电压(Rated voltage): 50V, AC/DC(=等效).
4. 接触电阻(Contact resistance):  $\leq 0.03\Omega$ .
5. 绝缘电阻(Insulation resistance):  $\geq 500\text{M}\Omega$ .

