

1. Description

These N-channel enhancement mode power mosfets used advanced trench technology design, provided excellent $R_{DS(ON)}$ and low gate charge. Which accords with the RoHS standard.

2.2 Features

- Fast Switching
- Low ON Resistance($R_{DS(ON)} \leq 29m\Omega$)
- Low Gate Charge


2.1 Features

- $V_{DS(V)} = 60V$
- $I_D = 25A (V_{GS} = 10V)$
- $R_{DS(ON)} = 23m\Omega (V_{GS} = 10V)$
- $R_{DS(ON)} = 30m\Omega (V_{GS} = 4.5V)$

3. Pinning information

Pin	Symbol	Description
1	G	GATE
2	D	DRAIN
3	S	SOURCE

TO-252(DPAK)
top view



4. Absolute Maximum Ratings $T_A = 25^\circ C$

Parameter		Symbol	Rating	Units
Drain-Source Voltage		V_{DS}	60	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current	$T_C = 25^\circ C$	I_D	25	A
	$T_C = 100^\circ C$		17.5	
Pulsed Drain Current ¹⁾		I_{DM}	100	
Single Pulse Avalanche Energy ²⁾		E_{AS}	56.2	mJ
Maximum Power Dissipation	$T_C = 25^\circ C$	P_D	36.2	W
Storage Temperature Range		T_{STG}	-55 to 150	W
Junction Temperature Range		T_J	-55 to 150	$^\circ C$



5.Thermal resistance rating

Parameter	Symbol	Typ	Max	Units
Thermal Resistance,Junction-to-Case	$R_{\theta JC}$		3.45	°C/W
Thermal Resistance,Junction to Ambient	$R_{\theta JA}$		111.5	°C/W



6.SPECIFICATIONS (T_J= 25°C, unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
OFF CHARACTERISTICS						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _{DS} =250μA	60			V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =60V, V _{GS} =0V			1	μA
Gate-Body Leakage	I _{GSS}	V _{GS} =±20V, V _{DS} =0V			±100	nA
ON CHARACTERISTIC						
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _{DS} =250μA	1	1.5	2	V
Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =10V, I _{DS} =19A		23	29	mΩ
		V _{GS} =4.5V, I _{DS} =19A		30	38	mΩ
DYNAMIC CHARACTERISTICS						
Input Capacitance	C _{iss}	V _{DS} =30V, V _{GS} =0V, f=1MHz		939		pF
Output Capacitance	C _{oss}			73.5		pF
Reverse Transfer Capacitance	C _{rss}			52.7		pF
Gate Resitance	R _g	V _{DD} =0V, V _{GS} =0V, f=1MHz		1.9		Ω
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	t _{D(on)}	V _{GS} =10V, V _{DS} =30V R _{GEN} =3Ω, I _D =20A		8.4		ns
Rise Time	t _r			8.5		ns
Turn-Off Delay Time	t _{D(off)}			35.4		ns
Fall Time	t _f			4.8		ns
Total Gate Charge	Q _g	V _{DS} =30V, I _{DS} =20A, V _{GS} =10V		21.2		nC
Gate to Source Gate Charge	Q _{gs}			3.6		nC
Gate to Drain“Miller”Charge	Q _{gd}			5.5		nC




DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS						
Drain-Source Diode Forward Voltage	V_{SD}	$V_{GS}=30V, I_{DS}=20A$			1.2	V
Reverse Recovery Time	t_{rr}	$T_J=25^{\circ}C, I_F=20A$		18.8		nS
Reverse Recovery Charge	Q_{rr}	$di/dt=100A/\mu s$		13.4		nC

Notes:

- 1) Repetitive rating; pulse width limited by maximum junction temperature .
- 2) $L=0.5mH, V_{DD}=30V, I_{AS}=15A$ Start $T_J=25^{\circ}C$.
- 3) Recommend soldering temperature defined by IPC/JEDEC J-STD 020.









7.1 Typical Characteristics






7.2Typical Characteristics

	
Figure 6: TypicalTransfer Characteristics	Figure 7: Typical Body Diode TransferCharacteristics
	
Figure 8: Drain-to-Source On Resistance vs Drain Curent	Figure 9: Normalized On Resistance vs Junction Temperature
	
Figure 10: Normalized Threshold Voltage vs Junction Temperature	Figure 11: Normalized Breakdown Voltage vs Junction Temperature



7.3Typical Characteristics





7.4 Typical Characteristics




Figure 14: Gate Charge Test Circuit




Figure 15: Gate Charge Waveforms




Figure 16: Resistive Switching Test Circuit




Figure 17: Resistive Switching Waveforms



7.5 Typical Characteristics




Figure 18: Diode Reverse Recovery Test Circuit




Figure 19: Diode Reverse Recovery Waveform




Figure 20: Unclamped Inductive Switching Test Circuit





Figure 21: Unclamped Inductive Switching Waveform



8.TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A1	A2	A3	b	c	D	D1	D2	E	E1	E2	e	L1	L2	L3	θ
Min	0.00	2.18	0.90	0.65	0.46	6.35	4.95	4.32	9.40	5.97	5.21	2.286 BSC	0.89	1.70	0.60	0.00
Max	0.13	2.39	1.10	0.85	0.61	6.73	5.46	4.90	10.41	6.22	5.38		1.27	1.90	1.00	8.00



9.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW 25N06	TO-252	2500	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.