

http://hcdz2017.com/

23456789

标记  
MARK

ECN编号/变更内容  
ECN NO/DEFINITION

修改  
REVISE

日期  
DATE

核准  
APPROVE

CKI

DIM A

DIM B

DIM C

2

1.00

3.06

6.90

3

2.00

4.06

7.90

4

3.00

5.06

8.90

5

4.00

6.06

9.90

6

5.00

7.06

10.90

7

6.00

8.06

11.90

8

7.00

9.06

12.90

9

8.00

10.06

13.90

10

9.00

11.06

14.90

11

10.00

12.06

15.90

12

11.00

13.06

16.90

13

12.00

14.06

17.90

14

13.00

15.06

18.90

15

14.00

16.06

19.90

16

15.00

17.06

20.90

17

16.00

18.06

21.90

18

17.00

19.06

22.90

19

18.00

20.06

23.90

20

19.00

21.06

24.90

21

20.00

22.06

25.90

22

21.00

23.06

26.90

23

22.00

24.06

27.90

24

23.00

25.06

28.90

25

24.00

26.06

29.90

26

25.00

27.06

30.90

27

26.00

28.06

31.90

28

27.00

29.06

32.90

29

28.00

30.06

33.90

30

29.00

31.06

34.90

32

31.00

33.06

36.90

1.00

1.00±0.05(PITCH)

A±0.10

1.00

1.40

1.00

2.35

1.00

N-0.20±0.02

2.00

3.20±0.05

1.70

1.2

1.50

1.00±0.05

0.50±0.05

A±0.05

0.30±0.03

3.5 Min.

4.0 Min.

2.00

5.35±0.15

2.00±0.15

0.85±0.05

6.0±0.15

0.10

90°

1.2

2.7

(3.6)

2~11 PIN结构样式

适用扁平线(Applicable Flat Cable)

适用线路板(PCB LAYOUT)

SECTION A-A

技术指标(Technical Index):  
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)  
2. 温度范围(Temperature range): -25° C~85° C.  
3. 额定电压(Rated voltage): 50V, AC/DC(=等效).  
4. 接触电阻(Contact resistance): ≤0.03Ω.  
5. 绝缘电阻(Insulation resistance): ≥500MΩ.

2端子铜镀锡

1胶芯LCP黑色

序号品名材质电镀/颜色备注

品名  
TITLEFPC座

料号  
PART NOHC-FPC-1.0-22P-FH20

GENERAL TOLERANCES  
(UNLESS SPECIFIED)

比列  
SCALE1:1

X. ±.50 .XX ±.10

.X ±.20 .XXX ±.05

ANGLES ±1°

单位  
UNITMM

张数  
PART NO1 OF 1

版本  
REVA

制图  
DRAWAhYe

审核  
CHECKED夏操云

批准  
APPROVE赵亮亮

QR Code

12345678

http://hcdz2017.com/