

1.Description

The IRF7807TR uses advanced trench technology to provide excellent $R_{DS(on)}$ with low gate charge. This device is suitable for use as a load switch or in PWM applications.


3.Application

- Synchronous Rectifier MOSFET for Graphics Cards and POL Converters in Networking and Telecommunication Systems
- Control FET for Notebook Processor Power

4.Pinning information

Pin	Symbol	Description
1,2,3	S	SOURCE
4	G	GATE
5,6,7,8	D	DRAIN

SOP-8



5.Maximum ratings ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Parameter		Symbol	Value	Units
Drain-Source Voltage		V_{DS}	30	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current, V_{GS} @ 10V	$T_A=25^{\circ}\text{C}$	I_D	11	A
Continuous Drain Current, V_{GS} @ 10V	$T_A=70^{\circ}\text{C}$		8.7	
Pulsed Drain Current ①		I_{DM}	88	
Power Dissipation ④	$T_A=25^{\circ}\text{C}$	P_D	2.5	W
Power Dissipation ④	$T_A=70^{\circ}\text{C}$		1.6	
Linear Derating Factor			0.02	W/ $^{\circ}\text{C}$
Operating Junction and Storage Temperature Range		T_J, T_{STG}	-55 to 150	$^{\circ}\text{C}$



UMW IRF7807TR

6.Thermal resist ance rating

Parameter	Symbol	Typ	Max	Units
Junction-to-Drain Lead	$R_{\theta JL}$		20	°C/W
Junction-to-Ambient ⑤	$R_{\theta JA}$		50	°C/W



7. Electrical Characteristics $T_J=25^{\circ}\text{C}$

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain-Source Breakdown Voltage	BV_{DSS}	$I_D=250\mu\text{A}$, $V_{GS}=0\text{V}$	30			V
Breakdown Voltage Temp. Coefficient	$\Delta BV_{DSS}/T_J$	$I_D=1\text{mA}$, Reference to 25°C		0.023		$\text{V}/^{\circ}\text{C}$
Static Drain-to-Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=10\text{V}$, $I_D=11\text{A}$ ③		11	13.8	$\text{m}\Omega$
		$V_{GS}=4.5\text{V}$, $I_D=8.8\text{A}$ ③		14.5	18.2	
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}$, $I_D=250\mu\text{A}$	1.35	1.8	2.25	V
Forward Transconductance	$\Delta V_{GS(th)}$			-4.7		$\text{mV}/^{\circ}\text{C}$
Drain-to-Source Leakage Current	I_{DSS}	$V_{DS}=24\text{V}$, $V_{GS}=0\text{V}$			1	μA
		$V_{DS}=24\text{V}$, $V_{GS}=0\text{V}$, $T_J=125^{\circ}\text{C}$			150	
Gate-to-Source Forward Leakage	I_{GSS}	$V_{GS}=20\text{V}$			100	nA
Gate-to-Source Reverse Leakage		$V_{GS}=-20\text{V}$			-100	
Forward Transconductance	g_{fs}	$V_{DS}=15\text{V}$, $I_D=8.8\text{A}$	22			S
Total Gate Charge	Q_g	$V_{DS}=15\text{V}$ $V_{GS}=4.5\text{V}$ $I_D=8.8\text{A}$ See Fig. 16		7.2	11	nC
Pre-V _{th} Gate-to-Source Charge	Q_{gs1}			2.1		
Post-V _{th} Gate-to-Source Charge	Q_{gs2}			0.7		
Gate-to-Drain Charge	Q_{gd}			2.7		
Gate Charge Overdrive	Q_{godr}			1.7		
Switch Charge ($Q_{gs2} + Q_{gd}$)	Q_{sw}			3.4		
Output Charge	Q_{oss}	$V_{DS}=15\text{V}$, $V_{GS}=0\text{V}$		2.8		nC
Gate Resistance	R_G			2.5	4.8	Ω
Turn-On Delay Time	$t_{D(on)}$	$V_{DD}=15\text{V}$, $V_{GS}=4.5\text{V}$ ③ $I_D=8.8\text{A}$ Clamped Inductive Load		6.9		ns
Rise Time	t_r			6.2		
Turn-Off Delay Time	$t_{D(off)}$			10		
Fall Time	t_f			3.1		
Input Capacitance	C_{iss}	$V_{GS}=0\text{V}$		770		pF
Output Capacitance	C_{oss}	$V_{DS}=15\text{V}$		190		
Reverse Transfer Capacitance	C_{rss}	$f=1.0\text{MHz}$		100		



Avalanche Characteristics						
Single Pulse Avalanche Energy ②					63	mJ
Avalanche Current ①					8.8	A
Source-Drain Ratings and Characteristics						
Continuous Source Current (Body Diode)	I_S	MOSFET symbol showing the integral reverse p-n junction diode.			3.1	A
Pulsed Source Current (Body Diode) ①	I_{SM}				88	
Diode Forward Voltage	V_{SD}	$T_J=25^{\circ}\text{C}, I_S=8.8\text{A}, V_{GS}=0\text{V}$ ③			1	V
Reverse Recovery Time	t_{rr}	$T_J=25^{\circ}\text{C}, I_F=8.8\text{A}, V_{DD}=15\text{V}$		31	46	ns
Reverse Recovery Charge	Q_{rr}	$di/dt=100\text{A}/\mu\text{s}$		17	26	nC

Notes:

① Repetitive rating; pulse width limited by max. junction temperature.(See fig.11)


② Starting $T_J=25^{\circ}\text{C}$, $L=9.8\text{mH}$ $R_G=252$, $I_{AS}=7.3\text{A}$.(See Figure 12)③ $I_{SD}\leq 7.3\text{A}$, $di/dt\leq 100\text{A}/\mu\text{s}$, $V_{DD}\leq V_{(BR)DSS}$, $T_J\leq 150^{\circ}\text{C}$ ④ Pulse width $\leq 300\mu\text{s}$; duty cycle $\leq 2\%$

⑤ Surface mounted on FR-4 board

⑥ Rois measured at T_J approximately 90°C




8.1Typical Characterisitics





8.2Typical Characteristics





8.3Typical Characterisitics




Fig 9. Maximum Avalanche EnergyVs. Drain Current




Fig 10. Maximum Drain Current Vs. Case Temperature




Fig 11. Threshold Voltage Vs. Temperature



8.4Typical Characterisitics




Figure 12: Maximum Effective Transient Thermal Impedance, Junction-to-Ambient



8.5 Typical Characteristics




Fig 12a. Unclamped Inductive Test Circuit




Fig 12b. Unclamped Inductive Waveforms




Fig 13a. Switching Time Test Circuit




Fig 13b. Switching Time Waveforms





Fig 14. Gate Charge Test Circuit



UMW IRF7807TR

9.SOP-8 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	L	θ
Min	1.350	0.000	1.350	0.330	0.170	4.700	3.800	5.800	1.270	0.400	0°
Max	1.750	0.100	1.550	0.510	0.250	5.100	4.000	6.200	BSC	1.270	8°



10.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW IRF7807TR	SOP-8	3000	Tape and reel



11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.