

## 1.Description

This N-Channel logic level enhancement mode field effect transistor is produced using Fairchild's proprietary, high cell density, DMOS technology. This very high density process is especially tailored to minimize on-state resistance.

## 2.Features

- $V_{DS(V)}=20V$
- $I_D=6A(V_{GS}=10V)$
- $R_{DS(ON)}<28m\Omega(V_{GS}=4.5V)$
- $R_{DS(ON)}<42m\Omega(V_{GS}=2.5V)$
- $R_{DS(ON)}<50m\Omega(V_{GS}=1.8V)$



## 3.Applications

- DC/DC Converters
- Load Switch for Portable Applications

## 4.Pinning information

| Pin | Symbol | Description |
|-----|--------|-------------|
| 1   | G      | GATE        |
| 2   | S      | SOURCE      |
| 3   | D      | DRAIN       |

### SOT-23



## 5.Maximum ratings ( $T_A=25^{\circ}C$ unless otherwise noted)

| Parameter                                         |                   | Symbol   | Maximum             | Units |
|---------------------------------------------------|-------------------|----------|---------------------|-------|
| Drain-Source Voltage                              |                   | $V_{DS}$ | 20                  | V     |
| Gate-Source Voltage                               |                   | $V_{GS}$ | $\pm 12$            |       |
| Continuous Drain Current ( $T_J = 150^{\circ}C$ ) | $T_C=25^{\circ}C$ | $I_D$    | 6 <sup>a</sup>      | A     |
|                                                   | $T_C=70^{\circ}C$ |          | 5.1                 |       |
|                                                   | $T_A=25^{\circ}C$ |          | 5 <sup>b,c</sup>    |       |
|                                                   | $T_A=70^{\circ}C$ |          | 4 <sup>b,c</sup>    |       |
| Pulsed Drain Current                              |                   | $I_{DM}$ | 20                  |       |
| Continuous Source-Drain Diode Current             | $T_C=25^{\circ}C$ | $I_S$    | 1.75                |       |
|                                                   | $T_A=25^{\circ}C$ |          | 1.04 <sup>b,c</sup> |       |



|                                                  |                          |                |              |                    |
|--------------------------------------------------|--------------------------|----------------|--------------|--------------------|
| Maximum Power Dissipation                        | $T_C=25^{\circ}\text{C}$ | $P_D$          | 2.1          | W                  |
|                                                  | $T_C=70^{\circ}\text{C}$ |                | 1.3          |                    |
|                                                  | $T_A=25^{\circ}\text{C}$ |                | $1.25^{b,c}$ |                    |
|                                                  | $T_A=70^{\circ}\text{C}$ |                | $0.8^{b,c}$  |                    |
| Operating Junction and Storage Temperature Range |                          | $T_J, T_{STG}$ | -55 to 150   | $^{\circ}\text{C}$ |
| Soldering Recommendations (Peak Temperature)     |                          |                | 260          | $^{\circ}\text{C}$ |

6.Thermal resistance rating

| Parameter                                  |                    | Symbol     | Typ | Max | Units                |
|--------------------------------------------|--------------------|------------|-----|-----|----------------------|
| Maximum Junction-to-Ambient <sup>b,d</sup> | $t \leq 5\text{s}$ | $R_{thJA}$ | 80  | 100 | $^{\circ}\text{C/W}$ |
| Maximum Junction-to-Foot (Drain)           | Steady-State       | $R_{thJF}$ | 40  | 60  | $^{\circ}\text{C/W}$ |

- Notes:
- a. Package limited
  - b. Surface Mounted on 1" x 1" FR4 board.
  - c.  $t = 5\text{ s}$ .
  - d. Maximum under steady state conditions is  $125\text{ }^{\circ}\text{C/W}$ .
  - e. Based on  $TC = 25\text{ }^{\circ}\text{C}$ .



## 7. Electrical Characteristics (T<sub>J</sub>=25°C unless otherwise noted)

| Parameter                                     | Symbol                               | Conditions                                                                                                     | Min  | Typ  | Max  | Units |
|-----------------------------------------------|--------------------------------------|----------------------------------------------------------------------------------------------------------------|------|------|------|-------|
| <b>Static</b>                                 |                                      |                                                                                                                |      |      |      |       |
| Drain-Source Breakdown Voltage                | V <sub>DS</sub>                      | V <sub>DS</sub> =0V, I <sub>D</sub> =250μA                                                                     | 20   |      |      | V     |
| V <sub>DS</sub> Temperature Coefficient       | ΔV <sub>DS</sub> /T <sub>J</sub>     | I <sub>D</sub> =250μA                                                                                          |      | 25   |      | mV/°C |
| V <sub>GS(th)</sub> Temperature Coefficient   | ΔV <sub>GS(th)</sub> /T <sub>J</sub> |                                                                                                                |      | -2.6 |      |       |
| Gate-Source Threshold Voltage                 | V <sub>GS(th)</sub>                  | V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA                                                       | 0.45 |      | 1    | V     |
| Gate-Source Leakage                           | I <sub>GSS</sub>                     | V <sub>DS</sub> =0V, V <sub>GS</sub> =±8V                                                                      |      |      | ±100 | nA    |
| Zero Gate Voltage Drain Current               | I <sub>DSS</sub>                     | V <sub>DS</sub> =20V, V <sub>GS</sub> =0V                                                                      |      |      | 1    | μA    |
|                                               |                                      | V <sub>DS</sub> =20V, V <sub>GS</sub> =0V, T <sub>J</sub> =70°C                                                |      |      | 10   |       |
| On-State Drain Current <sup>a</sup>           | I <sub>D(ON)</sub>                   | V <sub>DS</sub> ≤5V, V <sub>GS</sub> =4.5V                                                                     | 20   |      |      | A     |
| Drain-Source On-State Resistance <sup>a</sup> | R <sub>DS(ON)</sub>                  | V <sub>GS</sub> =4.5V, I <sub>D</sub> =5A                                                                      |      | 28   |      | mΩ    |
|                                               |                                      | V <sub>GS</sub> =2.5V, I <sub>D</sub> =4.7A                                                                    |      | 42   |      |       |
|                                               |                                      | V <sub>DS</sub> =1.8V, I <sub>D</sub> =4.3A                                                                    |      | 50   |      |       |
| Forward Transconductance <sup>a</sup>         | g <sub>FS</sub>                      | V <sub>DS</sub> =10V, I <sub>D</sub> =5A                                                                       |      | 24   |      | S     |
| <b>Dynamic<sup>b</sup></b>                    |                                      |                                                                                                                |      |      |      |       |
| Input Capacitance                             | C <sub>iss</sub>                     | V <sub>DS</sub> =10V, V <sub>GS</sub> =0V, f=1MHz                                                              |      | 865  |      | pF    |
| Output Capacitance                            | C <sub>oss</sub>                     |                                                                                                                |      | 105  |      |       |
| Reverse Transfer Capacitance                  | C <sub>rss</sub>                     |                                                                                                                |      | 55   |      |       |
| Total Gate Charge                             | Q <sub>g</sub>                       | V <sub>DS</sub> =10V, V <sub>GS</sub> =5V<br>I <sub>D</sub> =5A                                                |      | 12   | 18   | nC    |
|                                               |                                      |                                                                                                                |      | 8.8  | 14   |       |
| Gate Source Charge                            | Q <sub>gs</sub>                      | V <sub>DS</sub> =10V, V <sub>GS</sub> =4.5V<br>I <sub>D</sub> =5A                                              |      | 1.1  |      |       |
| Gate Drain Charge                             | Q <sub>gd</sub>                      |                                                                                                                |      | 0.7  |      |       |
| Gate Resistance                               | R <sub>g</sub>                       | f=1MHz                                                                                                         | 0.5  | 2.4  | 4.8  | Ω     |
| Turn-On DelayTime                             | t <sub>D(on)</sub>                   | V <sub>DD</sub> =10V, R <sub>L</sub> =2.2Ω<br>I <sub>D</sub> ≤4A, V <sub>GEN</sub> =4.5V<br>R <sub>g</sub> =1Ω |      | 8    | 16   | ns    |
| Rise Time                                     | t <sub>r</sub>                       |                                                                                                                |      | 17   | 26   |       |
| Turn-Off DelayTime                            | t <sub>D(off)</sub>                  |                                                                                                                |      | 31   | 47   |       |
| Fall Time                                     | t <sub>f</sub>                       |                                                                                                                |      | 8    | 16   |       |



|                                          |              |                                                                      |  |      |      |    |
|------------------------------------------|--------------|----------------------------------------------------------------------|--|------|------|----|
| Turn-On Delay Time                       | $t_{D(on)}$  | $V_{DD}=10V, R_L=2.2\Omega$<br>$I_D=4A, V_{GEN}=5V$<br>$R_g=1\Omega$ |  | 5    | 10   | ns |
| Rise Time                                | $t_r$        |                                                                      |  | 13   | 20   | ns |
| Turn-Off Delay Time                      | $t_{D(off)}$ |                                                                      |  | 21   | 32   | ns |
| Fall Time                                | $t_f$        |                                                                      |  | 6    | 12   | ns |
| Drain-Source Body Diode Characteristics  |              |                                                                      |  |      |      |    |
| Continuous Source-Drain Diode Current    | $I_S$        | $T_C=25^{\circ}C$                                                    |  |      | 1.75 | A  |
| Pulse Diode Forward Current <sup>a</sup> | $I_{SM}$     |                                                                      |  |      | 20   | A  |
| Body Diode Voltage                       | $V_{SD}$     | $I_S=4A, V_{GS}=0V$                                                  |  | 0.75 | 1.2  | V  |
| Body Diode Reverse Recovery Time         | $t_{rr}$     | $I_F=4A, dI/dt=100A/\mu s$<br>$T_J=25^{\circ}C$                      |  | 12   | 20   | ns |
| Body Diode Reverse Recovery Charge       | $Q_{rr}$     |                                                                      |  | 5    | 10   | nC |
| Reverse Recovery Fall Time               | $t_a$        |                                                                      |  | 7    |      | ns |
| Reverse Recovery Rise Time               | $t_b$        |                                                                      |  | 5    |      | ns |


Notes:

a. Pulse test; pulse width  $\leq 300 \mu s$ , duty cycle  $\leq 2\%$ .

b. Guaranteed by design, not subject to production testing.




8.1 Typical Characteristics







## 8.2 Typical Characteristics




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage




Single Pulse Power, Junction-to-Ambient



Safe Operating Area, Junction-to-Ambient




8.3Typical Characterisitics



\* The power dissipation  $P_D$  is based on  $T_{J(max)} = 150\text{ }^{\circ}C$ , using junction-to-case thermal resistance, and is more useful in settling the upperdissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.




8.4Typical Characterisitics







9.SOT-23 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

| Symbol | A     | A1    | L1    | L2    | C     | D     | E     | E1    | B     | B1    | θ  |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|----|
| Min    | 1.050 | 0.000 | 0.300 | 0.350 | 0.100 | 2.820 | 1.500 | 2.700 | 1.800 | 0.950 | 0° |
| Max    | 1.150 | 0.100 | 0.500 | 0.550 | 0.200 | 3.020 | 1.700 | 2.900 | 2.000 | TYP   | 8° |



10.Ordering information



YWW: Batch Code

| Order Code  | Package | Base QTY | Delivery Mode |
|-------------|---------|----------|---------------|
| UMW FDV301N | SOT-23  | 3000     | Tape and reel |



## 11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.