

1.Features

- $V_{DS(V)} = -30V$
- $I_D = -12A (V_{GS} = -10V)$
- $R_{DS(ON)} < 11.9m\Omega (V_{GS} = -10V)$
- $R_{DS(ON)} < 19.7m\Omega (V_{GS} = -4.5V)$



2.Application

- Charge and Discharge Switch for Notebook PC Battery Application

3.Pinning information

Pin	Symbol	Description
1,2,3	S	SOURCE
4	G	GATE
5,6,7,8	D	DRAIN

SOP-8



4.Absolute Maximum Ratings

Parameter		Symbol	Rating	Units
Drain- Source Voltage		V_{DS}	-30	V
Gate-to-Source Voltage		V_{GS}	±20	V
Continuous Drain Current, $V_{GS}=10V$	$T_A=25^{\circ}C$	I_D	-12	A
Continuous Drain Current, $V_{GS}=10V$	$T_A=70^{\circ}C$		-9.6	A
Pulsed Drain Current ①		I_{DM}	-96	A
Power Dissipation ④	$T_A=25^{\circ}C$	P_D	2.5	W
Power Dissipation ④	$T_A=70^{\circ}C$		1.6	W
Linear Derating Factor			0.02	W/°C
Junction and Storage Temperature Range		T_J, T_{STG}	-55 to 150	°C



5. Electrical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Static						
Drain-Source Breakdown Voltage	BV_{DSS}	$I_D = -250\mu\text{A}$, $V_{GS} = 0\text{V}$	-30			V
Breakdown Voltage Temp. Coefficient	$\Delta BV_{DSS}/\Delta T_J$	$I_D = -1\text{mA}$, Reference to 25°C		0.021		V/ $^\circ\text{C}$
Static Drain-to-Source On-Resistance	$R_{DS(ON)}$	$V_{GS} = -10\text{V}$, $I_D = -12\text{A}$ ③		10	11.9	m Ω
		$V_{GS} = -4.5\text{V}$, $I_D = -9.6\text{A}$ ③		16.1	19.7	
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = -25\mu\text{A}$	-1	-1.5	-2	V
Gate Threshold Voltage Coefficient	$\Delta V_{GS(th)}$			-5.8		mV/ $^\circ\text{C}$
Drain-to-Source Leakage Current	I_{DSS}	$V_{DS} = -24\text{V}$, $V_{GS} = 0\text{V}$			-1	μA
		$V_{DS} = -24\text{V}$, $V_{GS} = 0\text{V}$, $T_J = 125^\circ\text{C}$			-150	μA
Gate-to-Source Forward Leakage	I_{GSS}	$V_{GS} = -20\text{V}$			-100	nA
Gate-to-Source Reverse Leakage		$V_{GS} = 20\text{V}$			100	nA
Forward Transconductance	g_{FS}	$V_{DS} = -10\text{V}$, $I_D = -9.6\text{A}$	20			S
Total Gate Charge ⑥	Q_g	$V_{DS} = -15\text{V}$, $V_{GS} = -4.5\text{V}$, $I_D = -9.6\text{A}$		18		nC
Total Gate Charge ⑥	Q_g	$V_{DS} = -10\text{V}$		35	52	nC
Gate-to-Source Charge ⑥	Q_{gs}	$V_{GS} = -15\text{V}$		5.3		nC
Gate-to-Drain Charge ⑥	Q_{gd}	$I_D = -9.6\text{A}$		8.5		nC
Gate Resistance ⑥	R_g			15		Ω
Turn-On Delay Time	$t_{D(on)}$	$V_{DD} = -15\text{V}$, $V_{GS} = -4.5\text{V}$ ③ $I_D = -1\text{A}$ $R_G = 6.8\Omega$ See Figs. 20a & 20b		19		ns
Rise Time	t_r			57		ns
Turn-Off Delay Time	$t_{D(off)}$			80		ns
Fall Time	t_f			66		ns
Input Capacitance	C_{iss}	$V_{GS} = 0\text{V}$		1680		pF
Output Capacitance	C_{oss}	$V_{DS} = -25\text{V}$		350		pF
Reverse Transfer Capacitance	C_{rss}	$f = 1.0\text{MHz}$		220		pF
Avalanche Characteristics						
Single Pulse Avalanche Energy ②	E_{AS}				120	mJ
Avalanche Current ①	I_{AR}				-9.6	A



Diode Characteristics						
Continuous Source Current (Body Diode)	I_S	MOSFET symbol showing the integral reverse p-n junction diode.			-2.5	A
Pulsed Source Current (Body Diode) ①	I_{SM}				-96	
Diode Forward Voltage	V_{SD}		$T_J=25^{\circ}\text{C}, I_S=-2.5\text{A}, V_{GS}=0\text{V}$ ③		-1.2	V
Reverse Recovery Time	t_{rr}	$T_J=25^{\circ}\text{C}, I_F=-2.5\text{A}, V_{DD}=-24\text{V}$		51	76	ns
Reverse Recovery Charge	Q_{rr}	$dI/dt=100\text{A}/\mu\text{s}$ ③		35	53	nC
Thermal Resistance						
Junction-to-Drain Lead ⑤	$R_{\theta JL}$				20	$^{\circ}\text{C}/\text{W}$
Junction-to-Ambient ④	$R_{\theta JA}$				50	$^{\circ}\text{C}/\text{W}$

Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature.
- ② Starting $T_J=25^{\circ}\text{C}$, $L=2.6\text{mH}$, $R_G=25\Omega$, $I_{AS}=-9.6\text{A}$.
- ③ Pulse width $\leq 400\mu\text{s}$; duty cycle $\leq 2\%$.
- ④ When mounted on 1 inch square copper board.
- ⑤ R_{θ} is measured at T_J of approximately 90°C .
- ⑥ For DESIGN AID ONLY, not subject to production testing.



6.1 Typical Characteristics




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics




Fig 3. Typical Transfer Characteristics






Fig 4. Normalized On-Resistance Vs. Temperature

Fig 5. Typical Capacitance Vs.
Drain-to-Source VoltageFig 6. Typical Gate Charge Vs.
Gate-to-Source Voltage



6.2 Typical Characteristics




Fig 7. Typical Source-Drain Diode Forward Voltage




Fig 8. Maximum Safe Operating Area




Fig 9. Maximum Drain Current vs. Ambient Temperature




Fig 10. Threshold Voltage vs. Temperature




Fig 11. On-Resistance vs. Gate Voltage





Fig 12. Typical On-Resistance vs. Drain Current



6.3Typical Characterisitics





6.4 Typical Characteristics




Fig 16a. Gate Charge Test Circuit




Fig 16b. Gate Charge Waveform




Fig 17a. Unclamped Inductive Test Circuit




Fig 17b. Unclamped Inductive Waveforms




Fig 18a. Switching Time Test Circuit





Fig 18b. Switching Time Waveforms



7.SOP-8 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	L	θ
Min	1.350	0.000	1.350	0.330	0.170	4.700	3.800	5.800	1.270	0.400	0°
Max	1.750	0.100	1.550	0.510	0.250	5.100	4.000	6.200	BSC	1.270	8°



8.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW IRF9328TR	SOP-8	3000	Tape and reel



9.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.