

绕线贴片功率电感—SWRH-C 系列

Wire Wound SMD Power Inductors—SWRH-C Series



工作温度 Operating Temp

- ◆ $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$ (Including self-heating)

特征 Features

- ◆ 高饱和电流, 低 DCR
- ◆ 适合表面贴装
- ◆ 闭合磁路结构设计, 减少漏磁
- ◆ High saturation current, low DCR
- ◆ Suitable for surface mounting equipment
- ◆ Close magnetic circuit design reduce leakage


用途 Applications

- ◆ 用于安防、仪器仪表等工业电子和 TV、路由器、游戏机等消费电子的滤波、DC/DC 转换、去耦。
- ◆ Used for filtering, DC/DC conversion, and decoupling in industrial electronics such as security and instrumentation, as well as consumer electronics such as TVs, routers, and game consoles.

产品型号 Product Identification

1	2	3	4	5	6
SWRH	1003	C	-1R0	N	T
1	2	3	4	5	6
分类 Type	外形尺寸 External Dimensions	结构 Configuration	公称电感量 Nominal Inductance	电感公差 Inductance Tolerance	包装 Packing
SWRH	1003~1005	C C Type Base	Example Nominal Value	M $\pm 20\%$ N $\pm 30\%$	T 编带 Tape Carrier Package
绕线贴片功率电感 Wire Wound SMD Type Power Inductors (With Metallic Base)			1R0 1.0 μH 100 10 μH 101 100 μH		

外观尺寸 Shape and Dimensions



Unit: mm

Series	A max.	B max.	C max.	D typ.	I typ.	J typ.	H typ.
SWRH1003C	10.6	10.5	3.0	13.5	1.7	7.3	3.6
SWRH1004C	10.6	10.5	4.0	13.5	1.7	7.3	3.6
SWRH1005C	10.6	10.5	5.2	13.5	1.7	7.3	3.6

规格特性

Specifications

SWRH1003C TYPE

型号 Part Number	电感量 Inductance	L 测试条件 L Test Condition	直流电阻 Max. DC Resistance	额定电流 Max. Rated Current
单位 Units	μH	Hz, V	Ω	A
符号 Symbol	L	-	DCR	I _r
SWRH1003C-1R0NT	1.0±30%	100k, 0.3V	0.009	6.50
SWRH1003C-1R5NT	1.5±30%	100k, 0.3V	0.011	5.80
SWRH1003C-2R2NT	2.2±30%	100k, 0.3V	0.017	5.10
SWRH1003C-3R3NT	3.3±30%	100k, 0.3V	0.021	4.70
SWRH1003C-4R7NT	4.7±30%	100k, 0.3V	0.030	4.00
SWRH1003C-6R8NT	6.8±30%	100k, 0.3V	0.035	3.60
SWRH1003C-8R2NT	8.2±30%	100k, 0.3V	0.050	3.00
SWRH1003C-100MT	10±20%	1k, 0.3V	0.059	2.80
SWRH1003C-150MT	15±20%	1k, 0.3V	0.091	2.05
SWRH1003C-220MT	22±20%	1k, 0.3V	0.143	1.60
SWRH1003C-330MT	33±20%	1k, 0.3V	0.202	1.35
SWRH1003C-470MT	47±20%	1k, 0.3V	0.299	1.20
SWRH1003C-560MT	56±20%	1k, 0.3V	0.325	1.15
SWRH1003C-680MT	68±20%	1k, 0.3V	0.429	0.95
SWRH1003C-820MT	82±20%	1k, 0.3V	0.494	0.80
SWRH1003C-101MT	100±20%	1k, 0.3V	0.683	0.70
SWRH1003C-121MT	120±20%	1k, 0.3V	0.754	0.65
SWRH1003C-151MT	150±20%	1k, 0.3V	0.878	0.62
SWRH1003C-221MT	220±20%	1k, 0.3V	1.625	0.60
SWRH1003C-301MT	300±20%	1k, 0.3V	1.700	0.55
SWRH1003C-331MT	330±20%	1k, 0.3V	1.700	0.50
SWRH1003C-391MT	390±20%	1k, 0.3V	1.900	0.30
SWRH1003C-102MT	1000±20%	1k, 0.3V	4.500	0.23

SWRH1004C TYPE

型号 Part Number	电感量 Inductance	L 测试条件 L Test Condition	直流电阻 Max. DC Resistance	额定电流 Max. Rated Current
单位 Units	μH	Hz, V	Ω	A
符号 Symbol	L	-	DCR	I _r
SWRH1004C-1R5NT	1.5±30%	100k, 0.3V	0.008	6.5
SWRH1004C-2R5NT	2.5±30%	100k, 0.3V	0.011	6.1
SWRH1004C-3R3NT	3.3±30%	100k, 0.3V	0.014	5.6
SWRH1004C-3R8NT	3.8±30%	100k, 0.3V	0.018	5.5
SWRH1004C-4R7NT	4.7±30%	100k, 0.3V	0.022	5.4
SWRH1004C-5R2NT	5.2±30%	100k, 0.3V	0.022	5.4
SWRH1004C-6R2NT	6.2±30%	100k, 0.3V	0.025	5.0
SWRH1004C-6R8NT	6.8±30%	100k, 0.3V	0.025	5.0
SWRH1004C-7R0NT	7.0±30%	100k, 0.3V	0.027	4.5
SWRH1004C-8R2NT	8.2±30%	100k, 0.3V	0.030	4.1
SWRH1004C-100MT	10±20%	1k, 0.3V	0.035	3.8
SWRH1004C-150MT	15±20%	1k, 0.3V	0.050	3.1
SWRH1004C-220MT	22±20%	1k, 0.3V	0.073	2.5
SWRH1004C-330MT	33±20%	1k, 0.3V	0.093	2.2
SWRH1004C-470MT	47±20%	1k, 0.3V	0.128	1.9
SWRH1004C-560MT	56±20%	1k, 0.3V	0.185	1.6
SWRH1004C-680MT	68±20%	1k, 0.3V	0.213	1.42
SWRH1004C-820MT	82±20%	1k, 0.3V	0.275	1.32
SWRH1004C-101MT	100±20%	1k, 0.3V	0.304	1.25
SWRH1004C-151MT	150±20%	1k, 0.3V	0.506	0.85
SWRH1004C-221MT	220±20%	1k, 0.3V	0.756	0.70
SWRH1004C-331MT	330±20%	1k, 0.3V	1.090	0.52

规格特性 Specifications

SWRH1005C TYPE

型号 Part Number	电感量 Inductance	L 测试条件 L Test Condition	直流电阻 Max. DC Resistance	额定电流 Max. Rated Current
单位 Units	μH	Hz, V	Ω	A
符号 Symbol	L	-	DCR	Ir
SWRH1005C-3R3NT	3.3±30%	100k, 0.3V	0.013	6.00
SWRH1005C-4R7NT	4.7±30%	100k, 0.3V	0.016	5.70
SWRH1005C-6R8NT	6.8±30%	100k, 0.3V	0.020	5.35
SWRH1005C-8R2NT	8.2±30%	100k, 0.3V	0.023	5.00
SWRH1005C-100MT	10±20%	1k, 0.3V	0.026	4.45
SWRH1005C-120MT	12±20%	1k, 0.3V	0.033	3.80
SWRH1005C-150MT	15±20%	1k, 0.3V	0.041	3.40
SWRH1005C-180MT	18±20%	1k, 0.3V	0.046	3.10
SWRH1005C-220MT	22±20%	1k, 0.3V	0.061	2.90
SWRH1005C-270MT	27±20%	1k, 0.3V	0.069	2.60
SWRH1005C-330MT	33±20%	1k, 0.3V	0.084	2.40
SWRH1005C-390MT	39±20%	1k, 0.3V	0.106	2.25
SWRH1005C-470MT	47±20%	1k, 0.3V	0.130	2.00
SWRH1005C-560MT	56±20%	1k, 0.3V	0.149	1.90
SWRH1005C-680MT	68±20%	1k, 0.3V	0.201	1.60
SWRH1005C-820MT	82±20%	1k, 0.3V	0.227	1.45
SWRH1005C-101MT	100±20%	1k, 0.3V	0.253	1.35
SWRH1005C-121MT	120±20%	1k, 0.3V	0.303	1.18
SWRH1005C-151MT	150±20%	1k, 0.3V	0.370	1.10
SWRH1005C-181MT	180±20%	1k, 0.3V	0.419	1.00
SWRH1005C-221MT	220±20%	1k, 0.3V	0.500	0.94
SWRH1005C-271MT	270±20%	1k, 0.3V	0.672	0.80
SWRH1005C-331MT	330±20%	1k, 0.3V	0.812	0.73
SWRH1005C-391MT	390±20%	1k, 0.3V	0.953	0.70
SWRH1005C-471MT	470±20%	1k, 0.3V	1.290	0.54
SWRH1005C-561MT	560±20%	1k, 0.3V	1.430	0.52
SWRH1005C-681MT	680±20%	1k, 0.3V	1.600	0.51
SWRH1005C-821MT	820±20%	1k, 0.3V	1.770	0.48