

1

2

3





4

5



6

7

8

RoHS

配插示意图



RECOMMENDED P.C.B BOARD LAYOUT

TABLE 1:

NO.	PART NAME	MATERIALS	DESCRIPTION	REMARK	QTY.
①	WAFER	NYLON UL94-V0		WHITE	1
②	CONTACT PIN	PHOSPHOR BRONZE	G/F, 2u", 3u", 5u", 10u", 15u", 30u", TIN-PLATED		N
③	CONTACT PIN	PHOSPHOR BRONZE	G/F, 2u", 3u", 5u", 10u", 15u", 30u", TIN-PLATED		N
④	SOLDER TAB	BRASS	G/F, TIN-PLATED		2

NOTE(UNLESS OTHERWISE SPECIFIED):

1. ALL MATERIAL MUST BE COMPLY WITH ROHS.
2. PRODUCT PERFORMANCE:

- 2.1 RATED VOLTAGE(MAX.):50V AC/DC
- 2.2 RATED CURRENT(MAX.):1.0A AC/DC
- 2.3 DIELECTRIC STRENGTH:250V AC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL, NO BREAKDOWN
- 2.4 INSULATION RESISTANCE:100 MΩ MIN. 250VDC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL
- 2.5 CONTACT RESISTANCE:30 mΩ MAX.
- 2.6 OPERATING TEMPERATURE:-25°C to +85°C
3. PART NO. LEGEND: 1WF02-325XXX-00XX

CODE
XXX:XX POSITIONS






PART NO.	POLES	DIM A	DIM B
	2*4P	3.00	7.10
1WF02-325010-0001	2*5P	4.00	8.10
1WF02-325012-0001	2*6P	5.00	9.10
	2*7P	6.00	10.10
1WF02-325016-0001	2*8P	7.00	11.10
1WF02-325020-0001	2*10P	9.00	13.10
	2*11P	10.00	14.10
	2*12P	11.00	15.10
	2*13P	12.00	16.10
	2*15P	14.00	18.10
	2*20P	19.00	23.10
	2*25P	24.00	28.10

G	5.0			DRAWING: ZQH	GENERAL TOLERANCE $.X:=\pm 0.30$ $.X^*:=\pm 2^\circ$ $.XX:=\pm 0.20$ $.XX^*:=\pm 1^\circ$ $.XXX:=\pm 0.10$ $.XXX^*:=\pm 0.5^\circ$	
H	4.0			CHECKED: Tianhai	UNIT: MM	PROJECTION:
	3.0				SCALE: 1/1	
	2.0	22.06.07	Update the drawing frame	ZQH	APPROVAL: Cykin	SHEET: 1/1
	1.0	21.06.23	NEW	LWJ		
	REV.	DATE	DESCRIPTION	DRAWING		

CHIN-BAN
Electronic Technology


DESCRIPTION: 1.00mm WTB WAFER H5.6mm SMT TYPE	REV: 2.0
PART NO: 1WF02-325XXX-00XXX	
DRAWING NO: UK0470	SIZE: A4

1 2 3 4 5 6 7 8

RoHS

PACKING INFORMATION: (包装信息)

PART NAME	W	PCS/REEL	REEL/CARTON	TOTAL	CARTON
1WF02-325010-00001	24.0	1000PCS	9PCS	9000PCS	350*350*296mm
1WF02-325012-00001	24.0	1000PCS	9PCS	9000PCS	350*350*296mm
1WF02-325016-00001	24.0	1000PCS	9PCS	9000PCS	350*350*296mm
1WF02-325020-00001	24.0	1000PCS	9PCS	9000PCS	350*350*296mm



2. MATERIAL: (材料)
CARRIER TAPE: POLYSTYREN(PS) (载带: PS)
COVER TAPE: TAPE (盖带: TPE)
REEL TAPE: PS (卷带: PS)
3. PART NUMBER: (料号)
1WF02-325XXX-00001

CHIN-BAN
Electronic Technology

DRAWING:

GENERAL TOLERANCE

.X:=±0.50 .X:=±2°
.XX:=±0.30 .XX:=±1°
.XXX:=±0.20 .XXX:=±0.5°

CHECKED:

Tianhai

APPROVAL:

Cykin

UNIT: MM

PROJECTION:

SCALE: 1:1

SHEET: 1/1

DESCRIPTION:

1.00mm Wafer 双排 卧式 系列 包装图

PART NO: F-1WF02-325XXX-00001 REV: 2.0

DRAWING NO: UT0248 SIZE: A4

G

4.0

3.0

2.0

1.0

NO.

DATE

DESCRIPTION

DRAWING

1

2

3

4

5

6

7

8

A

B

C

D

E

F

G

H