








RoHS+REACH+HF



3D VIEW



SECTION A-A



NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	LCP UL94V-0	WHITE	1
2	STATOR	C2680 T=0.20mm	SURFACE PLATING:TIN PLATING	2
3	TERMINAL	C5191 T=0.20mm	SURFACE PLATING: TIN PLATING/GOLD-PLATED G/F	N/R

NOTE(UNLESS OTHERWISE SPECIFIED):
1. ALL MATERIAL MUST BE COMPLY WITH ROHS+REACH+HF.
2. PRODUCT PERFORMANCE:
2.1 RATED VOLTAGE(MAX.):50V AC/DC
2.2 RATED CURRENT(MAX.):1.0A AC/DC
2.3 DIELECTRIC STRENGTH:500V AC FOR 1 MINUTE BETWEEN ADJACENT
TERMINAL, NO BREAKDOWN
2.4 INSULATION RESISTANCE:100 MΩ MIN. 500VDC FOR 1 MINUTE
BETWEEN ADJACENT TERMINAL
2.5 CONTACT RESISTANCE:20 mΩ MAX.
2.6 OPERATING TEMPERATURE:-25°C to +85°C
3.PART NO. LEGEND: 1WF02-14 X 0XX -0000X

WATER CODE
PIN
3:TUBE 5:REEL(自黏) 7:REEL(热封)


POLES	DIM A	DIM B	DIM C
2P	1.00	4.00	2.60
3P	2.00	5.00	3.60
4P	3.00	6.00	4.60
5P	4.00	7.00	5.60
6P	5.00	8.00	6.60
7P	6.00	9.00	7.60
8P	7.00	10.00	8.60
9P	8.00	11.00	9.60
10P	9.00	12.00	10.60
11P	10.00	13.00	11.60
12P	11.00	14.00	12.60
13P	12.00	15.00	13.60
14P	13.00	16.00	14.60
15P	14.00	17.00	15.60
16P	15.00	18.00	16.60
17P	16.00	19.00	17.60
18P	17.00	20.00	18.60
19P	18.00	21.00	19.60
20P	19.00	22.00	20.60

11.0	22.09.16	Added gold plating specifications for terminals	ZengQiuHong
10.0	22.07.12	Correct product number information	ZQH
9.0	22.03.29	Revise size and product number	ZQH
8.0	19.05.24	Update dimension	LWJ
7.0	17.06.01	Updated version	Tianhai
6.0	16.02.26	Updated version	Tianhai
5.0	16.01.20	Updated version	Tianhai
4.0	15.11.09	Add packaging	Tianhai
REV.	DATE	DESCRIPTION	DRAWING

DRAWING:
LWJ
CHECKED:
APPROVAL:

GENERAL TOLERANCE
.X:=±0.30 .X*:=±2°
.XX:=±0.20 .XX*:=±1°
.XXX:=±0.10 .XXX*:=±0.5°

UNIT: MM
SCALE: 1/1
SHEET: 1/2



CHIN-BAN
Electronic Technology

DESCRIPTION: wafer(P=1.0mm 单排 卧式) 成品图
PART NO: 1WF02-14X0XX-0000X
OLD CODE: WB1002UR-XXXX-XX
DRAWING NO: UK0035
REV: 11.0
SIZE: A4

RoHS+REACH+HF

THE DIMENSION LIST

PIN数	品 号	PIN数	品 号	PIN数	品 号
02PIN	1WF02-143002-00001	07PIN	1WF02-143007-00001	12PIN	1WF02-143012-00001
	1WF02-145002-00001		1WF02-145007-00001		1WF02-145012-00001
	1WF02-147002-00001		1WF02-147007-00001		1WF02-147012-00001
03PIN	1WF02-143003-00001	08PIN	1WF02-143008-00001	13PIN	1WF02-143013-00001
	1WF02-145003-00001		1WF02-145008-00001		1WF02-145013-00001
	1WF02-147003-00001		1WF02-147008-00001		1WF02-147013-00001
04PIN	1WF02-143004-00001	09PIN	1WF02-143009-00001	14PIN	1WF02-145014-00001
	1WF02-145004-00001		1WF02-145009-00001	15PIN	1WF02-145015-00001
	1WF02-147004-00001		1WF02-147009-00001	16PIN	1WF02-145016-00001
05PIN	1WF02-143005-00001	10PIN	1WF02-143010-00001	20PIN	1WF02-145020-00001
	1WF02-145005-00001		1WF02-145010-00001		
	1WF02-147005-00001		1WF02-147010-00001		
06PIN	1WF02-143006-00001	11PIN	1WF02-145011-00001		
	1WF02-145006-00001		1WF02-147011-00001		
	1WF02-147006-00001		1WF02-147011-00002		

11.0	22.09.16	Added gold plating specifications for terminals	ZengQiuHong
10.0	22.07.12	Correct product number information	ZQH
9.0	22.03.29	Revise size and product number	ZQH
8.0	19.05.24	Update dimension	LWJ
7.0	17.06.01	Updated version	Tianhai
6.0	16.02.26	Updated version	Tianhai
5.0	16.01.20	Updated version	Tianhai
4.0	15.11.09	Add packaging	Tianhai
REV.	DATE	DESCRIPTION	DRAWING

DRAWING: LWJ	GENERAL TOLERANCE .X:=±0.30 .X*::=±2° .XX:=±0.20 .XX*::=±1° .XXX:=±0.10 .XXX*::=±0.5°	
	CHECKED:	UNIT: MM
APPROVAL:	SCALE: 1/1	PROJECTION:
	SHEET: 2/2	



DESCRIPTION: wafer(P=1.0mm 单排 卧式) 成品图	
PART NO: 1WF02-14X0XX-0000X	REV: 11.0
OLD CODE: WB1002UR-XXXX-XX	SIZE: A4
DRAWING NO: UK0035	

