




**RoHS+REACH**

NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	INSULATOR	High NYLON (UL94V-0) Temperature Plastic	Natural(Beige)	1
2	CONTACTS	COPPER ALLOY	Tin-Plated	N
3	SOLDER TAP	COPPER ALLOY	Tin-Plated	2



- 1.ELECTRICAL SPECIFICATIONS:
    - 1.1 Rated current and voltage(额定电流):  
1.0A 125V AC(r.m.s)
    - 1.2 Dielectric Withstanding Voltage(耐电压) :  
250V AC for one minute
    - 1.3 Contact Resistance(接触电阻) :  
20mΩ max
    - 1.4 Insulation Resistance(绝缘电阻) :  
100MΩ min
    - 1.5 Operating Temperature(工作温度) :  
-40°C ~ +85°C

## 2. MATERIAL SPECIFICATION

- 2.1 Insulator Material(绝缘体材质):  
HIGH TEMPERATURE PLASTIC  
NYLON,UL94V-0
  - 2.2 Solder Tab Material(焊片脚材质):  
COPPER ALLOY,Tin Plated
  - 2.3 Contact Material(端子材质):  
COPPER ALLOY,Tin Plated
  - 2.4 Applicable wire:AWG#32~#28

**3.PART NO.**







1WF03-32500X-0000

00001: 流水码  
006: 6PIN 见附表

Circuit No.	PART NO	Dimensions		
		A	B	C
02P	1WF03-325002-00001	1.25	7.75	3.05
03P	1WF03-325003-00001	2.50	9.00	4.30
04P	1WF03-325004-00001	3.75	10.25	5.55
05P	1WF03-325005-00001	5.00	11.50	6.80
06P	1WF03-325006-00001	6.25	12.75	8.05
07P	1WF03-325007-00001	7.50	14.00	9.30
08P	1WF03-325008-00001	8.75	15.25	10.55
09P	—	10.00	16.50	11.80
10P	—	11.25	17.75	13.05
11P	—	12.50	19.00	14.30
12P	—	13.75	20.25	15.55
13P	—	15.00	21.50	16.80
14P	—	16.25	22.75	18.05
15P	—	17.50	24.00	19.30
16P	—	18.75	25.25	20.55

**CHIN-BAN**  
Electronic Technology

1 2 3 4 5 6 7 8

**RoHS**

## PACKING INFORMATION:

PART NAME	W	PCS/REEL	REEL/CARTON	TOTAL	CARTON
1WF03-325002-00001	16.0	1000PCS	11PCS	11000PCS	350*350*296mm
1WF03-325003-00001	16.0	1000PCS	11PCS	11000PCS	350*350*296mm
1WF03-325004-00001	24.0	1000PCS	8PCS	8000PCS	350*350*296mm
1WF03-325005-00001	24.0	1000PCS	8PCS	8000PCS	350*350*296mm
1WF03-325006-00001	24.0	1000PCS	8PCS	8000PCS	350*350*296mm
1WF03-325007-00001	24.0	1000PCS	8PCS	8000PCS	350*350*296mm
1WF03-325008-00001	24.0	1000PCS	8PCS	8000PCS	350*350*296mm
	32.0	1000PCS	6PCS	6000PCS	350*350*296mm
	32.0	1000PCS	6PCS	6000PCS	350*350*296mm

DRAWING:  
ShunMingWenGENERAL TOLERANCE  
.X: ±0.50 .X°: ±2°  
.XX: ±0.30 .XX°: ±1°  
.XXX: ±0.20 .XXX°: ±0.5°CHECKED:  
Tianhai

UNIT: MM PROJECTION:

APPROVAL:  
Cykin

SCALE: 1/1 SHEET: 1/1

DESCRIPTION:

1.25PITCH 卧式WAFER-卷装-包装图

**CHIN-BAN**  
Electronic Technology

5.0				
4.0				
3.0				
2.0	22.11.17	新增7PIN规格	ShunMingWen	
1.0	22.09.07	NEW	ShunMingWen	
NO.	DATE	DESCRIPTION	DRAWING	

PART NO: F-1WF03-32500X-0000X REV: 2.0  
DRAWING NO: UT0257 SIZE: A4

1 2 3 4 5 6 7 8