

1.Description

SOP-8 P-Channel enhancement mode power field effect transistors are produced using,high cell density, DMOS technology. This very high density process is especially tailored to minimize on-state resistance and provide superior switching performance

2.2Features

- High power and current handling capability in a widely used surface mount package.

2.1Features



- $V_{DS(V)} = -30V$
- $I_D = -7.9A (V_{GS} = -10V)$
- $R_{DS(ON)} < 23m\Omega (V_{GS} = -10V)$
- $R_{DS(ON)} < 35m\Omega (V_{GS} = -4.5V)$

- High density cell design for extremely low $R_{DS(ON)}$

3.Pinning information

Pin	Symbol	Description
1,2,3	S	SOURCE
4	G	GATE
5,6,7,8	D	DRAIN

SOP-8



4.Absolute Maximum Ratings $T_A = 25^\circ C$

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DSS}	-30	V
Gate-Source Voltage	V_{GSS}	± 20	V
Drain Current - Continuous (Note 1a)	I_D	-7.9	A
- Pulsed		-25	A
Power Dissipation for Single Operation (Note 1a)	P_D	2.5	W
(Note 1b)		1.2	W
(Note 1c)		1	W
Temperature Range	T_J, T_{STG}	-55 to 150	$^\circ C$



5. Thermal Characteristics

Parameter		Symbol	Rating	Units
Thermal Resistance, Junction-to-Ambient	(Note 1a)	$R_{\theta JA}$	50	°C/W
Thermal Resistance, Junction-to-Case	(Note 1)	$R_{\theta JC}$	25	°C/W



6. Electrical Characteristic ($T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=-250\mu A$	-30			V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=-24V, V_{GS}=0V$ $T_J=55^\circ\text{C}$			-1	μA
					-10	μA
Gate - Body Leakage, Forward	I_{GSSF}	$V_{GS}=20V, V_{DS}=0V$			100	nA
Gate - Body Leakage, Reverse	I_{GSSR}	$V_{GS}=-20V, V_{DS}=0V$			-100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=-250\mu A$ $T_J=125^\circ\text{C}$	-1	-1.3	-3	V
			-0.7	-1	-2.2	V
Static Drain-Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=-10V, I_D=-7.9A$		20	23	m Ω
		$V_{GS}=-4.5V, I_D=-6.5A$		30	35	m Ω
On-State Drain Current	$I_{D(ON)}$	$V_{GS}=-10V, V_{DS}=-5V$	-25			A
		$V_{GS}=-4.5V, V_{DS}=-5V$	-10			A
Forward Transconductance	g_{FS}	$V_{DS}=-10V, I_D=-7.9A$		-17		S
Input Capacitance	C_{iss}	$V_{DS}=-15V, V_{GS}=0V, f=1\text{MHz}$		1800		pF
Output Capacitance	C_{oss}			950		pF
Reverse Transfer Capacitance	C_{rss}			240		pF
Turn - On Delay Time	$t_{D(on)}$	$V_{DD}=-10V, I_D=-1A$ $V_{GEN}=-10V, R_{GEN}=6\Omega$		11	22	ns
Turn - On Rise Time	t_r			20	35	ns
Turn - Off Delay Time	$t_{D(off)}$			95	180	ns
Turn - Off Fall Time	t_f			46	100	ns
Total Gate Charge	Q_g	$V_{DS}=-15V, I_D=-7.9A, V_{GS}=-10V$		48	67	nC
Gate-Source Charge	Q_{gs}			6		nC
Gate-Drain Charge	Q_{gd}			12		nC
Maximum Continuous Drain-Source Diode Forward Current	I_S				-2.1	A
Drain-Source Diode Forward Voltage	V_{SD}	$V_{GS}=0V, I_S=-2.1A$ (Note 2)		-0.74	-1.2	V




Notes:

1. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.

$$P_D(t) = \frac{T_J - T_A}{R_{\theta JA(t)}} = \frac{T_J - T_A}{R_{\theta JC} + R_{\theta CA(t)}} = I_D^2(t) \times R_{DS(ON)} @ T_J$$

Typical $R_{\theta JA}$ for single device operation using the board layouts shown below on 4.5"x5" FR-4 PCB in a still air environment:

- 50°C/W when mounted on a 1 in² pad of 2oz copper.
- 105°C/W when mounted on a 0.04 in² pad of 2oz copper.
- 125°C/W when mounted on a 0.006 in² pad of 2oz copper.



Scale 1 : 1 on letter size paper

2. Pulse Test: Pulse Width < 300μs, Duty Cycle < 2.0%.



7.1 Typical characteristic




Figure 1: On-Region Characteristics




Figure 2: On-Resistance Variation with Gate Voltage and Drain Current




Figure 3: On-Resistance Variation with Temperature




Figure 4: On-Resistance Variation with Drain Current and Temperature.




Figure 5: Transfer Characteristics




Figure 6: Gate Threshold Variation with Temperature.



7.2 Typical characteristic




Figure 7: Breakdown Voltage Variation with Temperature




Figure 8: Body Diode Forward Voltage Variation with Current and Temperature




Figure 9: Capacitance Characteristics




Figure 10: Gate Charge Characteristics




Figure 11: Switching Test Circuit




Figure 12: Switching Waveforms



7.3 Typical characteristic




Figure 13: Transconductance Variation with Drain Current and Temperature




Figure 14: SOT-223 Maximum Steady-state Power Dissipation versus Copper Mounting Pad Area




Figure 15: Maximum Steady-State Drain Current versus Copper Mounting Pad Area




Figure 16: Maximum Safe Operating Area





Figure 17: Transient Thermal Response Curve



8.SOP-8 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	L	θ
Min	1.350	0.000	1.350	0.330	0.170	4.700	3.800	5.800	1.270	0.400	0°
Max	1.750	0.100	1.550	0.510	0.250	5.100	4.000	6.200	BSC	1.270	8°



9.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW NDS8435A	SOP-8	3000	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.