


Features

- 324 Watts Peak Pulse Power per Line ($t_p = 8/20\mu s$)
- Protects one I/O or power line
- Low Clamping Voltage
- Working Voltage: 3.3 V
- Low Leakage Current



IEC COMPATIBILITY (EN61000-4)

- IEC 61000-4-2 (ESD) $\pm 30kV$ (air), $\pm 30kV$ (contact)
- IEC 61000-4-4 (EFT) 40A (5/50ns)
- IEC 61000-4-5 (Lightning) 27A (8/20 μs)


Mechanical Characteristics

- JEDEC SOD-323 package
- Molding compound flammability rating: UL 94V-0
- Marking : Marking Code
- Packaging : Tape and Reel per EIA 481
- RoHS Compliant

Applications

- Laptop Computers
- Cellular Phones
- Digital Cameras
- Personal Digital Assistants (PDAs)

Schematic & PIN Configuration




SOD-323 (Top View)

Absolute Maximum Rating

Rating	Symbol	Value	Units
Peak Pulse Power ($t_p = 8/20\mu s$)	P_{PP}	324	Watts
Peak Pulse Current ($t_p = 8/20\mu s$)	I_{PP}	27	A
Operating Temperature	T_J	-55 to + 125	°C
Storage Temperature	T_{STG}	-55 to +150	°C

Electrical Parameters (T=25°C)


Symbol	Parameter
I_{PP}	Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_F	Forward Current
V_F	Forward Voltage @ I_F




Electrical Characteristics

Parameter	Symbol	Conditions	Minimum	Typical	Maximum	Units
Reverse Stand-Off Voltage	V_{RWM}				3.3	V
Reverse Breakdown Voltage	V_{BR}	$I_T = 1mA$	5.0			V
Reverse Leakage Current	I_R	$V_{RWM} = 3.3V, T = 25^\circ C$			0.5	μA
Peak Pulse Current	I_{PP}	$t_p = 8/20\mu s$			27	A
Clamping Voltage	V_C	$I_{PP} = 1A, t_p = 8/20\mu s$		6.5		V
Clamping Voltage	V_C	$I_{PP} = 27A, t_p = 8/20\mu s$		10		V
Junction Capacitance	C_j	$V_R = 0V, f = 1MHz$		150		pF


Typical Characteristics




Non-repetitive peak pulse power vs. Pulse time




Power derating vs. Ambient temperature




Clamping voltage vs. Peak pulse current



Capacitance vs. Reverse voltage




8/20 μs waveform per IEC61000-4-5





Contact discharge current waveform per IEC61000-4-2

Soldering Parameters


Reflow Condition		Pb – Free assembly
Pre Heat	Temperature Min ($T_{S(min)}$)	150°C
	Temperature Max ($T_{S(max)}$)	200°C
	Time (min to max) (t_s)	60 – 190 secs
Average ramp up rate (Liquidus Temp) (T_L) to peak		5°C/second max
$T_{S(max)}$ to T_L ——Ramp-up Rate		5°C/second max
Reflow	Temperature (T_L) (Liquidus)	217°C
	Temperature (t_L)	60 – 150 seconds
Peak Temperature (T_P)		260+0/-5 °C
Time within actual peak Temperature (t_p)		20 – 40 seconds
Ramp-down Rate		5°C/second max
Time 25°C to peak Temperature (T_P)		8 minutes Max.
Do not exceed		280°C



Outline Drawing – SOD-323

PACKAGE OUTLINE 	 SOD-323 DIMENSIONS <table><tr><th rowspan="2">SYMBOL</th><th colspan="2">MILLIMETER</th><th colspan="2">INCHES</th></tr><tr><th>MIN</th><th>MAX</th><th>MIN</th><th>MAX</th></tr><tr><td>A</td><td>1.60</td><td>1.80</td><td>0.063</td><td>0.071</td></tr><tr><td>B</td><td>0.25</td><td>0.35</td><td>0.010</td><td>0.014</td></tr><tr><td>C</td><td>2.50</td><td>2.70</td><td>0.098</td><td>0.106</td></tr><tr><td>D</td><td>0.80</td><td>1.00</td><td>0.000</td><td>0.039</td></tr><tr><td>E</td><td>1.20</td><td>1.40</td><td>0.047</td><td>0.055</td></tr><tr><td>F</td><td>0.08</td><td>0.15</td><td>0.003</td><td>0.006</td></tr><tr><td>L</td><td colspan="2">0.475 REF</td><td colspan="2">0.019REF</td></tr><tr><td>L1</td><td>0.25</td><td>0.40</td><td>0.010</td><td>0.016</td></tr><tr><td>H</td><td>0.00</td><td>0.10</td><td>0.000</td><td>0.004</td></tr></table>	SYMBOL	MILLIMETER		INCHES		MIN	MAX	MIN	MAX	A	1.60	1.80	0.063	0.071	B	0.25	0.35	0.010	0.014	C	2.50	2.70	0.098	0.106	D	0.80	1.00	0.000	0.039	E	1.20	1.40	0.047	0.055	F	0.08	0.15	0.003	0.006	L	0.475 REF		0.019REF		L1	0.25	0.40	0.010	0.016	H	0.00	0.10	0.000	0.004
SYMBOL	MILLIMETER		INCHES																																																				
	MIN	MAX	MIN	MAX																																																			
A	1.60	1.80	0.063	0.071																																																			
B	0.25	0.35	0.010	0.014																																																			
C	2.50	2.70	0.098	0.106																																																			
D	0.80	1.00	0.000	0.039																																																			
E	1.20	1.40	0.047	0.055																																																			
F	0.08	0.15	0.003	0.006																																																			
L	0.475 REF		0.019REF																																																				
L1	0.25	0.40	0.010	0.016																																																			
H	0.00	0.10	0.000	0.004																																																			
MOUNTING PAD 	Notes 1. Controlling Dimensions in Millimeters. 2. Dimensions are exclusive of mold flash and metal burrs.																																																						

Part Numbering System



Device	Package	Shipping	MarKing	Parameter
ST3V3FD322	SOD-323	3000/Tape&Reel	03	03= Product Code