


Features

- Small Body Outline Dimensions:
0.02"x 0.01"(0.6 mm x 0.30 mm)
- Protects one I/O or power line
- Low Clamping Voltage
- Ultra Low Capacitance:15pF
- Working Voltage: $\pm 7V$
- Low Leakage Current



IEC COMPATIBILITY (EN61000-4)

- IEC 61000-4-2 (ESD) $\pm 30kV$ (air), $\pm 30kV$ (contact)
- IEC 61000-4-4 (EFT) 40A (5/50ns)
- IEC 61000-4-5 (Lightning)6A (8/20 μs)


Mechanical Characteristics

- DSN2 package
- Molding compound flammability rating:
UL 94V-0
- Packaging: Tape and Reel per EIA 481
- RoHS/WEEE Compliant

Applications

- Laptop Computers
- Cellular Phones
- Digital Cameras
- Personal Digital Assistants (PDAs)


Schematic & PIN Configuration



Absolute Maximum Rating			
Rating	Symbol	Value	Units
Electrostatic discharge Voltage	V_{ESD}	30KV (contact)	Volts
		30KV (air)	
Peak Pulse Current ($t_p = 8/20\mu s$)	I_{pp}	6	A
Operating Temperature	T_J	-55 to + 125	°C
Storage Temperature	T_{STG}	-55 to +150	°C

Electrical Parameters (TA = 25°C unless otherwise noted)

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current



Note: 8/20 μs pulse waveform.


Electrical Characteristics

Parameter	Symbol	Conditions	Minimum	Typical	Maximum	Units
Reverse Stand-Off Voltage	V_{RWM}				7.0	V
Reverse Breakdown Voltage	V_{BR}	$I_T=1mA$	7.5		9	V
Reverse Leakage Current	I_R	$V_{RWM}=5V$, $T=25^\circ C$			0.5	μA
Clamping Voltage	V_C	$I_{PP}=1A$, $t_p=8/20\mu s$			12	V
Clamping Voltage	V_C	$I_{PP}=6A$, $t_p=8/20\mu s$			16	V
Junction Capacitance	C_j	$V_R = 0V$, $f= 1MHz$		15		pF


Note1: ESD Pulse Waveform according to IEC 61000-4-2. see Table1 and Figure4.

Note2: ESD tests Setup see Figure 5.


Typical Characteristics




Non-repetitive peak pulse power vs. Pulse time




Power derating vs. Ambient temperature




Clamping voltage vs. Peak pulse current



Capacitance vs. Reverse voltage




8/20μs waveform per IEC61000-4-5



Contact discharge current waveform per IEC61000-4-2


Package Outline Dimensions

DFN0603 Package Outline



Symbol	Dimensions In Millimeters		
	Min	Typical	Max
A	0.26	0.32	0.35
D	0.25	0.30	0.35
E	0.55	0.60	0.65
D1	0.20	0.25	0.30
E1		0.35	
L	0.13	0.18	0.23

Part Numbering System



Device	Package	Shipping	MarKing	Parameter
SE7VFBN062	DFN0603-2L	10000/Tape&Reel	A *	A = Product Code 7 = Device Code