

1.Description

The PESDNC5D5VB protects sensitive semiconductor components from damage or upset due to electrostatic discharge (ESD) and other voltage induced transient events. They feature large cross-sectional area junctions for conducting high transient currents, offer desirable electrical characteristics for board level protection, such as fast response time, low operating voltage.

3.Applications

- Cellular phones
- Portable devices

4.Mechanical Characteristics


- Lead finish:100% matte Sn(Tin) Mounting
- position: Any
- Qualified max reflow temperature:260°C

2.Features

- 80W peak pulse power per line ($t_p=8/20\mu s$)
 - Replacement for MLV(0603)
 - Bidirectional configurations
 - Protects one power or I/O port
 - Low clamping voltage
- Transient protection for data lines to IEC
61000-4-2(ESD)+30KV(air),+30KV(contact);
IEC 61000-4-4(EFT)40A(5/50ns)

- Digital cameras
- Power supplies

5.Pinning information



SOD-523



6. Absolute Maximum Ratings $T_A = 25^\circ\text{C}$


| Parameter | Symbol | Value | Units |
|--|-----------|-------------|------------------|
| Peak Pulse Power ($t_p=8/20\mu\text{s}$) | P_{PP} | 80 | W |
| Junction Temperature | T_J | -55 to +150 | $^\circ\text{C}$ |
| Storage Temperature | T_{STG} | -55 to +150 | $^\circ\text{C}$ |



7. Electrical Characteristic ($T_A=25^\circ\text{C}$ unless otherwise noted)

| Parameter | Symbol | Conditions | Min | Typ | Max | Units |
|------------------------------|-----------|--|-----|-----|-----|---------------|
| Peak Reverse Working Voltage | V_{RWM} | | | | 5 | V |
| Breakdown Voltage | V_{BR} | $I_T=1\text{mA}$ | 6 | | 8 | V |
| Reverse Leakage Current | I_R | $V_{RWM}=5\text{V}$, $T=25^\circ\text{C}$ | | | 1 | μA |
| Junction Capacitance | C_J | $V_R=0\text{V}$, $f=1\text{MHz}$ | | 20 | | pF |


8. Electrical Parameters ($T_A=25^\circ\text{C}$ unless otherwise noted)



| Symbol | Parameter |
|-----------|-------------------------------------|
| V_{RWM} | Peak Reverse Working Voltage |
| I_R | Reverse Leakage Current @ V_{RWM} |
| V_{BR} | Breakdown Voltage @ I_T |
| I_T | Test Current |
| I_{PP} | Maximum Reverse Peak Pulse Current |
| V_C | Clamping Voltage @ I_{PP} |
| P_{PP} | Peak Pulse Power |
| C_J | Junction Capacitance |
| I_F | Forward Current |
| V_F | Forward Voltage @ I_F |



9. Typical characteristic





10. Solder Reflow Recommendation





Figure 5: Peak Temp=257°C, Ramp Rate=0.802deg. °C/sec

For TVS diodes a low-ohmic and low-inductive path to chassis earth is absolutely mandatory in order to achieve good ESD protection. Novices in the area of ESD protection should take following suggestions to heart:

- Do not use stubs, but place the cathode of the TVS diode directly on the signal trace.
- Do not make false economies and save copper for the ground connection.
- Place via holes to ground as close as possible to the anode of the TVS diode.
- Use as many via holes as possible for the ground connection.
- Keep the length of via holes in mind! The longer the more inductance they will have.



11.SOD-523 Package Outline Dimensions



DIMENSIONS (mm are the original dimensions)

| Symbol | A | b _p | C | D | E | H _E | θ |
|--------|------|----------------|-------|------|------|----------------|----|
| Min | 0.58 | 0.3 | 0.100 | 1.15 | 0.75 | 1.5 | 5° |
| Max | 0.68 | 0.4 | 0.135 | 1.25 | 0.85 | 1.7 | |



12.Ordering information



yww: Batch Code

| Order Code | Package | Base QTY | Delivery Mode |
|-----------------|---------|----------|---------------|
| UMW PESDNC5D5VB | SOD-523 | 3000 | Tape and reel |



13.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.