

1.Description

The AOD210 uses Trench MOSFET technology that is uniquely optimized to provide the most efficient high frequency switching performance. Power losses are minimized due to an extremely low combination of $R_{DS(ON)}$ and C_{rss} .


2.Features

- $V_{DS(V)}=30V$
- $I_D=70A(V_{GS}=10V)$
- $R_{DS(ON)}\leq 3m\Omega(V_{GS}=10V)$
- $R_{DS(ON)}\leq 3.9m\Omega(V_{GS}=4.5V)$

3.Pinning information

Pin	Symbol	Description
1	G	GATE
3	S	SOURCE
2	D	DRAIN

TO-252(DPAK)
top view



4.Absolute Maximum Ratings $T_A=25^{\circ}C$

Parameter		Symbol	Rating	Units
Drain-Source Voltage		V_{DS}	30	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ^G	$T_C=25^{\circ}C$	I_D	70	A
	$T_C=100^{\circ}C$		55	
Pulsed Drain Current ^C		I_{DM}	390	
Continuous Drain Current	$T_A=25^{\circ}C$	I_{DSM}	23	
	$T_A=70^{\circ}C$		18	
Avalanche Current ^C		I_{AS}, I_{AR}	68	
Avalanche energy $L=0.1mH$ ^C		E_{AS}, E_{AR}	231	mJ
Power Dissipation ^B	$T_C=25^{\circ}C$	P_D	150	W
	$T_C=100^{\circ}C$		75	
Power Dissipation ^A	$T_A=25^{\circ}C$	P_{DSM}	2.7	
	$T_A=70^{\circ}C$		1.7	
Junction and Storage Temperature Range		T_J, T_{STG}	-55 to 175	$^{\circ}C$



5.Thermal Characteristics

Parameter		Symbol	Typ	Max	Units
Maximum Junction-to-Ambient ^A	t ≤ 10s	R _{θJA}	14.2	17	°C/W
Maximum Junction-to-Ambient ^{AD}	Steady-State		39	47	°C/W
Maximum Junction-to-Case	Steady-State	R _{θJC}	0.8	1	°C/W



6. Electrical Characteristic (T_J=25°C unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain-Source Breakdown Voltage	BV _{DSS}	I _D =250μA, V _{GS} =0V	30			V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =30V, V _{GS} =0V			1	μA
		T _J =55°C			5	μA
Gate-Body leakage current	I _{GSS}	V _{DS} =0V, V _{GS} =±20V			100	nA
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250μA	1	1.7	2.2	V
On state drain current	I _{D(ON)}	V _{GS} =10V, V _{DS} =5V	390			A
Static Drain-Source On-Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =20A		2.4	3	mΩ
		V _{GS} =4.5V, I _D =20A		2.95	3.9	mΩ
Forward Transconductance	g _{FS}	V _{DS} =5V, I _D =20A		78		S
Diode Forward Voltage	V _{SD}	I _S =1A, V _{GS} =0V		0.65	1	V
Maximum Body-Diode Continuous Current ^G	I _S				70	A
Input Capacitance	C _{iss}	V _{GS} =0V, V _{DS} =15V, f=1MHz	2800	3520	4300	pF
Output Capacitance	C _{oss}		920	1320	1720	pF
Reverse Transfer Capacitance	C _{rss}		50	90	155	pF
Gate resistance	R _g	V _{GS} =0V, V _{DS} =0V, f=1MHz	0.5	1	1.5	Ω
Total Gate Charge	Q _g (10V)	V _{GS} =10V, V _{DS} =15V I _D =20A	39	48	58	nC
Total Gate Charge	Q _g (4.5V)		17	22	27	nC
Gate Source Charge	Q _{gs}		7	9	11	nC
Gate Drain Charge	Q _{gd}		4	7	10	nC
Turn-On DelayTime	t _{D(on)}	V _{GS} =10V, V _{DS} =15V R _L =0.75Ω, R _{GEN} =3Ω		11		ns
Turn-On Rise Time	t _r			10		ns
Turn-Off DelayTime	t _{D(off)}			38		ns
Turn-Off Fall Time	t _f			10		ns
Body Diode Reverse Recovery Time	t _{rr}	I _F =20A, dI/dt=500A/μs	14	21	28	ns
Body Diode Reverse Recovery Charge	Q _{rr}	I _F =20A, dI/dt=500A/μs	40	58	76	nC



- A. The value of $R_{\theta JA}$ is measured with the device mounted on 1in2 FR-4 board with 2oz. Copper, in a still air environment with $T_A = 25^\circ\text{C}$. The Power dissipation P_{DSM} is based on $R_{\theta JA}$ and the maximum allowed junction temperature of 150°C . The value in any given application depends on the user's specific board design, and the maximum temperature of 175°C may be used if the PCB allows it.
- B. The power dissipation P_D is based on $T_{J(MAX)} = 175^\circ\text{C}$, using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heatsinking is used.
- C. Repetitive rating, pulse width limited by junction temperature $T_{J(MAX)} = 175^\circ\text{C}$. Ratings are based on low frequency and duty cycles to keep initial $T_J = 25^\circ\text{C}$.
- D. The $R_{\theta JA}$ is the sum of the thermal impedance from junction to case $R_{\theta JC}$ and case to ambient.
- E. The static characteristics in Figures 1 to 6 are obtained using $< 300\mu\text{s}$ pulses, duty cycle 0.5% max.
- F. These curves are based on the junction-to-case thermal impedance which is measured with the device mounted to a large heatsink, assuming a maximum junction temperature of $T_{J(MAX)} = 175^\circ\text{C}$. The SOA curve provides a single pulse rating.
- G. The maximum current rating is package limited.
- H. These tests are performed with the device mounted on 1 in2 FR-4 board with 2oz. Copper, in a still air environment with $T_A = 25^\circ\text{C}$.



7.1 Typical characteristic




Fig 1: On-Region Characteristics (Note E)




Figure 2: Transfer Characteristics (Note E)




Figure 3: On-Resistance vs. Drain Current and Gate Voltage (Note E)




Figure 4: On-Resistance vs. Junction Temperature (Note E)




Figure 5: On-Resistance vs. Gate-Source Voltage (Note E)




Figure 6: Body-Diode Characteristics (Note E)



7.2 Typical characteristic




Figure 7: Gate-Charge Characteristics




Figure 8: Capacitance Characteristics




Figure 9: Maximum Forward Biased Safe Operating Area (Note F)




Figure 10: Single Pulse Power Rating Junction-to-Case (Note F)




Figure 11: Normalized Maximum Transient Thermal Impedance (Note F)



7.3 Typical characteristic




Figure 12: Gate-Charge Characteristics




Figure 13: Capacitance Characteristics




Figure 14: Single Pulse Avalanche capability (Note C)




Figure 15: Maximum Forward Biased Safe Operating Area (Note F)





Figure 16: Normalized Maximum Transient Thermal Impedance (Note H)



8.TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A1	A2	A3	b	c	D	D1	D2	E	E1	E2	e	L1	L2	L3	θ
Min	0.00	2.18	0.90	0.65	0.46	6.35	4.95	4.32	9.40	5.97	5.21	2.286 BSC	0.89	1.70	0.60	0.00
Max	0.13	2.39	1.10	0.85	0.61	6.73	5.46	4.90	10.41	6.22	5.38		1.27	1.90	1.00	8.00



9.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW AOD210	TO-252	2500	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.