


### Features

- 240Watts peak pulse power ( $t_p = 8/20\mu s$ )
- Solid-state silicon-avalanche technology
- Low clamping voltage
- Low leakage current
- Protection one data/power line
- IEC 61000-4-2  $\pm 30kV$  contact  $\pm 30kV$  air
- IEC 61000-4-4 (EFT) 40A (5/50ns)
- IEC 61000-4-5 (Lightning) 10A (8/20 $\mu s$ )




### Applications

- Cell Phone Handsets and Accessories
- Microprocessor based equipment
- Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- Portable Instrumentation

### Mechanical Data

- SOD-523 package
- Molding compound flammability rating: UL 94V-0
- Packaging: Tape and Reel
- RoHS/WEEE Compliant

### Schematic & PIN Configuration




SOD-523 (Top View)

### Absolute Maximum Rating

Rating	Symbol	Value	Units
Peak Pulse Power ( $t_p = 8/20\mu s$ )	$P_{PP}$	240	Watts
Peak Pulse Current ( $t_p = 8/20\mu s$ )(note1)	$I_{PP}$	10	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	$V_{ESD}$	30 30	kV
Lead Soldering Temperature	$T_L$	260(10seconds)	°C
Junction Temperature	$T_J$	-55 to + 125	°C
Storage Temperature	$T_{stg}$	-55 to + 125	°C

### Electrical Parameters (TA = 25°C unless otherwise noted)

Symbol	Parameter
$I_{PP}$	Maximum Reverse Peak Pulse Current
$V_C$	Clamping Voltage @ $I_{PP}$
$V_{RWM}$	Working Peak Reverse Voltage
$I_R$	Maximum Reverse Leakage Current @ $V_{RWM}$
$V_{BR}$	Breakdown Voltage @ $I_T$
$I_T$	Test Current




Note: 8/20 $\mu s$  pulse waveform.


### Electrical Characteristics

Parameter	Symbol	Conditions	Min	Typical	Max	Units
Reverse Stand-Off Voltage	$V_{RWM}$				12	V
Reverse Breakdown Voltage	$V_{BR}$	$I_T = 1mA$	13.5			V
Reverse Leakage Current	$I_R$	$V_{RWM} = 12V, T = 25^\circ C$			0.1	$\mu A$
Peak Pulse Current	$I_{PP}$	$t_p = 8/20\mu s$		10		A
Clamping Voltage	$V_C$	$I_{PP} = 10A, t_p = 8/20\mu s$		24		V
Junction Capacitance	$C_j$	$V_R = 0V, f = 1MHz$		50		pF


### Typical Characteristics




**Non-repetitive peak pulse power vs. Pulse time**




**Power derating vs. Ambient temperature**




**Clamping voltage vs. Peak pulse current**



**Capacitance vs. Reverse voltage**






**8/20μs waveform per IEC61000-4-5**



**Contact discharge current waveform per IEC61000-4-2**


### Outline Drawing – SOD-523



DIMENSIONS: MILLIMETERS

DIMENSIONS				
SYMBOL	MILLIMETER		INCHES	
	MIN	MAX	MIN	MAX
A	0.50	0.70	0.020	0.028
b	0.25	0.35	0.010	0.014
C	0.07	0.20	0.0028	0.0079
D	1.10	1.30	0.043	0.051
E	0.70	0.90	0.028	0.035
H <sub>E</sub>	1.50	1.70	0.059	0.067
L	0.15	0.25	0.006	0.010

### Part Numbering System



Device	Package	Shipping	MarKing	Parameter
SE12VFD522	SOD-523	3000/Tape&Reel	ZM*	ZM= Product Code * = Device Code