

SOT-89 Plastic-Encapsulate MOSFETS

Features

- VDS=100V
- ID=3.4A
- RDS(on)@VGS=10V < 100mΩ
- RDS(on)@VGS=4.5V < 130mΩ
- Avalanche energy tested
- Fast Switching Speedze
- Improved dv/dt capability, high ruggedness


Applications

- Battery protection
- Load switch
- Power management


Mechanical Data

- Case: SOT-89
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Drain-source Voltage
100 V
Drain Current
3.4 Ampere



Ordering Information

Table with 7 columns: PACKAGE, PACKAGE CODE, UNIT WEIGHT(g), REEL(pcs), BOX(pcs), CARTON(pcs), DELIVERY MODE. Row 1: SOT-89, R1, 0.045, 1000, 8000, 48000, 7"

Maximum Ratings (Ta=25°C Unless otherwise specified)

Table with 4 columns: PARAMETER, SYMBOL, UNIT, VALUE. Rows include: Drain-source Voltage (VDS, V, 100), Gate-source Voltage (VGS, V, ±20), Drain Current (ID, A, 3.4), Pulsed Drain Current (IDM, A, 16), Total Power Dissipation (PD, W, 2), Junction temperature (TJ, °C, -55 ~+150), Storage temperature (Tstg, °C, -55 ~+150), Thermal Resistance Junction-to-Ambient (RθJA, °C / W, 62).

● Static Parameter Characteristics (T_j=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0V, I _D =250μA	V	100	—	—
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =100V, V _{GS} =0V	μA	—	—	1.0
Gate-Body Leakage Current	I _{GSS}	V _{GS} = ±20V, V _{DS} =0V	nA	—	—	±100
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D =250μA	V	1.0	1.65	2.5
Static Drain-Source On-Resistance ⁽²⁾	R _{DS(on)}	V _{GS} = 10V, I _D =3A	mΩ	—	86	100
		V _{GS} = 4.5V, I _D =1A		—	113	130

● Dynamic Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C _{iss}	V _{DS} =50V, V _{GS} =0V, f=1MHZ	pF	—	210	—
Output Capacitance	C _{oss}			—	30	—
Reverse Transfer Capacitance	C _{rss}			—	2	—

● Switching Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	t _{D(on)}	V _{GS} =10V, V _{DD} =50V, I _D =1.5A, R _{GEN} =1Ω	nS	—	15	—
Turn-on Rise Time	t _r		nS	—	5	—
Turn-off Delay Time	t _{D(off)}		nS	—	22	—
Turn-off fall Time	t _f		nS	—	3	—
Total Gate Charge	Q _g	V _{DS} =50V, I _D =3A V _{GS} =10V	nC	—	4	—
Gate-Source Charge	Q _{gs}		nC	—	2	—
Gate-Drain Charge	Q _{gd}		nC	—	1	—

● Drian-Source Diode Characteristics







PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Diode Forward Voltage	V _{SD}	I _S =3A, V _{GS} =0V	V	—	—	1.2
Maximum Body-Diode Continuous Current	I _S	—	A	—	—	3.4

Note :






(1) Repetitive Rating: Pulse width limited by maximum junction temperature.

(2) Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.

● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




Fig.12 Normalized Maximum Transient Thermal Impedance

● Package Outline Dimensions (SOT-89)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.4	4.6	0.176	0.184
B	1.6	1.8	0.064	0.072
C	3.9	4.1	0.156	0.164
D	2.4	2.6	0.096	0.104
E	2.9	3.1	0.116	0.124
a	0.41	0.43	0.0164	0.018
b	0.35	0.45	0.014	0.018
L	0.95	1.05	0.037	0.041
G	0.3	0.5	0.012	0.020
H	1.4	1.5	0.055	0.059

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
c	0.80	1.00	0.032	0.04
d	1.30	1.50	0.052	0.060
e	0.70	0.90	0.028	0.036
J	1.80	2.00	0.072	0.080
K	1.40	1.60	0.056	0.064
X	2.50	2.70	0.100	0.108
X1	1.30	1.50	0.052	0.060
Y	4.30	4.50	0.172	0.180
Y1	3.10	3.30	0.124	0.132
θ	-	45°	-	45°


1. Gate Charge Test Circuit & Waveforms



2. Resistive Switching Test Circuit & Waveforms



3. Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



4. Diode Recovery Test Circuit & Waveforms

