

SOP-8 Plastic-Encapsulate MOSFETS

Features

- $V_{DS}=-60V$
- $I_D=-8A$
- $R_{DS(on)}@V_{GS}=-10V < 40m\Omega$
- $R_{DS(on)}@V_{GS}=-4.5V < 50m\Omega$
- Low Gate Charge and R_{dson}
- Fast Switching Speedze
- Improved dv/dt capability, high ruggedness


Applications

- DC/DC Converter
- Hard switched and high frequency circuits
- Uninterruptible Power Supply

Mechanical Data

- Case: SOP-8
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOP-8	R3	0.077	4000	8000	48000	13"

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Drain-source Voltage	V_{DS}	V	-60
Gate-source Voltage	V_{GS}	V	± 20
Drain Current	I_D	A	-8
Pulsed Drain Current ⁽¹⁾	I_{DM}	A	-32
Total Power Dissipation	P_D	W	3.1
Single pulse avalanche energy ⁽²⁾	EAS	mJ	12
Junction temperature	T_J	°C	-55 ~+150
Storage temperature	T_{stg}	°C	-55 ~+150
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	°C / W	40

Drain-source Voltage
-60 V
Drain Current
-8 Ampere



● Static Parameter Characteristics (Tj=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0V, I _D =-250μA	V	-60	—	—
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =-48V, V _{GS} =0V	μA	—	—	-1.0
Gate-Body Leakage Current	I _{GSS}	V _{GS} = ±20V, V _{DS} =0V	nA	—	—	±100
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D =-250μA	V	-1.0	-1.7	-2.5
Static Drain-Source On-Resistance ⁽³⁾	R _{DS(ON)}	V _{GS} = -10V, I _D =-6.2A	mΩ	—	27	40
		V _{GS} = -4.5V, I _D =-5A		—	34	50

● Dynamic Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C _{iss}	V _{DS} =-30V, V _{GS} =0V, f=1MHZ	pF	—	3050	—
Output Capacitance	C _{oss}			—	169	—
Reverse Transfer Capacitance	C _{rss}			—	156	—

● Switching Parameters







PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	t _{D(on)}	V _{GS} =-10V, V _{DD} =-30V, I _D =-6.2A ,R _{GEN} =3Ω	nS	—	9.9	—
Turn-on Rise Time	t _r		nS	—	6.2	—
Turn-off Delay Time	t _{D(off)}		nS	—	44	—
Turn-off fall Time	t _f		nS	—	12.8	—
Total Gate Charge	Q _g	V _{DS} =-30V, I _D =-6.2A V _{GS} =-10V	nC	—	58.5	—
Gate-Source Charge	Q _{gs}		nC	—	9.6	—
Gate-Drain Charge	Q _{gd}		nC	—	15.7	—

● Drian-Source Diode Characteristics






PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Diode Forward Voltage	V _{SD}	I _S =-1A, V _{GS} =0V	V	—	—	-1.2
Maximum Body-Diode Continuous Current	I _S	—	A	—	—	-8

Note :
(1)Repetitive Rating: Pulse width limited by maximum junction temperature.
(2)EAS condition : Tj=25°C ,VDD=-30V,VG=-10V,L=0.5mH,IAS=-7A,Rg=25Ω.
(3)Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)





● Package Outline Dimensions (SOP-8)





● Suggested Pad Layout





1. Gate Charge Test Circuit & Waveforms



2. Resistive Switching Test Circuit & Waveforms



3. Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



4. Diode Recovery Test Circuit & Waveforms

