


1. Dual SMT package contains transmit and receive transformers
2. Matched to leading transceiver ICs.
3. Design to meet ITU-T G.703
4. Operating temperature range:0℃ to +70℃
5. Reflow Condition:Maximum reflow temperature is 240℃~245℃, time is 20~40 sec.(Refer to IPC/JEDEC J-STD 020C standard)




DIMENSIONS & SCHEMATICS



Unless otherwise specified, all tolerances are $\pm \frac{.010}{0.25}$ Dimensions: Inches mm


Note: 1、Dimension: inches/mm 2.Unless otherwise specified,tolerances are: $\pm 0.15\text{mm}$



TECHNICAL SPECIFICATIONS

OCL :	1.2mH Min.@ 100KHz 0.1V
Leakage Inductance:	0.6 μ H Max @ 100KHz 0.1V
Cw/w:	30pF Max@ 100KHz 0.1V
DCR:	1.30 Ω Max.
Turns Ratio($\pm 2\%$):	TX:1CT:1CT RX:1CT:2CT
Primary Pins:	TX:1-3 RX:6-8

PACKING SPECIFICATION



1. units/reel:600PCS
2. reel/carton:5PCS
3. units/carton :3000PCS

EXPORT CARTON:367(L)x337(W)x235(H)