



1	2	3	4	5	6	7	8
REV.	REVISION DESCRIPTION					DATE	APPD

- NOTES:
- 1. Rated voltage: 125V AC/DC
 - 2. Rated current: 1A AC/DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 100\text{ M}\Omega$
 - 5. Withstand voltage: 500V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : Nylon UL94V-0(2)
 - 8. Matched RoHS criteria



Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2X2	MHD1.25-4Y	1.25	/	2.95	2X9	MHD1.25-18Y	10.00	8.75	11.70
2X3	MHD1.25-6Y	2.50	1.25	4.20	2X10	MHD1.25-20Y	11.25	10.00	12.95
2X4	MHD1.25-8Y	3.75	2.50	5.45	2X11	MHD1.25-22Y	12.50	11.25	14.20
2X5	MHD1.25-10Y	5.00	3.75	6.70	2X12	MHD1.25-24Y	13.75	12.50	15.45
2X6	MHD1.25-12Y	6.25	5.00	7.95	2X13	MHD1.25-26Y	15.00	13.75	16.70
2X7	MHD1.25-14Y	7.50	6.25	9.20	2X14	MHD1.25-28Y	16.25	15.00	17.95
2X8	MHD1.25-16Y	8.75	7.50	10.45	2X15	MHD1.25-30Y	17.50	16.25	19.20


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL12514 (MHD1.25)-Y	TITLE: 1.25 mm Pitch Wire To Wire Housing
.XX: ± 0.15	.X° : ± 2.0°	DR: Chen Quan Long	DATE:24/01/09
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:24/01/09	PART NO:
FINISH:	CHKD: Wu Hui	DATE:24/01/09	SCALE: N/A
DRAWING NO:	APPD:Ren An De	DATE:24/01/09	PAGE: 1/1
		UNITS: mm	REV.: A



7		8	
REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
1. Rated voltage: 125V AC/DC
2. Rated current: 1A AC/DC
3. Contact resistance: $\leq 20\text{ m}\Omega$
4. Insulation resistance: $\geq 100\text{ M}\Omega$
5. Withstand voltage: 500V AC/minute
6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
7. Material : Nylon UL94V-0(2)
8. Matched RoHS criteria

Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2X2	MHD1.25-4R	1.25	4.25	3.00	2X9	MHD1.25-18R	10.00	13.00	11.75
2X3	MHD1.25-6R	2.50	5.50	4.25	2X10	MHD1.25-20R	11.25	14.25	13.00
2X4	MHD1.25-8R	3.75	6.75	5.50	2X11	MHD1.25-22R	12.50	15.50	14.25
2X5	MHD1.25-10R	5.00	8.00	6.75	2X12	MHD1.25-24R	13.75	16.75	15.50
2X6	MHD1.25-12R	6.25	9.25	8.00	2X13	MHD1.25-26R	15.00	18.00	16.75
2X7	MHD1.25-14R	7.50	10.50	9.25	2X14	MHD1.25-28R	16.25	19.25	18.00
2X8	MHD1.25-16R	8.75	11.75	10.50	2X15	MHD1.25-30R	17.50	20.50	19.25

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL12514(MHD1.25)-R	TITLE: 1.25 mm Pitch Wire To Wire Housing
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE:24/01/09
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE:24/01/09
FINISH: 		APPD:Ren An De	DATE:24/01/09
DRAWING NO:		UNITS: mm	REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in DL12514-Y Series Housing.

Accepts AWG #28~32 Wire Range.

0.08~ 0.032 mm² .




Insulation O.D.=0.5~1.0 mm.

Material : Phosphor Bronze .


Finish: Tin plated.

Qty/Reel: 10,000 PCS.


Thickness: 0.15 mm.



SECTION A-A




SECTION B-B



SECTION C-C

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:	TITLE:
.XX: ± 0.15	.X° : ± 2.0°	DL12514 (MHD1.25) -T	1.25 mm Pitch Crimp Terminal
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Chen Quan Long	DATE: 19/08/01
FINISH:		CHKD: Wu Hui	DATE: 19/08/01
DRAWING NO:		APPD: Ren An De	DATE: 19/08/01
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A



REV.	7	REVISION DESCRIPTION	8	DATE	APPD

NOTES

Used in DL12514-R Series Housing.
Accepts AWG #28~32 Wire Range.
0.08~ 0.032 mm² .
Insulation O.D.=0.5~1.0 mm.
Material : Phosphor Bronze .
Finish: Tin plated.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	.X° : ± 2.0°	DL12514(MHD1.25)-RT		1.25 mm Pitch Crimp Terminal	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:19/08/01	PART NO:	
FINISH:		CHKD: Wu Hui	DATE:19/08/01	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD:Ren An De	DATE:19/08/01	UNITS: mm	REV. : A