




SMD PULSE TRANSFORMER


Meets IEEE 802.3af Standards.
Designed For 1G BASE-T Applications, Surface Mount Type.
Operating Temperature Range: -40 °C to +85°C.
RoHS Compliant.
350mA Current Capability

Part Number	Electrical Specifications @25°C						
	Turns Ratio (±5%)	OCL(uH Min) @100KHz,0.1V With10.5mADC Bias	CWW(pF Max) @100KHz,0.1V	DCR (Ω Max)	Insertion Loss (dB Max)	Return Loss (dB Min)	HI-POT (Vrms)
LT4532B-351MGF T6	1CT:1CT	350	45	4.5	-1.0@1-100MHz -1.2@100-125MHz	-18@1-40MHz -17 + 10*Log(F/40) @40-100MHz	1500

MECHANICAL





SCHEMATICS



Unless otherwise specified all tolerances are:±0.25 in mm

TAPING AND PACKING



Quantity (pcs):
2400 PCS PER REEL
10REELS PER CARTON
24000 PCS PER CARTON