





1	2	3	4	5	6	7	8
REV.	DESCRIPTION	APPD.	DATE				
A	INITIAL RELEASED	Chen	05/20/2025				



TYPICAL SPECIFICATIONS

1.0.ELECTRICAL

1.1.FREQUENCY RANGE: DC-6GHZ

1.2.NOMINAL IMPEDANCE: 50 Ohm

1.3.WORKING VOLTAGE:335V MAX.

1.4.PROOF VOLTAGE:750V

1.5.VSWR:1.5MAX.

1.6.INSULATION RESISTANCE: 1000 Mohm

1.7.CONTACT RESISTANCE: CENTER CONTACT:5 mohm

1.8.OUTER CONTACT: ≤2.5 mohm

2.0.ENVIRONMENTAL

2.1.OPERATING TEMPERATURE RANGE: -55°C TO +125°C

2.2.SALT SPRAY:48HOURS

2.3.ROHS COMPLIANT

ITEM	DRAWING NO.	PART NAME	DESCRIPTION	QTY
⑤	SMA065135G-3382	BODY	GOLD-PLATED BRASS (GOLDEN)	1PCS
④	SMA4180725-1752	INSULATOR	PTFE (WHITE)	1PCS
③	SMA4180725-1751	INSULATOR	PTFE (WHITE)	1PCS
②	SMA0714124G-3382	CENTER PIN	GOLD-PLATED BRASS (GOLDEN)	1PCS
①	SMA065135G-3386	BODY	GOLD-PLATED BRASS (GOLDEN)	1PCS

DIMENSIONS ARE IN MILLIMETERS	CUS P/N:	A-SMA-KWE-15.1A
UNLESS OTHERWISE SPECIFIED	PART NO.:	M04-0105130R0A
TOLERANCES	APPD:	DWG NO.:
ANGLES = ±3°	CHKD:	SCALE
UP TO 6 = ±0.1	DR:	SHEET
6-40 = ±0.2		REV.
40-120 = ±0.6		1/1
120-315 = ±1.0		V01
ABOVE 315 = ±1.6		

MyAntenna

TITLE: SMA JCAK S/T FOR PCB