



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PA66 BLACK

b.CONTACT:SUS304 T=0.4MM

(SURFACE PLATING: Ni-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: -10°C~ +80°C

ORDERING INFORMATION

BH-18650-A1BJ034

电池盒

电池型号

DIP 90° TYPE

PLATING:

A-Au-PLATING

J-Ni-PLATING

K-Sn-PLATING





MATERIAL:

1B-PA66 BLACK


工程部

2025-04-24

H. WANG



SECTION VIEW A-A



PCB Layout Diagram

TOP View

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyoungdz.com					
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2025-04-24	TITLE:	
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2025-04-24	电池盒BH-18650-2J Ni DIP PA66并联	
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2025-04-24	PART NO.:	
X.XX :±0.20		SCALE: 1:1		SIZE: A4		BH-18650-A1BJ034	
X.XXX :±0.10		UNIT: mm		REV.: A/0		DRAW NO.:WD-CP-0473	
WEIGHT:		VIEW: ① ②		OBJECT: MY			
SHEET 1 OF 1							

2	TERMINAL	6	SUS304, T=0.4MM	Ni-Plating
1	HOUSING	1	PA66	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR