

Description


MPT015N10, the N-channel Enhanced Power MOSFETs, is obtained by advanced double trench technology which reduce the conduction loss, improve switching performance and enhance the avalanche energy. This is suitable device for BMS and high current switching applications.

KEY CHARACTERISTICS

- ① $V_{DS}=100V$, $R_{ds(on)}<1.35m\Omega$ @ $V_{GS}=10V$, $I_D=399A$ (Typ:1.12m Ω)
- ② Fast Switching
- ③ On-Resistance
- ④ Low Gate Charge
- ⑤ Low Reverse transfer capacitances
- ⑥ High avalanche ruggedness
- ⑦ RoHS product

APPLICATIONS

- ① BMS
- ② High current switching applications



ORDERING INFORMATION

Ordering Codes	Package	Product Code	Packing
MPT015N10-T	TOLL8	MPT015N10	Reel

ABSOLUTE RATINGS (at $T_c=25^\circ C$, unless otherwise specified)

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	100	V
I_D	Continuous Drain Current, Silicon Limited	399	A
	Continuous Drain Current, Package Limited	480	A
	Continuous Drain Current @ $T_c=100^\circ C$, Silicon Limited	276	A
I_{DM} Note1	Pulsed Drain Current	1560	A
V_{GS}	Gate-Source Voltage	± 20	V
E_{AS} Note2	Avalanche Energy	1890	mJ
P_D	Power Dissipation	432	W
	Derating Factor above $25^\circ C$	4.33	W/ $^\circ C$
T_J , T_{stg}	Operating Junction and Storage Temperature Range	150, -55 to 150	$^\circ C$
T_L	Maximum Temperature for Soldering	260	$^\circ C$

Note1: Repetitive Rating: Pulse width limited by maximum junction temperature Note2: $L=0.5mH$, $I_{AS}=70A$, Start $T_J=25^\circ C$

Thermal characteristics

Symbol	Parameter	Max	Units
$R_{\theta JC}$	thermal resistance, Junction-Case	0.3	$^{\circ}\text{C}/\text{W}$
$R_{\theta JA}$	thermal resistance, Junction-Ambient	58	$^{\circ}\text{C}/\text{W}$

Electrical Characteristics (at $T_C=25^{\circ}\text{C}$, unless otherwise specified)

OFF Characteristics						
Symbol	Parameter	Test Conditions	Values			Units
			Min	Typ	Max	
V_{DS}	Drain-Source Breakdown Voltage	$V_{GS}=0\text{V}$, $I_D=250\mu\text{A}$	100	110	--	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=100\text{V}$, $V_{GS}=0\text{V}$	--	--	1	μA
		$V_{DS}=80\text{V}$, $V_{GS}=0\text{V}$ @ $T_C=125^{\circ}\text{C}$	--	--	100	μA
$I_{GSS(F)}$	Gate-Source Forward Leakage	$V_{GS}=+20\text{V}$	--	--	100	nA
$I_{GSS(R)}$	Gate-Source Reverse Leakage	$V_{GS}=-20\text{V}$	--	--	-100	nA

ON Characteristics						
Symbol	Parameter	Test Conditions	Values			Unit s
			Min	Typ	Max	
$R_{DS(on)}$	Drain-Source On-Resistance	$V_{GS}=10\text{V}$, $I_D=50\text{A}$	--	1.12	1.35	m Ω
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}$, $I_D=250\mu\text{A}$	2	3	4	V
Pulse width $t_p \leq 300\mu\text{s}$, $\delta \leq 2\%$						

Dynamic Characteristics						
Symbol	Parameter	Test Conditions	Values			Units
			Min	Typ	Max	
C_{iss}	Input Capacitance	$V_{DS}=50\text{V}$, $V_{GS}=0$, $f=1\text{MHz}$	--	11679	--	pF
C_{oss}	Output Capacitance		--	2684	--	
C_{rss}	Reverse Transfer Capacitance		--	105	--	
Q_g	Total Gate Charge	$V_{DD}=50\text{V}$, $I_D=100\text{A}$, $V_{GS}=10\text{V}$	--	203	--	nC
Q_{gs}	Gate-Source charge		--	67	--	
Q_{gd}	Gate-Drain charge		--	30	--	
R_G	Gate resistance	$V_{GS}=0$, $V_{DS}=0$		3.6		Ω



迈诺斯科技

MPT015N10

Switching Characteristics

Symbol	Parameter	Test Conditions	Values			Units
			Min	Typ	Max	
$t_{d(on)}$	Turn-On Delay Time	$V_{DD}=50V$, $I_D=10A$, $V_{GS}=10V$, $R_G=3\Omega$, Resistive Load	--	34	--	ns
t_r	Rise Time		--	26	--	
$t_{d(off)}$	Turn-Off Delay Time		--	78	--	
t_f	Fall Time		--	30	--	

Source-Drain Diode Characteristics

Symbol	Parameter	Test Conditions	Values			Units
			Min	Typ	Max	
I_S	Continuous Source Current		--	--	399	A
I_{SM}	Maximum Pulsed Current		--	--	1560	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=50A$	--	--	1.2	V
T_{rr}	Reverse Recovery Time	$I_S=100A$, $V_{GS}=0$, $di/dt=100A/us$	--	100	--	ns
Q_{rr}	Reverse Recovery Charge		--	280	--	nC

Characteristics Curves

Figure 1. Safe Operating Area




Figure 2. Maximum Power Dissipation vs Case Temperature




Figure 3. Maximum Continuous Drain Current vs Case Temperature




Figure 4. Typical Output Characteristics




Figure 5. Transient Thermal Impedance




Figure 6. Typical Transfer Characteristics




Figure 7. Source-Drain Diode Forward Characteristics




Figure 8. Drain-Source On-Resistance vs Drain Current




Figure 9. Normalized On-Resistance vs Junction Temperature




Figure 10. Normalized Threshold Voltage vs Junction Temperature




Figure 11. Normalized Breakdown Voltage vs Junction Temperature




Figure 12. Capacitance Characteristics





Figure 13. Typical Gate Charge vs Gate-Source Voltage



Test Circuit and Waveform

Figure 14. Resistive Switching Test Circuit




Figure 15. Resistive Switching Waveforms




Figure 16. Gate Charge Test Circuit




Figure 17. Gate Charge Waveforms




Figure 18. Diode Reverse Recovery Test Circuit




Figure 19. Diode Reverse Recovery Waveform




Figure 20. Unclamped Inductive Switching Test Circuit






Figure 21. Unclamped Inductive Switching Waveform



Package Description



SYMBOL	MIN	NOM	MAX
A	2.20	2.30	2.40
b	0.70	0.80	0.90
b1	9.70	9.80	9.90
C	0.40	0.50	0.60
D	10.28	10.43	10.58
D1	3.15	3.30	3.45
E	9.70	9.90	10.10
E1	7.35	7.50	7.65
E2	8.35	8.50	8.65
E3	9.31	9.46	9.61
e	1.10	1.20	1.30
H	11.48	11.73	11.88
H1	6.55	6.65	6.75
H2	7.20	7.35	7.50
H3	3.44	3.59	3.74
H4	3.11	3.26	3.41
K	4.03	4.18	4.33
L	1.60	1.85	2.10
L1	0.55	0.70	0.85
L2	0.45	0.60	0.75
L3	1.00	1.15	1.30

TOLL-8 Package



迈诺斯科技

MPT015N10

NOTE:

Exceeding the maximum ratings of the device in performance may cause damage to the device, even the permanent failure, which may affect the dependability of the machine. Please do not exceed the absolute maximum ratings of the device when circuit designing.

1. When installing the heat sink, please pay attention to the torsional moment and the smoothness of the heat sink.
2. MOSFETs is the device which is sensitive to the static electricity, it is necessary to protect the device from being damaged by the static electricity when using it.
3. Shenzhen Minos reserves the right to make changes in this specification sheet and is subject to change without prior notice.

CONTACT:

深圳市迈诺斯科技有限公司（总部）

地址：深圳市福田区华富街道田面社区深南中路4026号田面城市大厦22B-22C

邮编：518025

电话：0755-83273777