

Features

- Low on resistance
- Low gate charge
- Fast switching
- High avalanche current
- Low reverse transfer capacitances

Application


- Brushed and BLDC Motor drive systems
- Battery Management
- DC/DC and AC/DC Converter
- UPS

Product Summary


V_{DS}	68V
$R_{DS(on)}$ typ.	5.5mΩ
I_D	100A

100% DVDS Tested

100% Avalanche Tested



SFP066N68BI2



Package Marking and Ordering Information

Part #	Marking	Package	Packing	Reel Size	Tape Width	Qty
SFP066N68BI2	066N68BI2	TO-220	Tube	N/A	N/A	50pcs

Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Drain - Source Voltage	V_{DS}	68	V
Gate - Source Voltage	V_{GS}	±20	V
Continuous Drain Current	I_D	$T_C = 25^{\circ}C$ 100	A
		$T_C = 100^{\circ}C$ 70	
Pulsed Drain Current($T_C=25^{\circ}C, t_p$ limited by T_{Jmax})	$I_{D,Pulse}$	400	A
Single Pulsed Avalanche Energy($L=0.5mH, I_{AS}=30A, R_G=15\Omega, T_J=25^{\circ}C$)	E_{AS}	527	mJ
Power Dissipation	P_{tot}	$T_C = 25^{\circ}C$ 115	W
Junction Temperature	T_J	-55 ~ 150	°C
Storage Temperature	T_{STG}	-55 ~ 150	°C

Thermal Resistance

Parameter	Symbol	Max	Unit
Thermal resistance , junction – case	R_{thJC}	1.08	°C/W
Thermal resistance , junction – ambient(min. footprint)	R_{thJA}	62.5	°C/W

Electrical Characteristics ($T_J = 25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	Test Condition	Min	Type	Max	Unit
-----------	--------	----------------	-----	------	-----	------

Static Characteristics

Drain - Source Breakdown Voltage	BV_{DSS}	$V_{GS} = 0V, I_D = 250\mu A$	68	-	-	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 68V, V_{GS} = 0V$ $T_C = 25^{\circ}\text{C}$ $T_C = 100^{\circ}\text{C}$	- - -	- - -	1 100	μA
Gate - Body Leakage Current	I_{GSS}	$V_{GS} = \pm 20V, V_{DS} = 0V$	-	-	± 100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250\mu A$	2	3	4	V
Drain-source On-resistance	$R_{DS(on)}$	$V_{GS} = 10V, I_D = 60A$	-	5.5	6.6	mΩ

Dynamic Characteristics

Input Capacitance	C_{iss}	$V_{DS} = 35V, V_{GS} = 0V, f = 1\text{MHz}$	-	3426	-	pF
Output Capacitance	C_{oss}		-	318	-	
Reverse Transfer Capacitance	C_{rss}		-	226	-	
Gate Resistance	R_g	$V_{DS} = 0V, V_{GS} = 0V, f = 1\text{MHz}$	-	1.5	-	Ω







Switching Characteristics

Total Gate Charge	Q_g	$V_{DS} = 35V, V_{GS} = 10V, I_D = 40A$	-	69	-	nC
Gate-source Charge	Q_{gs}		-	19	-	
Gate-drain Charge	Q_{gd}		-	22	-	
Turn-on Delay Time	$t_{d(on)}$	$V_{DD} = 35V, V_{GS} = 10V, I_D = 40A,$ $R_G = 6\Omega$	-	65	-	ns
Turn-on Rise Time	t_r		-	35	-	
Turn-off Delay Time	$t_{d(off)}$		-	87	-	
Turn-off Fall Time	t_f		-	28	-	






Body Diode Characteristic

Parameter	Symbol	Test Condition	Min	Type	Max	Unit
Diode continuous forward current	I_S	-	-	-	100	A
Diode pulse current	$I_{S,pulse}$	Pulsed, $t_p \leq 10\mu s$	-	-	400	A
Body Diode Forward Voltage	V_{SD}	$V_{GS} = 0V, I_{SD} = 40A$	-	-	1.4	V
Body Diode Reverse Recovery Time	T_{rr}	$I_F = 60A, di/dt = 100A/\mu s$	-	32	-	ns
Body Diode Reverse Recovery Charge	Q_{rr}	$I_F = 60A, di/dt = 100A/\mu s$	-	35	-	nC

Typical Performance Characteristics



Fig1. Output Characteristics

Fig2. Transfer Characteristics

Fig3. Body-diode Forward Characteristics

Fig 4. Rds(on) vs Gate Voltage

Fig5. Rds(on) vs. Temperature

Fig6. Capacitance Characteristics


Typical Performance Characteristics



Fig7. Gate Charge Characteristics

Fig8. Safe Operating Area

Fig9. Power De-rating

Fig10. Current De-rating

Fig11. Max. Transient Thermal Impedance


Test Circuit & Waveform



Gate Charge Test Circuit & Waveform





Resistive Switching Test Circuit & Waveforms




Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



Diode Recovery Test Circuit & Waveforms



Package Outline: TO-220-3L


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.30	4.80	0.169	0.189
A1	2.20	2.70	0.087	0.106
b	0.70	0.95	0.276	0.037
b1	1.10	1.50	0.043	0.059
c	0.40	0.65	0.016	0.026
c1	1.20	1.45	0.047	0.057
D	9.70	10.30	0.382	0.406
E	8.75	9.65	0.344	0.380
E1	12.50	13.10	0.492	0.516
e	2.540 Typ.		0.100 Typ.	
e1	4.98	5.18	0.196	0.204
F	2.60	3.00	0.102	0.118
H	7.00	8.40	0.276	0.331
h	0	0.3	0	0.012
L	12.75	13.90	0.502	0.547
L1	2.85	3.40	0.112	0.134
V	6.700Ref.		0.264Ref.	
Φ	3.50	3.80	0.138	0.150

Revision History

Revision	Date	Major Changes
1.0	2023-12-28	Release of formal version

Disclaimer

Unless otherwise specified in the datasheet, the product is designed and qualified as a standard commercial product and is not intended for use in applications that require extraordinary levels of quality and reliability, such as automotive, aviation/aerospace and life-support devices or systems.

Any and all semiconductor products have certain probability to fail or malfunction, which may result in personal injury, death or property damage. Customer are solely responsible for providing adequate safe measures when design their systems.

Scilicon Electric reserves the right to improve product design,function and reliability without notice.