





REV.	ECN NO OR DESCRIPTION	REVISED	DATE



适用线规: **AWG#28~#22**
额定电压: **250V AC/DC**
额定电流: **5A**
耐 压: **1000V AC/minute**
绝缘电阻: $\geq 1000M\Omega$
接触电阻: $\leq 0.015\Omega$

- 技术要求:
- 1) 材质: 见附表;
 - 2) 电镀: 见附表;
 - 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
 - 4) 端子表面无氧化、电镀无不良现象。

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS: X :±0.30 X.X :±0.20 X.XX :±0.10		ANGLES: X :±2° X.X :±1°		TITLE: MX 3.00双排带扣端子(母端)	
DWN	xiong	PART NO.	WAFER-MX300DZ		
CHKD	lee	SCALE:1:1	UNIT: mm	REV: A4	
APVD	wang	SIZE: A4	SHEET:10F 1	CUSTOMER COPY	