


Kinghelm®

| REVISIONS |        |             |       |     |      |
|-----------|--------|-------------|-------|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN   | CHK | DATE |
| A         |        | DESIGN      | James |     |      |
|           |        |             |       |     |      |



NOTES:

- ELECTRICAL:
  - VOLTAGE RATING:DCV 300V 10MS
  - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - INSULATION RESISTANCE: 5.0M OHM/MIN.
  - THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
- MATERIAL:
  - SEE TABLE
- ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION         | QTY. |
|----------|-------------|---------------------|------|
| ③        | 套管          | OD:2.5*1.5mm热缩套管,黑色 | 2    |
| ②        | 接头          | SSMA母头母针(内孔),直头镀金   | 2    |
| ①        | 同轴线         | RG1.37黑色线,OD1.3mm   | AS   |

深圳市金航标电子有限公司  
SHENZHEN KINGHELM ELECTRON CO.,LTD.

WWW.KINGHELM.COM.CN  
0755-28190160

|                                                                     |                                                                         |                   |                                      |              |
|---------------------------------------------------------------------|-------------------------------------------------------------------------|-------------------|--------------------------------------|--------------|
| ALL DIMENSION<br>ARE IN MM                                          | DRAWN<br>James                                                          | DATE<br>2025-3-26 | TITLE<br>KH-SSMAK-SSMAK-RG1.37-280MM |              |
|                                                                     | CHKD.<br>Frank                                                          | 2025-3-26         |                                      |              |
| COMPUTER GENERATED<br>IN SOLIDWORKS<br>DO NOT SCALE<br>THIS DRAWING | APPD.<br>Scott                                                          | 2025-3-26         |                                      |              |
| PROJECTION<br>                                                      | GENERAL TOLERANCE FOR<br>ANGLES X.X X.XX X.XXX<br>±1° ±0.3 ±0.25 ±0.150 |                   | SIZE DWG Number.<br>B                | REV<br>A     |
| CUSTOMER P/N:                                                       |                                                                         | SCALE:Free        | TYPE                                 | SHEET 1 OF 1 |