


Kinghelm®

| REVISIONS |        |             |       |     |      |
|-----------|--------|-------------|-------|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN   | CHK | DATE |
| A         |        | DESIGN      | James |     |      |
|           |        |             |       |     |      |



NOTES:

1. ELECTRICAL:

- 1.1. VOLTAGE RATING:DCV 300V 10MS
- 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
- 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
- 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
- 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.

2. MATERIAL:

- 2.1. SEE TABLE

3. ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION         | QTY. |
|----------|-------------|---------------------|------|
| ③        | 套管          | OD:2.5*1.5mm热缩套管 黑色 | 2    |
| ②        | 接头          | SSMA公头公针(内针),直头镀金   | 2    |
| ①        | 同轴线         | RG1.37黑色线,OD1.3mm   | AS   |

深圳市金航标电子有限公司  
SHENZHEN KINGHELM ELECTRON CO.,LTD.

WWW.KINGHELM.COM.CN  
0755-28190160

|                                                                     |                                                                         |                |                                      |       |
|---------------------------------------------------------------------|-------------------------------------------------------------------------|----------------|--------------------------------------|-------|
| ALL DIMENSION<br>ARE IN MM                                          | DRAWN James                                                             | DATE 2025-3-26 | TITLE<br>KH-SSMAJ-SSMAJ-RG1.37-200MM |       |
|                                                                     | CHKD. Frank                                                             | 2025-3-26      |                                      |       |
| COMPUTER GENERATED<br>IN SOLIDWORKS<br>DO NOT SCALE<br>THIS DRAWING | APPD. Scott                                                             | 2025-3-26      | SIZE DWG Number.                     |       |
|                                                                     |                                                                         |                |                                      |       |
| PROJECTION                                                          | GENERAL TOLERANCE FOR<br>ANGLES X.X X.XX X.XXX<br>±1° ±0.3 ±0.25 ±0.150 |                | B                                    | REV A |
| SCALE:Free                                                          |                                                                         | TYPE           | SHEET 1                              | OF 1  |

CUSTOMER P/N: