


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-21-004389	09APR2021	CD	CD

ABSOLUTE MAXIMUM RATINGS	SYMBOL	MIN	MAX	UNIT
STORAGE TEMPERATURE	T _{stg}	-40	105	°C
LINE TO NEUTRAL VOLTAGE	V _{in}	90	300	VAC
MAXIMUM AC CURRENT (RESISTIVE)	A _{switch}	--	8	AMPS

ELECTRICAL CHARACTERISTICS	
INPUT VOLTAGE RANGE	110/120, 230/240 AND 277 VAC NOMINAL SOURCES
INPUT FREQUENCY	47-63 Hz FOR 50/60 Hz NOMINAL SOURCES
MAXIMUM AC CURRENT	8 AMPS (RESISTIVE), 5 AMPS (ELECTRONIC BALLAST)@120V, 3AMPS @277V
DC POWER SUPPLIES	
DIMMING	24 VDC AT 50 mA MAXIMUM
COMMUNICATIONS	5 VDC AT 1000 mA MAXIMUM
AUXILIARY	3.3VDC AT 500 mA MAXIMUM
SURGE PROTECTION	ANSI C62.41 6 kV, 3 kA COMBINATION WAVE SURGE PROTECTION
POWER CONSUMPTION (MIN LOAD)	< 1W @ 120 VAC, < 2W @ 277 VAC
FAIL MODE	ON (NORMALLY CLOSED) OR OFF (NORMALLY OPEN)

ENVIRONMENTAL CHARACTERISTICS	
OPERATING TEMPERATURE	-40°C TO +85°C (SEE 114-133085 FOR DETAILS)
RELATIVE HUMIDITY	OPERATING: 15% TO 96%, NON-CONDENSING ENVIRONMENT.
ALTITUDE	OPERATING: -15m TO +2,000m NON-OPERATING: -15m TO +14,000m

- 1 MATERIALS:
HOUSING: PBT
DIMMING CONTACTS (QTY. 4): COPPER ALLOY
LINE VOLTAGE CONTACTS (QTY. 3): COPPER ALLOY
GASKET: VINYL/NITRILE FOAM
O-RING: SILICONE RUBBER
PCBA: FR4
- 2 FINISH:
DIMMING CONTACTS: NICKEL UNDERPLATE ENTIRE
CONTACT 0.127 µm MIN THICK. SELECTIVE GOLD PLATE CONTACT
MATING AREA (MATING FACE SIDE ONLY) 0.76 µm MIN THICK.
MATTE TIN PLATE TAB ON BOTH SIDES 0.30 µm MIN THICK.
LINE VOLTAGE CONTACTS: MATTE TIN PLATE
- 3 MATING INTERFACE PER ANSI C136.41-2013.
- 4 ADHESIVE BACKED GASKET SUPPLIED BUT NOT INSTALLED.
- 5 ADDITIONAL COVERS (P/N: 2306130-X) AVAILABLE
CONTACT TE CONNECTIVITY FOR MORE OPTIONS.
6. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
7. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
8. IN ADDITION TO THE STANDARD PRODUCT PART NUMBERS, OTHER
CONFIGURATIONS MAY BE AVAILABLE FOR SPECIAL ORDER.
PLEASE CONTACT A TE CONNECTIVITY SALES OFFICE FOR MORE INFO.
- 9 NOT PRODUCTION TOOLED



9	YES	50Hz	YES	YES	OFF	4-2314786-2
9	YES	50Hz	YES	YES	ON	4-2314786-1
9	YES	60Hz	YES	YES	OFF	3-2314786-2
9	YES	60Hz	YES	YES	ON	3-2314786-1
	NO	50Hz	YES	YES	OFF	1-2314786-2
	NO	50Hz	YES	YES	ON	1-2314786-1
	NO	60Hz	YES	YES	OFF	2314786-2
	NO	60Hz	YES	YES	ON	2314786-1
	VENT	FREQ.	ENERGY METERING HEADER	ZERO CROSS	FAIL MODE	PART NO.


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.DAILY 30DEC2016	TE Connectivity			
		CHK C.GINGRICH 30DEC2016				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, LUMAWISE ENDURANCE N ENHANCED BASE		
		0 PLC ±- 1 PLC ±0.35 2 PLC ±0.25 3 PLC ±- 4 PLC ±- ANGLES ±3° FINISH		SIZE A200779		
MATERIAL - 1		- 2		DRAWING NO C-2314786		
				RESTRICTED TO		
				SCALE 2:1 SHEET 1 OF 4 REV A1		
				CUSTOMER DRAWING		

1471-9 (3/13)

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

2.5 MAX
AT LOCATION P1


21.3 MAX
TO FIT UNDER TE COVER
PN: 2306130-X



RECOMMENDED CUSTOMER PCB
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 30DEC2016	TE Connectivity			
		CHK C. GINGRICH 30DEC2016				
DIMENSIONS:		APVD	NAME ASSEMBLY, LUMAWISE ENDURANCE N ENHANCED BASE			
mm		PRODUCT SPEC 108-133085	SIZE A200779			
		APPLICATION SPEC 114-133085	CAGE CODE C-2314786			
MATERIAL		WEIGHT	DRAWING NO			
		CUSTOMER DRAWING	RESTRICTED TO			
			SCALE 2:1 SHEET 3 OF 4 REV A1			

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



SECTION A-A

MATING COVER DIMENSIONS FOR
81MM DIAMETER BASES



(2306130-X REF)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 30DEC2016	 TE Connectivity							
		CHK C. GINGRICH 30DEC2016								
DIMENSIONS:		APVD	NAME							
mm		PRODUCT SPEC	ASSEMBLY, LUMAWISE ENDURANCE N ENHANCED BASE -							
		108-133085								
		APPLICATION SPEC	SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		114-133085	A2		00779		C-2314786			
MATERIAL		FINISH	WEIGHT							
-		-	-							
-		-	CUSTOMER DRAWING		SCALE		SHEET		REV	
					2:1		4 OF 4		A1	