






LOC		DIST		REVISIONS						
ES	00	P	LTR	DESCRIPTION				DATE	DWN	APVD
			E5	REV PWE ECR-12-021188				10DEC2012	ML	SZ



SECTION H-H




E3

.225	6.000	1.275	.250	6.350	.200	.375	6.050	NO	48S + 18P	6600323-9
.225	4.650	1.675	.250	5.000	.200	.375	4.700	NO	64S + 11P	6600323-8
.225	3.800	3.075	.250	4.150	.200	.375	3.850	YES	120S + 2P	6600323-7
.225	2.800	.200	.300	3.150	.200	.375	2.850	NO	4S + 8ACP	6600323-6
.225	3.800	1.075	.250	4.150	.200	.375	3.850	NO	40S + 10P	6600323-5
.225	1.500	-	-	1.850	.200	.375	1.550	NO	48S	6600323-4
.225	2.400	.675	.250	2.750	.200	.375	2.450	NO	24S + 6P	6600323-3
.225	2.900	.675	.250	3.250	.200	.375	2.950	NO	24S + 8P	6600323-2
.225	3.100	.875	.250	3.450	.200	.375	3.150	NO	32S + 8P	6600323-1
DIM TT	DIM U	DIM W	DIM T	DIM L	DIM K	DIM G	DIM D	RETENTION CLIP	DESCRIPTION	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN J. McCLINTON 15AUG05	TE Connectivity				
DIMENSIONS: INCH				CHK D. TROUT 15AUG05					
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD R. WHYNE 15AUG05	NAME VERTICAL HEADER ASSEMBLY, W/GUIDES, PRESS FIT, TYPE SP, MULTI-BEAM XL				
0 PLC ±.005				PRODUCT SPEC	SIZE CAGE CODE DRAWING NO				
1 PLC ±.005				APPLICATION SPEC	A100779C=6600323				
2 PLC ±.005				WEIGHT	RESTRICTED TO				
3 PLC ±.005				CUSTOMER DRAWING	SCALE 3:1 SHEET 1 OF 7 REV E5				
4 PLC ±.005									
ANGLES									
FINISH									

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-


PART NUMBER	ROWS		SIGNAL								POWER										
			1	2	3	4	5	6	7	8	P1	P2	P3	P4	P5	P6	P7	P8			
6600323-1	D		EV	EV	EV	EV	EV	EV	EV	EV	VM	VM	VM	VM	VM	VM	VM	VM			
	C		EV	EV	EV	EV	EV	EV	EV	EV										EV	
	B		EV	EV	EV	EV	EV	EV	EV	EV										EV	EV
	A		EV	EV	EV	EV	EV	EV	EV	EV										EV	EV
32S+8P																					




PART NUMBER	ROWS		SIGNAL						POWER									
			1	2	3	4	5	6	P1	P2	P3	P4	P5	P6	P7	P8		
6600323-2	D		EV	EV	EV	EV	EV	EV	VM	VM	VM	VM	VM	VM	VM	VM		
	C		EV	EV	EV	EV	EV	EV										
	B		EV	EV	EV	EV	EV	EV										EV
	A		EV	EV	EV	EV	EV	EV										EV
24S+8P																		




PART NUMBER	ROWS		SIGNAL												
			1	2	3	4	5	6	7	8	9	10	11	12	
6600323-4	D		EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	
	C		EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	
	B		EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	
	A		EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	
48S															




-	RETENTION CLIP	HD
MLBF	SIGNAL CONTACT	ES
STANDARD	SIGNAL CONTACT	EV
-	POWER CONTACT	VM
MATING SEQUENCE	DESCRIPTION	IDENTIFIER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. McCLINTON 15AUG05	 TE Connectivity		
DIMENSIONS:		CHK D. TROUT 15AUG05			
INCH		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME		
			VERTICAL HEADER ASSEMBLY, W/GUIDES, PRESS FIT, TYPE SP, MULTI-BEAM XL		
MATERIAL	FINISH	APVD R. WHYNE 15AUG05	SIZE		
			A100779C=6600323		
CUSTOMER DRAWING		WEIGHT	SCALE 3:1	SHEET 2 OF 7	
		RESTRICTED TO	REV E5		

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN	J. McCLENTON	15AUG05			
DIMENSIONS: 1 INCH 						CHK	D. TROUT	15AUG05	 TE Connectivity		
						APVD	R. WHYNE	15AUG05	NAME VERTICAL HEADER ASSEMBLY, W/GUIDES, PRESS FIT, TYPE SP, MULTI-BEAM XL		
TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P/LC ±. 1 P/LC ±. 2 P/LC ±. 3 P/LC ±0.005 4 P/LC ±0.0005 ANGLES ±. FINISH -						PRODUCT SPEC		SIZE CASE CODE DRAWING NO A 1 00779 C-6600323			
						APPLICATION SPEC					
MATERIAL	-	WEIGHT				-		RESTRICTED TO			
CUSTOMER DRAWING						SCALE	3:1	SHEET	3	OF	7 REV E5

PART NUMBER	ROWS		SIGNAL						POWER						
			1	2	3	4	5	6	P1	P2	P3	P4	P5	P6	
6600323-3	D		EV	EV	EV	EV	EV	EV	VM	VM	VM	VM	VM	VM	
	C		EV	EV	EV	EV	EV	EV							
	B		EV	EV	EV	EV	EV	EV							
	A		EV	EV	EV	EV	EV	EV							
24S+6P															

4805 (3/11)

Technical drawing of a rectangular plate with a grid of holes. The drawing includes dimensions and callouts:

- Overall width: 4.180 MIN
- Overall height: .600 MIN
- Central grid of holes: 20x10
- Hole diameters: $\varnothing .040 \pm .003$ (5), $\varnothing .098 \pm .002$ (5)
- Position dimensions: 3.850, 3.250, .225, .100 TYP, .250
- Surface finish: 4, 5, 7
- Material: BSC, -V-, -U-

4805 (3/11)

E

4805 (3/11)

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
ES	00	-	SEE SHEET 1	-	-	-	

PART NUMBER	ROWS		SIGNAL												POWER																		
			1	2	3	4	5	6	7	8	9	10	11	12	P1	P2	P3	P4	P5	P6	P7	P8	P9	P10	P11	P12	P13	P14	P15	P16		P17	P18
6600323-9	D		EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	VM	VM	VM	VM	VM	VM	VM	VM	VM	VM	VM	VM	VM	VM	VM	VM	VM		
	C		EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV																		EV	
	B		EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV																		EV	EV
	A		EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV	EV																		EV	EV
48S + 18P																																	

