






PCB 仅供参考

Note:

1. Material:

- 1.1 Housing: High temperature thermoplastic with g.f, UL94v-0
- 1.2 Contact: copper alloy, t=0.20mm
- 1.3 Shell: copper alloy, t=0.25mm

2. Specification:

- 2.1 Current rating: 1 A Max
- 2.2 Dielectric withstanding voltage: 100V(ac) for 1 Min
- 2.3 Contact resistance: 50mΩ Max
- 2.4 Insulation resistance: 100MΩ Min
- 2.5 Total mating force: 3.57kgf Max
- 2.6 Total unmating force: 1.0kgf Min. 0.81~2.05 kgf Min
- 2.7 Temperature range: -30℃~80℃

GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE:	NUMBER:	深圳市连欣科技有限公司	
	MM	1:1			
.X	±0.08	MATERIAL:	HRC:	NAME:	
.XX	±0.05	DRAWN BY	DATE	Mirco 5P 180° 平口	
.XXX	±0.03	ERIC	08.03.27		
ANGULAR ±2°		CHECKED BY	DATE	THIRD ANGLE PROJECTION	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		2016.09.01			
		APPROVED BY	DATE	PART NO.	REVISION
				XUDF-0418-016	1/1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO CYBERAPEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					