


## Description:

This N-Channel MOSFET uses advanced SGT technology and design to provide excellent  $R_{DS(on)}$  with low gate charge.

It can be used in a wide variety of applications.

## Features:

- 1)  $V_{DS}=60V, I_D=68A, R_{DS(on)} < 10m\Omega$  @  $V_{GS}=10V$ , Typ:  $7.5m\Omega$
- 2) Low gate charge.
- 3) Green device available.
- 4) Advanced high cell density trench technology for ultra  $R_{DS(on)}$ .
- 5) Excellent package for good heat dissipation.



## Absolute Maximum Ratings: ( $T_C=25^\circ C$ unless otherwise noted)

| Symbol         | Parameter                                        | Ratings     | Units      |
|----------------|--------------------------------------------------|-------------|------------|
| $V_{DS}$       | Drain-Source Voltage                             | 60          | V          |
| $V_{GS}$       | Gate-Source Voltage                              | $\pm 20$    | V          |
| $I_D$          | Continuous Drain Current- $T_C=25^\circ C^1$     | 68          | A          |
|                | Continuous Drain Current- $T_C=100^\circ C$      | ---         |            |
|                | Pulsed Drain Current <sup>2</sup>                | 204         |            |
| $E_{AS}$       | Single Pulse Avalanche Energy <sup>4</sup>       | 91          | mJ         |
| $P_D$          | Power Dissipation, $T_C=25^\circ C$              | 81          | W          |
| $T_J, T_{STG}$ | Operating and Storage Junction Temperature Range | -55 to +150 | $^\circ C$ |

## Thermal Characteristics:

| Symbol          | Parameter                                            | Max  | Units        |
|-----------------|------------------------------------------------------|------|--------------|
| $R_{\theta JC}$ | Thermal Resistance, Junction to Case                 | 1.54 | $^\circ C/W$ |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient <sup>5</sup> | 62   |              |

**Package Marking and Ordering Information:**

| Part NO.      | Marking | Package |
|---------------|---------|---------|
| IPD053N06N-DO | 053N06N | TO-252  |

**Electrical Characteristics:** ( $T_C=25^{\circ}\text{C}$  unless otherwise noted)

| Symbol                             | Parameter                          | Conditions                                                                              | Min | Typ   | Max   | Units |
|------------------------------------|------------------------------------|-----------------------------------------------------------------------------------------|-----|-------|-------|-------|
| Off Characteristics                |                                    |                                                                                         |     |       |       |       |
| BV <sub>DSS</sub>                  | Drain-Sourctce Breakdown Voltage   | V <sub>GS</sub> =0V,I <sub>D</sub> =250 μ A                                             | 60  | ---   | ---   | V     |
| I <sub>DSS</sub>                   | Zero Gate Voltage Drain Current    | V <sub>GS</sub> =0V, V <sub>DS</sub> =60V                                               | --- | ---   | 1     | μ A   |
| I <sub>GSS</sub>                   | Gate-Source Leakage Current        | V <sub>GS</sub> =± 20V, V <sub>DS</sub> =0A                                             | --- | ---   | ± 100 | nA    |
| On Characteristics                 |                                    |                                                                                         |     |       |       |       |
| V <sub>GS(th)</sub>                | GATE-Source Threshold Voltage      | V <sub>GS</sub> =V <sub>DS</sub> , I <sub>D</sub> =250 μ A                              | 1   | ---   | 2.5   | V     |
| R <sub>DS(ON)</sub>                | Drain-Source On Resistance         | V <sub>GS</sub> =10V,I <sub>D</sub> =20A                                                | --- | 7.5   | 10    | m Ω   |
|                                    |                                    | V <sub>GS</sub> =4.5V,I <sub>D</sub> =10A                                               | --- | 10    | 13    |       |
| Dynamic Characteristics            |                                    |                                                                                         |     |       |       |       |
| C <sub>iss</sub>                   | Input Capacitance                  | V <sub>DS</sub> =50V, V <sub>GS</sub> =0V, f=1MHz                                       | --- | 1204  | ---   | pF    |
| C <sub>Oss</sub>                   | Output Capacitance                 |                                                                                         | --- | 194.1 | ---   |       |
| C <sub>rss</sub>                   | Reverse Transfer Capacitance       |                                                                                         | --- | 9.9   | ---   |       |
| Switching Characteristics          |                                    |                                                                                         |     |       |       |       |
| t <sub>d(on)</sub>                 | Turn-On Delay Time                 | V <sub>DD</sub> =50V, I <sub>D</sub> =25A,<br>V <sub>GS</sub> =10V,R <sub>GEN</sub> =3Ω | --- | 23.9  | ---   | ns    |
| t <sub>r</sub>                     | Rise Time                          |                                                                                         | --- | 4.6   | ---   | ns    |
| t <sub>d(off)</sub>                | Turn-Off Delay Time                |                                                                                         | --- | 37.8  | ---   | ns    |
| t <sub>f</sub>                     | Fall Time                          |                                                                                         | --- | 6.4   | ---   | ns    |
| Q <sub>g</sub>                     | Total Gate Charge                  | V <sub>GS</sub> =10V, V <sub>DS</sub> =50V,<br>I <sub>D</sub> =25A                      | --- | 17.9  | ---   | nC    |
| Q <sub>gs</sub>                    | Gate-Source Charge                 |                                                                                         | --- | 3.8   | ---   | nC    |
| Q <sub>gd</sub>                    | Gate-Drain “Miller” Charge         |                                                                                         | --- | 4.2   | ---   | nC    |
| Drain-Source Diode Characteristics |                                    |                                                                                         |     |       |       |       |
| V <sub>SD</sub>                    | Source-Drain Diode Forward Voltage | V <sub>GS</sub> =0V,I <sub>S</sub> =20A                                                 | --- | ---   | 1.3   | V     |
| L <sub>s</sub>                     | Continuous Source Current          | V <sub>GS</sub> <V <sub>th</sub>                                                        |     | ---   | 68    | A     |

|            |                         |                                                        |      |     |    |
|------------|-------------------------|--------------------------------------------------------|------|-----|----|
| <b>trr</b> | Reverse Recovery Time   | $I_S=25\text{ A,}$<br>$di/dt=100\text{ A}/\mu\text{s}$ | 36.3 | --- | Ns |
| <b>qrr</b> | Reverse Recovery Charge |                                                        | 1.4  | --- | nc |

## Notes:

- 1) Calculated continuous current based on maximum allowable junction temperature.
- 2) Repetitive rating; pulse width limited by max. junction temperature.
- 3)  $P_d$  is based on max. junction temperature, using junction-case thermal resistance.
- 4)  $V_{DD}=30\text{ V}$ ,  $R_G=50\ \Omega$ ,  $L=0.3\text{ mH}$ , starting  $T_J=25\text{ }^\circ\text{C}$ .
- 5) The value of  $R_{\theta JA}$  is measured with the device mounted on 1 in 2 FR-4 board with 2oz. Copper, in a still air environment with  $T_a=25\text{ }^\circ\text{C}$ .

## Typical Characteristics: ( $T_C=25^\circ\text{C}$ unless otherwise noted)




Figure 1, Typ. output characteristics




Figure 2, Typ. transfer characteristics




Figure 3, Typ. capacitances




Figure 4, Typ. gate charge




Figure 5, Drain-source breakdown voltage




Figure 6, Drain-source on-state resistance




Figure 7, Threshold voltage




Figure 8, Forward characteristic of body diode




Figure 9, Drain-source on-state resistance




Figure 10, Drain current




Figure 11, Safe operation area  $T_C = 25^\circ\text{C}$




Figure 12, Max. transient thermal impedance