



8952




8952-0-05-XX-00-00-03-0
Square press-fit in .087 plated thru hole

8953




8953-0-05-XX-00-00-03-0
Square press-fit in .047 plated thru hole

7310




7310-0-01-XX-00-00-08-0
Board edge press-fit

8816




8816-0-00-XX-00-00-03-0
Press-fit in .057 mounting hole

8940




8940-0-00-XX-00-00-03-0
Press-fit in .057 mounting hole

8876



8876-0-00-XX-00-00-03-0
Press-fit in .057 mounting hole

3120



3120-X-00-XX-00-00-08-0
Swage mount in .034 mounting hole

Basic Part Number	Length A
3120-1	.205
3120-2	.250

SPECIFICATIONS

PIN MATERIAL:
Brass Alloy 360, 1/2 Hard
(Except Swage pins which are annealed)

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: $\pm .005$
DIAMETERS: $\pm .002$
ANGLES: $\pm 2^\circ$

ORDER CODE: XXXX - X - XX - XX - 00 - 00 - 0X - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- 80 200 μ " TIN OVER NICKEL $\diamond$
- 15 10 μ " GOLD OVER NICKEL $\diamond$
- 21 20 μ " GOLD OVER NICKEL $\diamond$
- 34 50 μ " GOLD OVER NICKEL $\diamond$

