




CHIP COMMON MODE CHOKE


High Common Mode Impedance at High Frequency.
Excellent Noise Suppression Performance.
Small Size and Low Profile, Surface Mount Type.
Operating Temperature Range: -40 °C to +125 °C.
RoHS Compliant.
AEC-Q200 Compliant.

Part Number	Electrical Specifications @25°C					
	Common mode Impedance (Ω@10MHz)	Common mode Impedance (uH +50%/-30%)	DCR (Ω Max)	Rated Current mA Max	Rated Volt (Vdc Max)	IR M(Ω Min)
CM4532S-201-A T	6000Min 12000Typ.	200	4.5	70	50	10

MECHANICAL





SCHEMATICS



Unless otherwise specified all tolerances are: ±0.25 in mm

TAPING AND PACKING



Quantity (pcs):
2000 PCS PER REEL
10 REELS PER CARTON
20000 PCS PER CARTON