


FEATURES

Lead Free Product is Acquired
Surface Mount Package
N-Channel Switch with Low $R_{DS(on)}$
Operated at Low Logic Level Gate Drive

APPLICATION

Load/Power Switching
Interfacing Switching
Battery Management for Ultra Small Portable Electronics
Logic Level Shift


MARKING : KF



SOT-723

$V_{(BR)DSS}$	$R_{DS(on)MAX}$	I_D
20 V	380mΩ@ 4.5V	0.75A
	450mΩ@ 2.5V	
	800mΩ@ 1.8V	

SOT-723 Package Outline Dimensions



Symbol	Dimensions in Millimeters		Dimensions in Inches	
	Min.	Max.	Min.	Max.
A	0.430	0.500	0.017	0.020
A1	0.000	0.050	0.000	0.002
b	0.170	0.270	0.007	0.011
b1	0.270	0.370	0.011	0.015
c	0.080	0.150	0.003	0.006
D	1.150	1.250	0.045	0.049
E	1.150	1.250	0.045	0.049
E1	0.750	0.850	0.030	0.033
e	0.800TYP.		0.031TYP.	
θ	7° REF.		7° REF.	

Maximum ratings ($T_a=25^{\circ}C$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	20	V
Typical Gate-Source Voltage	V_{GS}	±12	V
Continuous Drain Current (note 1)	I_D	0.75	A
Pulsed Drain Current ($t_p=10 \mu s$)	I_{DM}	1.8	A
Power Dissipation (note 1)	P_D	150	mW
Thermal Resistance from Junction to Ambient (note 1)	$R_{\theta JA}$	833	$^{\circ}C/W$
Operation Junction and Storage Temperature Range	T_J, T_{STG}	-55~+150	$^{\circ}C$
Lead Temperature for Soldering Purposes(1/8" from case for 10 s)	T_L	260	$^{\circ}C$

3134K

MOSFET ELECTRICAL CHARACTERISTICS

$T_a = 25^\circ\text{C}$ unless otherwise specified


Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
STATIC CHARACTERISTICS						
Drain-source breakdown voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D =250μA	20			V
Zero gate voltage drain current	I _{DSS}	V _{DS} =20V,V _{GS} = 0V			1	μA
Gate-body leakage current	I _{GSS}	V _{GS} =±10V, V _{DS} = 0V			±20	μA
Gate threshold voltage (note 2)	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250μA	0.35	0.54	1.1	V
Drain-source on-resistance (note 2)	R _{DS(on)}	V _{GS} =4.5V, I _D =0.65A		270	380	mΩ
		V _{GS} =2.5V, I _D =0.55A		320	450	mΩ
		V _{GS} =1.8V, I _D =0.45A		390	800	mΩ
Forward transconductance (note 2)	g _{FS}	V _{DS} =10V, I _D =0.8A		1.6		S
Diode forward voltage	V _{SD}	I _S =0.15A, V _{GS} = 0V			1.2	V
DYNAMIC CHARACTERISTICS (note 4)						
Input capacitance	C _{iss}	V _{DS} =16V,V _{GS} =0V,f =1MHz		79	120	pF
Output capacitance	C _{oss}			13	20	pF
Reverse transfer capacitance	C _{rss}			9	15	pF
SWITCHING CHARACTERISTICS (note 4)						
Turn-on delay time (note 3)	t _{d(on)}	V _{GS} =4.5V,V _{DS} =10V, I _D =500mA,R _{GEN} =10Ω		6.7		ns
Turn-on rise time (note 3)	t _r			4.8		ns
Turn-off delay time (note3)	t _{d(off)}			17.3		ns
Turn-off fall time (note 3)	t _f			7.4		ns
Total Gate Charge (note 3)	Q _g	V _{DS} =10V,V _{GS} =4.5V,I _D =0.25A		750		pC
Gate-Source Charge (note 3)	Q _{gs}			75		pC
Gate-Drain Charge (note 3)	Q _{gd}			225		pC

Notes :





1. Surface mounted on FR4 board using the minimum recommended pad size.
2. Pulse Test : Pulse Width=300 μs , Duty Cycle=2%.
3. Switching characteristics are independent of operating junction temperatures.
4. Guaranteed by design, not subject to producing.

RATING AND CHARACTERISTIC CURVES (3134K)

Output Characteristics



Transfer Characteristics



Threshold Voltage

