


	F	REVISED (REDRAW)	16APR2013	T.N	N.Y
	G	REVISED PER ECR-17-004338	18APR17	C.L	N.Y



1. TO PREVENT THREAD STRIPPING, SCREW TORQUE SHOULD NOT EXCEED 12kg-cm Max
2. SIMILAR P/N 202643-3

7-3	7-2	7-1	-3	-2	-1	TABLE 1				
PART NO.										
I	-	-	-	-	-	1.8	7.2	BRASS, Ni PLATED	JACK-SCREW BODY	③
-	I	-	-	-	-	2.6	26.0	BRASS, Ni PLATED	JACK-SCREW BODY	③
-	-	I	-	-	-	3.65	7.2	BRASS, Ni PLATED	JACK-SCREW BODY	③
-	-	-	I	-	-	1.8	7.2	BRASS, TIN PLATED	JACK-SCREW BODY	③
-	-	-	-	I	-	2.6	26.0	BRASS, TIN PLATED	JACK-SCREW BODY	③
-	-	-	-	-	I	3.65	7.2	BRASS, TIN PLATED	JACK-SCREW BODY	③
I	I	I	I	I	I	-	-	STAINLESS STEEL ORGANIC COATING	JACK-SCREW PIN	②
I	I	I	I	I	I	-	-	STAINLESS STEEL ORGANIC COATING	JACK-SCREW TIP	①
QTY						"A"	"B"	MATERIAL&FINISH	NAME	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±°
1 PLC ±°
2 PLC ±° ±0.4
3 PLC ±°
4 PLC ±°
ANGLES ±1°

FINISH -

APVD
N. YAMASAKI

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

Customer Drawing

DWN
T. NAGASAKI

CHK
S. YAMADA

APVD
N. YAMASAKI

16APR2013

16APR2013

16APR2013

TE Connectivity

NAME
JACK-SCREW MALE
EXTRA-LONG
M SERIES

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-170994

RESTRICTED TO
-

SCALE
2:1

SHEET
1

OF
1

REV
G