



### Description

MAX485EESA+T is 3V to 5.5V power supply,  $\pm 15\text{kV}$  anti-static slow limit differential transceiver and can provide complete RS485 compatibility for half-duplex applications. Each section contains a driver and a receiver designed for data transmission over an extended common-mode range (-7V to +12V). It can effectively transmit data at a high rate of up to 10Mbps.

Drivers are short-circuit current limited and are protected against excessive power dissipation by thermal shutdown circuitry that places the driver outputs into a high-impedance state. The Rx input has a fail-safe feature that guarantees a logic-high output if the input is open circuit, short-circuit and shutdown but not drive.

Both components have power-on/off modes, and fault-free driver outputs allow transceivers to be inserted or removed from bus in real time. CMOS designs aim to offer significant power savings without sacrificing overload or ESD damage. Typically, static current is only 300uA in operation and 1uA in shutdown mode.

### Feature

- High communication rate, 3.0V ~ 5.5V power supply 10Mbps
- High ESD protection
- Low power consumption down to 1uA, shutdown mode
- Input voltage range: -7V to +12V (common mode)
- Bus connection up to 256 nodes
- Thermal shutdown protection function
- Drive overload protection function
- Full fault-safe (open circuit, short circuit, etc.)

### Product Application


- Power communication
- Integrated digital network
- Industrial control local area network
- Power measurement (smart meter)
- Factory automation and control

### Ordering Information

Product Model	Package Type	Marking	Packing	Packing Qty
MAX485EESA+T	SOP-8	X485E	Tape	2500Pcs/Reel



## Description of Pins



Function Diagram

Pins		Type	Description
Name	Serial No.		
RO	1	Output	Reverse Output
RE	2	Input	Reverse Output Enable
DE	3	Input	Drive Enable
DI	4	Input	Drive Input
GND	5	Power	Ground
A	6	I/O	Noninverting Receiver Input and Noninverting Driver Output
B	7	I/O	Inverting Receiver Input and Inverting Driver Output
Vcc	8	Power	RS-485 Transceiver Power Supply

## Limit Parameters

Exceeding the absolute maximum rating may result in permanent damage to the device, and prolonged operation at the absolute maximum rating may affect the reliability of the device.

Name	Symbol	Notes	Min.	Max.	Unit
Positive Supply	Vcc		-0.3	7	V
Control Input Voltage	RE,DE		-0.3	Vcc+0.3	V
Drive Input Voltage	DI		-0.3	Vcc+0.3	V
Drive Output Voltage	A,B		-8	13	V
Reverse Input Voltage	A,B		-8	13	V
Reverse Output Voltage	RO		-0.3	Vcc+0.3	V
Operating Temperature Ranges	T <sub>a</sub>		-40	85	°C
Storage Temperature Range	T <sub>stg</sub>		-60	150	°C

## Electrostatic Protection

Human Body Model (HBM) testing in accordance with EIA/JESD22-A114-B HBM

Test Parameters			Value	Unit
Voltage of Electro-Static Discharge (VESD)	Human Body Model (HBM)	Pin A, B to GND	±15	kV
		Other Pins	±8	kV
	Charged-DeviceModel (CDM)		All Pins	±2



## Electrical Parameters

(V<sub>CC</sub> = +3.3V to +5V, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted, typical at 3.3V and +5V, ambient temperature +25°C.)

Parameters	Symbol	Conditions	Min.	Typ.	Max.	Unit
Power Supply						
Supply Voltage	V <sub>CC</sub>		3	5	5.5	V
Input Circuit Current	I <sub>CC</sub>	Receiving Mode $\overline{RE} = 0$ ; DE = 0; V <sub>CC</sub> =5V		240	650	uA
		Transmitting $\overline{RE} = 1$ ; DE = 1; V <sub>CC</sub> = 5V		270	750	uA
		Receiving Mode $\overline{RE}$ =0;DE=0; V <sub>CC</sub> =3.3V		250	650	uA
		Transmitting Mode $\overline{RE}$ =1;DE=1;V <sub>CC</sub> =3.3V		280	750	uA
Cut-off Current	I <sub>shdn</sub>	$\overline{RE} = V_{CC}$ ,DE=0, V <sub>CC</sub> =3.3V		0.2	10	uA
		$\overline{RE} = V_{CC}$ , DE=0, V <sub>CC</sub> =5V		0.2	10	uA
Logic						
Input a Logic-high Input Voltage	V <sub>IH</sub>	DE,DI,RE	2.0			V
Input a Logic-low Input Voltage	V <sub>IL</sub>	DE,DI,RE			0.8	V
DI Input Voltage Hysteresis	V <sub>HYS</sub>	-7V≤V <sub>CM</sub> ≤12V	10	30		mV
Receiving						
Three-phase Current	I <sub>OZR</sub>	0.4V<V <sub>O</sub> <2.4V			±1	uA
Short Circuit Current	I <sub>OSR</sub>	0V≤V <sub>O</sub> ≤V <sub>CC</sub>	±8		±90	mA
Output High Voltage	V <sub>O</sub>	V <sub>A</sub> =2.8V, V <sub>B</sub> =2.5V, I <sub>R0</sub> =8mA	V <sub>CC</sub> - 1.5			V
Output Low Voltage	V <sub>OL</sub>	V <sub>A</sub> =2.5V, V <sub>B</sub> =2.8V,I <sub>R0</sub> =-8mA			0.4	V
Input Impedance	R <sub>IN</sub>	-7V≤V <sub>CM</sub> ≤12V	96			kΩ
Differential Threshold Voltage	V <sub>TH</sub>		-200		-50	mV
Input Hysteresis Voltage	ΔV <sub>TH</sub>	-7V≤V <sub>CM</sub> ≤12V		25		mV
Transmitting						
Output Voltage (no load)	V <sub>OD1</sub>		3		5.5	V
Output Voltage	V <sub>OD2</sub>	R <sub>L</sub> = 54 Ω, V <sub>CC</sub> = 5 V	1.5		V <sub>CC</sub>	V
Voltage Magnitude Variation	ΔV <sub>OD</sub>	R <sub>L</sub> = 54 Ω			0.2	V
Common Mode Voltage	V <sub>OC</sub>	R <sub>L</sub> = 54 Ω			3	V
Common-mode Voltage Variation	ΔV <sub>OC</sub>	R <sub>L</sub> = 54 Ω			0.3	V
Short Circuit Current	I <sub>OSD</sub>	Short Circuit to Low -7-0V	-250			mA



## Switching Characteristics parameters

(V<sub>CC</sub> = +3.3V to +5V, T<sub>A</sub> = T<sub>MIN</sub> to T<sub>MAX</sub>, unless otherwise noted, typical at 3.3V and +5V, ambient temperature +25°C.)

Parameters	Symbol	Conditions	Min.	Typ.	Max.	Units
<b>Transmitting</b>						
Maximum Data Rate	f <sub>MAX</sub>			10		Mbps
Differential Output Time Delay	t <sub>DD</sub>	RL=60Ω, Figure 3		20	40	ns
Differential Output Conversion Time	t <sub>TD</sub>	RL=60Ω, Figure 3		12	28	ns
Driver Output Time Delay from Low to High	t <sub>PLH</sub>	RL=27Ω, Figure 4		20	40	ns
Driver Output Time Delay from High to Low	t <sub>PHL</sub>	RL=27Ω, Figure 4		20	40	ns
t <sub>plh</sub> - t <sub>phl</sub>   Output Time Delay	t <sub>PDS</sub>	RL=27Ω, Figure 4		1	8	ns
<b>Output Enable and Shutdown Times</b>						
Driver Output Enable to a Logic-low	t <sub>PZL</sub>	RL=110Ω, Figure 6			55	ns
Driver Output Enable to a Logic-high	t <sub>PZH</sub>	RL=110Ω, Figure 5			55	ns
Driver Output from Shutdown to a Logic-high	t <sub>PHZ</sub>	RL=110Ω, Figure 5			85	ns
Driver Output from Shutdown to a Logic-low	t <sub>PLZ</sub>	RL=110Ω, Figure 6			85	ns
Driver Output Enable Time from Shutdown to a Logic-low	t <sub>PSL</sub>	RL=110Ω, Figure 6		20	100	ns
Driver Output Enable Time from Shutdown to a Logic-high	t <sub>PSH</sub>	RL=110Ω, Figure 5		20	100	ns
<b>Receiving</b>						
Shutdown Time	t <sub>SHDN</sub>		50		300	ns
Receiver Delay Time from Low to High	t <sub>RPLH</sub>	VID=0 to 3.0V, CL=15pF, Figure 7		60		ns
Receiver Delay Time from High to Low	t <sub>RPHL</sub>	VID=0 to 3.0V, CL=15pF, Figure 7		60		ns
Trplh - Trphl  Delay Times	t <sub>RPDS</sub>	VID=0 to 3.0V, CL=15pF, Figure 7		3	10	ns
Output Enable Time to Low	t <sub>PRZL</sub>	CL=15pF, Figure 8		100	300	ns
Output Enable Time to High	t <sub>PRZH</sub>	CL=15pF, Figure 8		100	300	ns
Output Shutdown to High	t <sub>PRHZ</sub>	CL=15pF, Figure 8		25	55	ns
Output Shutdown to Low	t <sub>PRLZ</sub>	CL=15pF, Figure 8		25	55	ns
Output Enable Time from Shutdown to Low	t <sub>PRSL</sub>	CL=15pF, Figure 8		100	300	ns
Output Enable Time from Shutdown to High	t <sub>PRSH</sub>	CL=15pF, Figure 8		100	300	ns



## Communication Function Table

Table 1: Transmitting

Inputs			Outputs		Mode
$\overline{RE}$	DE	DI	B	A	
X	1	1	0	1	Normal.
X	1	0	1	0	Normal.
0	0	X	High-Z	High-Z	Normal I
1	0	X	High-Z	High-Z	Shutdown

Table 2: Receiving

Inputs			Outputs	Mode
$\overline{RE}$	DE	A, B	RO	
0	X	>-50mV	1	Normal
0	X	<-200mV	0	Normal
0	X	Input Open	1	Normal I
1	0	X	High-Z	Shutdown



## Test Circuits and Typical Circuits




Figure 1 Transmitting  $V_{OD}$  and  $V_{OC}$




Figure 2 Receiving  $V_{OH}$  and  $V_{OL}$




Figure 3. Differential Output Delay and Conversion Time





Figure 4 Transmission Delay Time







Figure 5. Enable and Shutdown Times ( $t_{PZH}$ ,  $t_{PSH}$ ,  $t_{PHZ}$ )





## MAX485EESA+T

10Mbps communication transceiver




Figure 6. Enable and Shutdown Times ( $t_{PZL}$ ,  $t_{PSL}$ ,  $t_{PLZ}$ )




Fig. 7 Receiving Transmission Delay





Figure 8 Receiving OPEN and CLOSE Times

**Note 1:** The input pulse is supplied by a generator with the following characteristics: PRR = 250kHz, 50% duty cycle,  $t_r \leq 6.0\text{ns}$ ,  $Z_0 = 50\Omega$ .

**Note 2:**  $C_L$  includes probe and stray capacitance.



### Figure 9 Typical Half-duplex RS-485 Network Application



## Detailed Function Description

The MAX485EESA+T series is a low-power transceiver for RS-485 communication network and can support data transmitting rates up to 10Mbps. All components are half duplex, including the Drive Enable (DE) and Receiver Enable (RE) pins. When powered off, the outputs of driver and receiver are high impedance.

### ◆ ESD Protection

The MAX485EESA+T A B pins are particularly susceptible to ESD shocks because they are typically as external pins in products. Human actions like simply touching the pins or other actions can result in ESD problems.

Though MAX485EESA+T itself already has good ESD capabilities, additional ESD protection devices are suggested to be added between the external A pin and B pin to enhance its performance.

### ◆ Low Power and Shutdown Mode

Low power shutdown mode is initiated by turning  $\overline{RE}$  up and turning DE down. When powered off, the device typically draws only 1uA of supply current.  $\overline{RE}$  and DE can be driven simultaneously. When  $\overline{RE}$  in high and DE are less than 50ns, the components are guaranteed to continue. If the input is in this state for at least 300ns, the components are guaranteed to close. From the switching characteristics table, if the Enable Times  $t_{PZH}$  and  $t_{PZL}$  is not in a low power shutdown state and the component to start the enable times is turned off, Time of enabling the driver and receiver from low power off mode ( $t_{PSH}$ ,  $t_{PSL}$ ) takes longer than that of enabling them from disabled mode ( $t_{PZH}$ ,  $t_{PZL}$ ).

### ◆ Bus Supports 256-node Transceiver

The standard RS-485 receiver has an input impedance of 12k $\Omega$  (one unit load), and the standard driver can drive up to 32 unit loads. The MAX485B transceiver has a 1/8 unit load receiver with input impedance (96k $\Omega$ ), allowing 256 transceivers to be connected in parallel on a single communication line. Any combination of these devices and/or other RS-485 transceivers with totaling 32 unit loads or less can be connected to the line.

### ◆ Output Protection


The output protection mechanism can prevent excessive output current and power loss due to faults or bus contention. First, the folded current limit on the output stage can provide immediate short-circuit protection over the entire common-mode voltage range. Second, a thermal shutdown circuit can force the driver output to a high impedance state if the mold temperature becomes too high.





## Package Information

### SOP-8



Symbol	Dimensions In Millimeters		Symbol	Dimensions In Inches	
	Min(mm)	Max(mm)		Min(in)	Max(in)
A	1.350	1.750	A	0.053	0.069
A1	0.100	0.250	A1	0.004	0.010
A2	1.350	1.550	A2	0.053	0.061
b	0.330	0.510	b	0.013	0.020
c	0.170	0.250	c	0.006	0.010
D	4.700	5.100	D	0.185	0.200
E	3.800	4.000	E	0.150	0.157
E1	5.800	6.200	E1	0.228	0.224
e	1.270(BSC)		e	0.050(BSQ)	
L	0.400	1.270	L	0.016	0.050
θ	0°	8°	θ	0°	8°



### Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.