



# Series 800 Mighty Mouse UN Mating Thread Inline and Panel Mount Receptacles 800-010 and 800-011 Ordering Information

**In-Line****Square Flange****Rear Panel Jam Nut**

**Integral Band Platform** for direct attachment of a cable shield using a Band-Master™ ATS strap. Install a boot, or overmold onto the band platform. An accessory thread is available for attaching strain reliefs and backshells.

**Three Shell Options:** Jam nut with o-ring for rear panel mounting, square flange or in-line receptacle for free-hanging cables.

C

How To Order						
Sample Part Number	800-011	-01	M	6-7	P	N
Series (See Table I)	<b>800-010</b> = With Banding Platform <b>800-011</b> = With Accessory Thread					
Shell Style (See Table II)	<b>-01</b> = In-Line <b>-02</b> = Square Flange for Front or Rear Mounting <b>-07</b> = Jam Nut for Rear Panel Mounting (See Jam Nut Panel Cutout Dimensions Page C-3)					
Shell Material and Finish	<b>C</b> = Aluminum / Black Anodize (Non-Conductive) RoHS Compliant <b>M</b> = Aluminum / Electroless Nickel RoHS Compliant <b>NF</b> = Aluminum / Cadmium with Olive Drab Chromate <b>ZNU</b> = Aluminum / Zinc-Nickel with Black Chromate <b>MT</b> = Aluminum / Nickel-PTFE RoHS Compliant <b>Z1</b> = Stainless Steel / Passivated RoHS Compliant					
Shell Size - Insert Arrangement	See Contact Arrangements page C-2					
Contact Type	<div> <b>Connector supplied with crimp contacts</b>  <b>P</b> = Pin  <b>S</b> = Socket            Connectors with contacts are supplied with signal and/or power crimp contacts. These contacts are not installed. Coaxial contacts and non-standard signal contacts are ordered separately.         </div> <div> <b>Connector supplied without contacts</b>  <b>A</b> = Pin Connector  <b>B</b> = Socket Connector         </div> <div> <b>Connector supplied with 30 AWG crimp contacts</b>  <b>G</b> = Pin  <b>H</b> = Socket         </div>					
Shell Key Position (See Table III)	<b>N</b> = Normal <b>X</b> = Pos. X <b>Y</b> = Pos. Y <b>Z</b> = Pos. Z					

**Table I: Series**

<b>800-010</b> Receptacle with Banding Platform	<b>800-011</b> Receptacle with Accessory Thread

**Table II: Shell Style**

<b>-01</b> In-Line	<b>-02</b> Square Flange or Rear Mounting	<b>-07</b> Jam Nut for Rear Panel Mounting

Dimensions in Inches (millimeters) are subject to change without notice.