

Coaxial Cable Connector 24_BMA-N50-2-21/11-_N

Description

Straight panel bulkhead cable jack, flange mount

Interface standards

IEC 60169-33_MIL-STD-348/321 fully intermateable

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.003657 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Stainless Steel	
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Nickel Plating

Related Documents

Outline drawing	DOU-00130826
Assembly instruction	DOC-0000453588
Mounting hole	DOU-00008950

Ordering Information

Single package	24_BMA-N50-2-21/11-_NE
----------------	------------------------

Additional Information

Suitable cables	RG_316/_U
-----------------	-----------