

SMC Surface Mount Schottky Barrier Rectifier

Features

- For surface mounted applications
- High forward surge current capability
- Low power loss,high efficiency
- Low power losses, high efficiency
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260°C

Applications

For use in low voltage high frequency inverters, free wheeling,DC/DC converters, and polarity protection applications.




Mechanical Data

- Case: DO-214AB(SMC)
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026
- Polarity: Cathode line denotes the cathode end

Function Diagram

Reverse Voltage
20-100 V
Forward Current
8 Ampere

DO-214AB(SMC)







Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	SS82C	SS84C	SS86C	SS88C	SS810C	SS815C	SS820C
Device marking code			SS82C	SS84C	SS86C	SS88C	SS810C	SS815C	SS820C
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	V	20	40	60	80	100	150	200
Maximum RMS Voltage	V _{RMS}	V	14	28	42	56	70	105	140
Maximum DC blocking Voltage	V _{DC}	V	20	40	60	80	100	150	200
Maximum Average Forward Rectified Current @60Hz sinewave, Resistance load,TL (Fig.1)	I _{F(AV)}	A	8.0						
Non-repetitive Peak Forward Surge Current @ t=8.3ms Half-sine wave	I _{FSM}	A	150						
Storage temperature	T _{stg}	°C	-55 ~ +150						
Junction temperature	T _j	°C	-55 ~ +125		-55 ~ +150				
Typical Thermal Resistance	R _{θJ-A}	°C /W	47						
	R _{θJ-L}	°C /W	15						

Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	SS82C	SS84C	SS86C	SS88C	SS810C	SS815C	SS820C
Maximum instantaneous forward voltage	$I_F=8.0A$	V_F	V	0.55	0.70	0.85	0.95			
Maximum DC reverse current at rated DC blocking voltage	$V_R=V_{DC}, T_A=25^{\circ}C$	I_{R1}	mA	0.5			0.05			
	$V_R=V_{DC}, T_A=100^{\circ}C$	I_{R2}		50			10			
Typical junction capacitance	4.0V DC, 1MHz	C_J	pF	880			720			

Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



SS82C THRU SS820C

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SMC	R3	0.257	3000	6000	48000	13"

● Package Outline Dimensions (SMC/DO-214AB)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	2.85	3.27	0.112	0.129
B	6.60	7.11	0.261	0.281
C	5.59	6.22	0.221	0.246
D	1.99	2.61	0.078	0.103
E	0.76	1.52	0.030	0.060
F	-	0.20	-	0.008
G	7.75	8.13	0.306	0.321
H	0.15	0.31	0.006	0.012

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
M	3.82	-	0.151	-
J	3.03	-	0.120	-
K	-	3.84	-	0.152