

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		A	INITIAL RELEASE	30JUN2011	PKS	RRP
			A1	ECR-14-003077	28FEB2014	PKS	RRP
			A2	ECR-14-009219	19JUN2014	PKS	RRP

D

D

C




C

B

B

A

A



NOTES

- 1

Geeignet fuer Kupferlackdraht Ø0.63...0.81mm
Einzeldraht oder zwei Draehte gleichen Durchmessers
SLOT ACCEPTS:
SINGLE OR DOUBLE MAGNET WIRE
SAME DIAMETERS 0.63...0.81mm DIA
- 2

Anlieferungszustand: Kontakte fortlaufend mit
Papierzwise­n­lage auf Kunststoffspule aufgewickelt
Max. 5 Splice Stellen pro Spule
Splice Stellen nicht miteinander verbunden
DELIVERYSTATE: CONTACTS CONTINUOUS REELED WITH PAPER
INTERLAYER ON PLASTIC-REEL.
MAX. 5 SPLICES PER REEL
SPLICES BE NOT BONDED TOGETHER.

3

Kontaktkammer nach Zeichnung } 411-18516
CAVITY ACCORDING DWG.

4

Kennziffer fuer Drahtgroessenbereich (15)
IDENTIFICATION NO. FOR MAGNET WIRE RANGE (15)

5

Materialdicke } 0.32 ± 0.02
STOCK THICKNESS



6

Materialdicke an den Stripping shoulders ist 0.32^{+0.04}
STOCK THICKNESS AT THE STRIPPING SHOULDERS IS 0.32^{+0.04}

7


DIE FEED 5.6 ±0.05

DIRECTION OFF TOP OF THE REEL



A2

1740829-2	A	CuSn	PRETINNED	MAG-MATE .300 mod.	9
1740829-1	A	CuSn	PRETINNED	MAG-MATE .300 mod.	8
TE PART NO	REV.	MATERIAL	SURFACE COLOR	DESCRIPTION	REELING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SENTHIL 30JUN2011	TE Connectivity					
		CHK SENTHIL 30JUN2011						
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD RAJENDRA 01JUL2011	NAME MAG-MATE Kontakt mit Loetpin -					
	0 PLC } ± 1 PLC } ± 2 PLC } ± 0.2 3 PLC } ± 4 PLC } ± ANGLES } ±1°	PRODUCT SPEC						SIZE CAGE CODE DRAWING NO RESTRICTED TO
		APPLICATION SPEC	A300779C-1740829					
		MATERIAL SEE TABLE	FINISH -	WEIGHT -				
Customer Drawing			SCALE 10:1	SHEET 1 OF 1	REV A2			