

620-051
Strain Relief
Rotatable Coupling - 45° and 90°




62

**CONNECTOR
DESIGNATOR**
G
**ROTATABLE
COUPLING**

620 G A 051 M 17

Product Series ——— 620
Connector Designator ——— G
Angle and Profile ——— A
A = 90°
B = 45°

Shell Size (Table III) ——— 17
Finish (Table II) ——— M
Basic Part No. ——— 051



See inside back cover fold-out or pages 13 and 14 for Tables I and II.

TABLE III: CABLE ENTRY

Shell Size	E Closed Max		F Max		G Max		H Closed Max		J Max		Cable Entry	
											Closed	Open
11	1.071	(27.2)	.929	(23.6)	.903	(22.9)	1.650	(41.9)	.929	(23.6)	.177	(4.5) .286 (7.3)
13	1.071	(27.2)	.929	(23.6)	.977	(24.8)	1.650	(41.9)	.929	(23.6)	.177	(4.5) .286 (7.3)
15	1.280	(32.5)	1.056	(26.8)	1.151	(29.2)	1.765	(44.8)	1.056	(26.8)	.250	(6.4) .416 (10.6)
17	1.392	(35.4)	1.233	(31.3)	1.281	(32.5)	1.874	(47.6)	1.233	(31.3)	.291	(7.4) .476 (12.1)
19	1.517	(38.5)	1.296	(32.9)	1.406	(35.7)	1.918	(48.7)	1.296	(32.9)	.348	(8.8) .626 (15.9)
23	1.642	(41.7)	1.358	(34.5)	1.576	(40.0)	1.962	(49.8)	1.358	(34.5)	.429	(10.9) .831 (21.1)
25	1.767	(44.9)	1.420	(36.1)	1.666	(42.3)	2.006	(51.0)	1.420	(36.1)	.523	(13.3) .956 (24.3)
29	1.905	(48.4)	1.634	(41.5)	2.046	(52.0)	2.301	(58.4)	1.634	(41.5)	.643	(16.3) 1.081 (27.5)
33	1.968	(50.0)	1.859	(47.2)	2.209	(56.1)	2.389	(60.7)	1.859	(47.2)	.704	(17.9) 1.187 (30.1)

1. Cable Entry is defined as the accommodation entry for the wire bundle or cable. Dimensions are not intended for inspection criteria.
2. Metric dimensions (mm) are indicated in parentheses.