


## 1.Features

- $V_{DS(V)}=60V$
- $R_{DS(ON)}<63m\Omega(V_{GS}=10V)$
- $R_{DS(ON)}<71m\Omega(V_{GS}=5V)$
- Ultra Low On-Resistance
- Peak Current vs Pulse Width Curve
- UIS Rating Curve
- Switching Time vs  $R_{GS}$  Curves

## 2.Pinning information

| Pin | Symbol | Description |
|-----|--------|-------------|
| 1   | G      | GATE        |
| 2   | D      | SOURCE      |
| 3   | S      | DRAIN       |

TO-252(DPAK)  
top view



## 3.Absolute Maximum Ratings $T_c=25^{\circ}C$

| Parameter                                                      | Symbol    | Value             | Units          |
|----------------------------------------------------------------|-----------|-------------------|----------------|
| Drain to Source Voltage (Note 1)                               | $V_{DS}$  | 60                | V              |
| Drain to Gate Voltage ( $R_{GS}=20k\Omega$ )(Note 1)           | $V_{DGR}$ | 60                | V              |
| Gate to Source Voltage                                         | $V_{GS}$  | $\pm 16$          | V              |
| Drain Current - Continuous ( $T_c=25^{\circ}C$ , $V_{GS}=5V$ ) | $I_D$     | 17                | A              |
| - Continuous ( $T_c=25^{\circ}C$ , $V_{GS}=10V$ ) (Figure 2)   |           | 18                | A              |
| - Continuous ( $T_c=135^{\circ}C$ , $V_{GS}=5V$ )              |           | 8                 | A              |
| - Continuous ( $T_c=135^{\circ}C$ , $V_{GS}=4.5V$ ) (Figure 2) |           | 8                 | A              |
| Pulsed Drain Current                                           | $I_{DM}$  | Figure 4          |                |
| Pulsed Avalanche Rating                                        | UIS       | Figures 6, 17, 18 |                |
| Power Dissipation                                              | $P_D$     | 49                | W              |
| Derate Above $25^{\circ}C$                                     |           | 0.327             | W/ $^{\circ}C$ |



|                                            |                |            |    |
|--------------------------------------------|----------------|------------|----|
| Storage Temperature                        | $T_J, T_{STG}$ | -55 to 175 | °C |
| Maximum Temperature for Soldering          |                |            |    |
| Leads at 0.063in (1.6mm) from Case for 10s | $T_L$          | 300        | °C |
| Package Body for 10s, See Techbrief TB334  | $T_{pkg}$      | 260        | °C |

Notes:

1.  $T_J$ =25°C to 150°C.

CAUTION: Stresses above those listed in “Absolute Maximum Ratings” may cause permanent damage to the device.

This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.



## 6. Electrical Characteristic ( $T_c=25^\circ\text{C}$ unless otherwise noted)

| Parameter                              | Symbol          | Conditions                                                                                             | Min | Typ | Max       | Units              |
|----------------------------------------|-----------------|--------------------------------------------------------------------------------------------------------|-----|-----|-----------|--------------------|
| Drain to Source Breakdown Voltage      | $BV_{DSS}$      | $I_D=250\mu\text{A}$ , $V_{GS}=0\text{V}$ , Figure 12                                                  | 60  |     |           | V                  |
|                                        |                 | $I_D=250\mu\text{A}$ , $V_{GS}=0\text{V}$ , $T_c=-40^\circ\text{C}$                                    | 60  |     |           | V                  |
| Zero Gate Voltage Drain Current        | $I_{DSS}$       | $V_{DS}=55\text{V}$ , $V_{GS}=0\text{V}$                                                               |     |     | 1         | $\mu\text{A}$      |
|                                        |                 | $V_{DS}=50\text{V}$ , $V_{GS}=0\text{V}$ , $T_c=150^\circ\text{C}$                                     |     |     | 250       | $\mu\text{A}$      |
| Gate to Source Leakage Current         | $I_{GSS}$       | $V_{GS}=\pm 16\text{V}$                                                                                |     |     | $\pm 100$ | nA                 |
| Gate to Source Threshold Voltage       | $V_{GS(th)}$    | $V_{DS}=V_{GS}$ , $I_D=250\mu\text{A}$ , Figure 11                                                     | 1   |     | 2.1       | V                  |
| Drain to Source On Resistance          | $R_{DS(on)}$    | $I_D=18\text{A}$ , $V_{GS}=10\text{V}$ , Figure 9,10                                                   |     | 52  | 63        | m $\Omega$         |
|                                        |                 | $I_D=8\text{A}$ , $V_{GS}=5\text{V}$ , Figure 9                                                        |     | 60  | 71        | m $\Omega$         |
|                                        |                 | $I_D=8\text{A}$ , $V_{GS}=4.5\text{V}$ , Figure 9                                                      |     | 64  | 75        | m $\Omega$         |
| Thermal Resistance Junction to Case    | $R_{\theta JC}$ | TO-252AA                                                                                               |     |     | 3.06      | $^\circ\text{C/W}$ |
| Thermal Resistance Junction to Ambient | $R_{\theta JA}$ |                                                                                                        |     |     | 100       | $^\circ\text{C/W}$ |
| Turn-On Time                           | $t_{(on)}$      | $V_{DD}=30\text{V}$ , $I_D=8\text{A}$<br>$V_{GS}=4.5\text{V}$ , $R_{GS}=22\Omega$<br>Figures 15, 21,22 |     |     | 153       | ns                 |
| Turn-On Delay Time                     | $t_{D(on)}$     |                                                                                                        |     | 13  |           | ns                 |
| Rise Time                              | $t_r$           |                                                                                                        |     | 89  |           | ns                 |
| Turn-Off Delay Time                    | $t_{D(off)}$    |                                                                                                        |     | 22  |           | ns                 |
| Fall Time                              | $t_f$           |                                                                                                        |     | 37  |           | ns                 |
| Turn-Off Time                          | $t_{(off)}$     |                                                                                                        |     |     | 89        | ns                 |
| Turn-On Time                           | $t_{(on)}$      | $V_{DD}=30\text{V}$ , $I_D=18\text{A}$<br>$V_{GS}=10\text{V}$ , $R_{GS}=24\Omega$<br>Figures 16, 21,22 |     |     | 59        | ns                 |
| Turn-On Delay Time                     | $t_{D(on)}$     |                                                                                                        |     | 5.3 |           | ns                 |
| Rise Time                              | $t_r$           |                                                                                                        |     | 34  |           | ns                 |
| Turn-Off Delay Time                    | $t_{D(off)}$    |                                                                                                        |     | 41  |           | ns                 |
| Fall Time                              | $t_f$           |                                                                                                        |     | 50  |           | ns                 |
| Turn-Off Time                          | $t_{(off)}$     |                                                                                                        |     |     | 136       | ns                 |



|                               |              |                                                |                  |  |      |      |    |
|-------------------------------|--------------|------------------------------------------------|------------------|--|------|------|----|
| Total Gate Charge             | $Q_{g(tot)}$ | $V_{GS}=0$ to 10V                              | $V_{DD}=30V$     |  | 12   | 15   | nC |
| Gate Charge at 5V             | $Q_{g(5)}$   | $V_{GS}=0$ to 5V                               | $I_D=8A$         |  | 6.8  | 8.2  | nC |
| Threshold Gate Charge         | $Q_{g(th)}$  | $V_{GS}=0$ to 1V                               | $I_{g(REF)}=1mA$ |  | 0.54 | 0.65 | nC |
| Gate to Source Gate Charge    | $Q_{gs}$     | (Figures 14, 19, 20)                           |                  |  | 1.7  |      | nC |
| Gate to Drain "Miller" Charge | $Q_{gd}$     |                                                |                  |  | 3    |      | nC |
| Input Capacitance             | $C_{iss}$    | $V_{DS}=25V, V_{GS}=0V, f=1MHz$<br>(Figure 13) |                  |  | 485  |      | pF |
| Output Capacitance            | $C_{oss}$    |                                                |                  |  | 130  |      | pF |
| Reverse Transfer Capacitance  | $C_{rss}$    |                                                |                  |  | 28   |      | pF |
| Source to Drain Diode Voltage | $V_{SD}$     | $I_{SD}=8A$                                    |                  |  |      | 1.25 | V  |
|                               |              | $I_{SD}=4A$                                    |                  |  |      | 1    | V  |
| Reverse Recovery Time         | $t_{rr}$     | $I_{SD}=8A, dI_{SD}/dt=100A/\mu s$             |                  |  |      | 70   | ns |
| Reverse Recovered Charge      | $Q_{rr}$     | $I_{SD}=8A, dI_{SD}/dt=100A/\mu s$             |                  |  |      | 165  | nC |



## 7.1 Typical characteristic




Figure 1: Normalized Power Dissipation vs Case Temperature




Figure 2: Maximum Continuous Drain Current vs Case Temperature




Figure 3: Normalized Maximum Transient Thermal Impedance




Figure 4: Peak Current Capability



## 7.2 Typical characteristic




Figure 5: Forward Bias Safe Operating Area




Figure 6: Unclamped Inductive Switching Capability




Figure 7: Transfer Characteristics




Figure 8: Saturation Characteristics




Figure 9: Drain To Source On Resistance Vs Gate Voltage And Drain Current




Figure 10: Normalized Drain to Source On Resistance vs Junction Temperature



### 7.3 Typical characteristic




Figure 11: Normalized Gate Threshold Voltage Vs Junction Temperature




Figure 12: Normalized Drain To Source Breakdown Voltage Vs Junction Temperature




Figure 13: Capacitance vs Drain To Source Voltage




Figure 14: Gate Charge Waveforms For Constant Gate Current




Figure 15: Switching Time vs Gate Resistance




Figure 16: Switching Time vs Gate Resistance



## 7.4 Typical characteristic




Figure 15. Unclamped Energy Test Circuit




Figure 16. Unclamped Energy Waveforms




Figure 17. Gate Charge Test Circuit




Figure 18. Gate Charge Waveforms




Figure 19. Switching Time Test Circuit





Figure 20. Switching Time Waveforms



8.TO-252 PACKAGE OUTLINE DIMENSIONS




DIMENSIONS (mm are the original dimensions)

| Symbol | A    | A2   | B    | B2   | C    | C2   | D    | D1   | E    | E1   | G    | H     | L    | L2   | V1 | V2 |
|--------|------|------|------|------|------|------|------|------|------|------|------|-------|------|------|----|----|
| Min    | 2.10 | 0    | 0.66 | 5.18 | 0.40 | 0.44 | 5.90 | 5.30 | 6.40 | 4.63 | 4.47 | 9.50  | 1.09 | 1.35 |    | 0° |
| Max    | 2.50 | 0.10 | 0.86 | 5.48 | 0.60 | 0.58 | 6.30 | REF  | 6.80 |      | 4.67 | 10.70 | 1.21 | 1.65 |    | 6° |



9.Ordering information



yy: Year Code  
ww: Week Code

| Order Code          | Package | Base QTY | Delivery Mode |
|---------------------|---------|----------|---------------|
| UMW RFD12N06RLESM9A | TO-252  | 2500     | Tape and reel |



## 10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.