


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AF	50		A	REV & REL PER 0G3A-0053-03	14FEB03	JR

IDENTIFICATION NUMBER 43
FOR MAGNET WIRE RANGE



- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 8.38 ± 0.08 $[\.330 \pm .003]$ CENTERS.
- 2 SLOT TERMINATES A SINGLE MAGNET WIRE ONLY. COPPER RANGE: 1.54–1.83mm $[\#14.5-\#13]$ AWG. ALUMINUM RANGE: 1.83–2.05mm $[\#13-\#12]$ AWG.
- 3 AFTER INSERTION INTO PLASTIC 'HOLDER' TAB PORTION MUST BE BENT OVER 45 TO 90 OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.



1217902

B

A

1217902-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 03DEC2002	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK KURT A. RANDOLPH 03DEC2002				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD KURT A. RANDOLPH 03DEC2002	NAME TAB, 4.75 $[\.187]$ FASTON,™ 500 SERIES MAG-MATE™			
	0 PLC ± -	PRODUCT SPEC 108-2053	SIZE A2			
	1 PLC ± -	APPLICATION SPEC 114-2066				
MATERIAL H03 BRASS	FINISH 0.002032 $[\.000080]$ MIN TIN PLATE	WEIGHT -	CAGE CODE 00779	DRAWING NO C=1217902	RESTRICTED TO -	SCALE 6:1
CUSTOMER DRAWING		SHEET 1 OF 1		REV A		