






Mating face according to : MIL-C-24308 / DIN 41652 / CECC 75301-802



Connector retention and insertion forces on the PCB = 25 / 80 newtons

09 66 252 6615	M 3	2					Dat.	Name
09 66 252 7615	M 3	3					Detail.	02/sept/00 jfb
09 66 252 5615	M 3	0.76 µm Au					Insp.	
09 66 252 6616	4-40 UNC	2	27961	24/nov/00	jfb		Stand.	
09 66 252 7616	4-40 UNC	3	27952	26/oct/00	jfb			
09 66 252 5616	4-40 UNC	0.76 µm Au	27948	02/sept/00	jfb			
Part number	Nut thread	Performance level	Mod.	Dat.	Name			



All Dim. in mm
Orig. Size DIN A 4

D-Sub 15 poles low profil angle female, solder pin with nut and grounding board lock.

Maßstab/
Scale

1.5:1

HARTING EURL
F-95972 Paris



TB 0966252x61x

Sub.

Blatt/ Page

2 / 6

09 66 252 6615
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	M 3
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 252 5616
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	UNC4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 252 5615
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	M 3
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



Data sheets are available in following formats
2D files

Typenblatt

Typenblatt

09 66 252 6616
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	UNC4-40
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 252 7615
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	M 3
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 252 7616
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	UNC4-40
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF