

SOT-23 Plastic-Encapsulate MOSFETS

Features

- $V_{DS}=20V$
- $I_D=5.5A$
- $R_{DS(on)}@V_{GS}=4.5V < 25m\Omega$
- $R_{DS(on)}@V_{GS}=2.5V < 32m\Omega$
- Trench Power MV MOSFET technology
- Voltage controlled small signal switch
- Fast Switching Speed

Applications



- Battery operated systems
- Solid-state relays
- Direct logic-level interface: TTL/CMOS

Mechanical Data

- Case: SOT-23
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Reference News

Drain-source Voltage
20 V
Drain Current
5.5 Ampere



Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER		SYMBOL	UNIT	VALUE
Drain-source Voltage		V_{DS}	V	20
Gate-source Voltage		V_{GS}	V	± 10
Drain Current ⁽¹⁾	$T_A=25^{\circ}C$ @ Steady State	I_D	A	5.5
Pulsed Drain Current ⁽²⁾		I_{DM}	A	20
Total Power Dissipation @ $T_A=25^{\circ}C$		P_D	W	1.2
Thermal Resistance Junction-to-Ambient @ Steady State ⁽¹⁾		$R_{\theta JA}$	$^{\circ}C / W$	104
Junction and Storage Temperature Range		T_J, T_{STG}	$^{\circ}C$	-55 ~+150

Note :
(1)Surface Mounted on 1" x 1" FR4 Board. Pulse test.
(2)Pulse width limited by maximum junction temperature.

Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-23	R1	0.008	3000	45000	180000	7"

● Static Parameter Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=250\mu A$	V	20	—	—
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=20V, V_{GS}=0V$	μA	—	—	1.0
Gate-Body Leakage Current	I_{GSS}	$V_{GS}=\pm 8.0V, V_{DS}=0V$	nA	—	—	± 100
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	V	0.45	0.62	1.0
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS}=4.5V, I_D=4.5A$	m Ω	—	19.5	25
		$V_{GS}=2.5V, I_D=3.0A$		—	25	32
		$V_{GS}=1.8V, I_D=2.7A$		—	33	49
Forward Transconductance	g_{fs}	$V_{DS}=15V, I_D=5.0A$	S	—	40	—
Diode Forward Voltage	V_{SD}	$I_S=4.5A, V_{GS}=0V$	V	—	0.8	1.2







● Dynamic Parameters (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C_{iss}	$V_{DS}=10V$ $V_{GS}=0V$ $f=1MHz$	pF	—	418	—
Output Capacitance	C_{oss}			—	82	—
Reverse Transfer Capacitance	C_{rss}			—	70	—






● Switching Parameters (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Total Gate Charge	Q _g	V _{GS} =4.5V V _{DS} =10V I _D =4.5A	nC	—	6.0	—
Gate-Source Charge	Q _{gs}			—	1.0	—
Gate-Drain Charge	Q _{gd}			—	2.0	—
Reverse Recovery Time	t _{rr}	I _F =1.0A, di/dt=-100A/us	ns	—	13	25
Turn-on Delay Time	t _{D(on)}	V _{GS} =4.5V V _{DS} =10V R _G =3.0Ω I _D =4.5A		—	4.0	—
Turn-on Rise Time	t _r			—	20	—
Turn-off Delay Time	t _{D(off)}			—	23	—
Turn-off fall Time	t _f			—	23	—

● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Package Outline Dimensions (SOT-23)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.90	1.15	0.035	0.045
A1	-	0.10	-	0.004
A2	0.90	1.05	0.035	0.041
b	0.30	0.50	0.012	0.020
c	0.10	0.20	0.004	0.008
D	2.80	3.00	0.110	0.118
E	1.20	1.40	0.047	0.055
E1	2.25	2.55	0.089	0.100
e	0.950TYP		0.037TYP	
e1	1.80	2.00	0.071	0.079
L	0.550REF		0.022REF	
L1	0.30	0.50	0.012	0.020
θ	-	8°	-	8°

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	0.80	-	0.031	-
K	-	0.90	-	0.035
M	2.00	-	0.078	-
N	-	1.90	-	0.074