


1.Features

- 250 watts peak pulse power ($t_p=8/20\mu s$)
- ESD Protection > 40 kilovolts
- Protects one bidirectional line or two unidirectional lines
- Working Voltages: 5V, 12V, 15V, 24V and 36V
- Low clamping voltages
- IEC 61000-4-2 (ESD) $\pm 15kV$ (air), $\pm 8kV$ (contact)
- IEC 61000 4 4 (EFT) 40A (5/50ns)

2.Applications

- Cellular Handsets and Accessories
- Control & Monitoring Systems
- Portable Electronics
- Set-Top Box
- Servers, Notebook, and Desktop PC
- Wireless Bus Protection

3.Pinning information




SOT-23



4. Absolute Maximum Ratings $T_A = 25^\circ\text{C}$

Parameter	Symbol	Value	Units
Peak Pulse Power($t_p=8/20\mu\text{s}$)	P_{PP}	250	Watts
Lead Soldering Temperature	T_L	260(10sec)	$^\circ\text{C}$
Junction Temperature	T_J	-55 to 125	$^\circ\text{C}$
Storage Temperature	T_{STG}	-55 to 150	$^\circ\text{C}$

5. Electrical Parameters ($T=25^\circ\text{C}$)



Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_F	Forward Current
V_F	Forward Voltage @ I_F



6.1 Electrical Characteristic (BST23C052V)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Reverse Stand-Off Voltage	V_{RWM}				5	V
Reverse Breakdown Voltage	V_{BR}	$I_T=1mA$	6			V
Reverse Leakage Current	I_R	$V_{RWM}=5V, T=25^{\circ}C$			1	μA
Peak Pulse Current	I_{PP}	$t_p=8/20\mu s$			17	A
Clamping Voltage	V_C	$I_{PP}=1A, t_p=8/20\mu s$			9.8	V
Maximum Clamping Voltage	V_C	$I_{PP}=18A, t_p=8/20\mu s$			16.7	V
Junction Capacitance	C_J	Pin 2 to 3, $V_R=0V, f=1MHz$		100		pF
		Pin 1 to 3 and Pin 2 to 3		100		pF
		$V_R=0V, f=1MHz$				

6.2 Electrical Characteristic (BST23C122V)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Reverse Stand-Off Voltage	V_{RWM}				12	V
Reverse Breakdown Voltage	V_{BR}	$I_T=1mA$	13.3			V
Reverse Leakage Current	I_R	$V_{RWM}=12V, T=25^{\circ}C$			1	μA
Peak Pulse Current	I_{PP}	$t_p=8/20\mu s$			12	A
Clamping Voltage	V_C	$I_{PP}=1A, t_p=8/20\mu s$			19	V
Maximum Clamping Voltage	V_C	$I_{PP}=12A, t_p=8/20\mu s$			25	V
Junction Capacitance	C_J	Pin 1 to 2, $V_R=0V, f=1MHz$		30		pF
		Pin 1 to 3 and Pin 2 to 3		50		pF
		$V_R=0V, f=1MHz$				



6.3 Electrical Characteristic (BST23C152V)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Reverse Stand-Off Voltage	V_{RWM}				15	V
Reverse Breakdown Voltage	V_{BR}	$I_T=1mA$	16.7			V
Reverse Leakage Current	I_R	$V_{RWM}=15V, T=25^{\circ}C$			1	μA
Peak Pulse Current	I_{PP}	$t_p=8/20\mu s$			10	A
Clamping Voltage	V_C	$I_{PP}=1A, t_p=8/20\mu s$			24	V
Maximum Clamping Voltage	V_C	$I_{PP}=10A, t_p=8/20\mu s$			30	V
Junction Capacitance	C_J	Pin 1 to 2, $V_R=0V, f=1MHz$		25		pF
		Pin 1 to 3 and Pin 2 to 3		40		pF
		$V_R=0V, f=1MHz$				

6.4 Electrical Characteristic (BST23C242V)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Reverse Stand-Off Voltage	V_{RWM}				24	V
Reverse Breakdown Voltage	V_{BR}	$I_T=1mA$	26.7			V
Reverse Leakage Current	I_R	$V_{RWM}=24V, T=25^{\circ}C$			1	μA
Peak Pulse Current	I_{PP}	$t_p=8/20\mu s$			5	A
Clamping Voltage	V_C	$I_{PP}=1A, t_p=8/20\mu s$			43	V
Maximum Clamping Voltage	V_C	$I_{PP}=5A, t_p=8/20\mu s$			60	V
Junction Capacitance	C_J	Pin 1 to 2, $V_R=0V, f=1MHz$		20		pF
		Pin 1 to 3 and Pin 2 to 3		30		pF
		$V_R=0V, f=1MHz$				







6.5 Electrical Characteristic (BST23C362V)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Reverse Stand-Off Voltage	V_{RWM}				36	V
Reverse Breakdown Voltage	V_{BR}	$I_T=1mA$	40			V
Reverse Leakage Current	I_R	$V_{RWM}=36V, T=25^{\circ}C$			1	μA
Peak Pulse Current	I_{PP}	$t_p=8/20\mu s$			4	A
Clamping Voltage	V_C	$I_{PP}=1A, t_p=8/20\mu s$			60	V
Maximum Clamping Voltage	V_C	$I_{PP}=4A, t_p=8/20\mu s$			75	V
Junction Capacitance	C_J	Pin 1 to 2, $V_R=0V, f=1MHz$		20		pF
		Pin 1 to 3 and Pin 2 to 3		26		pF
		$V_R=0V, f=1MHz$				




7. Typical characteristic

 P_{PP}, Peak Pulse Power (W) t_d, Pulse Duration (μs)	 Percent of Rated Power for I_{PP} Ambient Temperature - $T_A(^{\circ}C)$	Figure 1: Peak Pulse Power vs. Pulse Time	Figure 2: Power Derating Curve
 Percent of I_{PP} Time (μs) Waveform Parameters $t_r=8\mu s$ $t_d=20\mu s$ e^{-1} $t_d=I_{PP}/2$	 Ref1 500mV 10.0ns	Figure 3: Pulse Waveform	Figure 4: ESD Pulse Waveform (Per IEC 61000-4-2)



8.SOT-23 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	B	b _p	C	D	E	H _E	A1	L _p
Min	0.95	1.78	0.35	0.08	2.70	1.20	2.20	0.013	0.20
Max	1.40	2.04	0.50	0.19	3.10	1.65	3.00	0.100	0.50



9.Ordering information



y: Year Code
ww: Week Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW BST23C242V	CB2	SOD-323	3000	Tape and reel
UMW BST23C052V	5B2	SOD-323	3000	Tape and reel
UMW BST23C122V	AB2	SOD-323	3000	Tape and reel
UMW BST23C152V	BB2	SOD-323	3000	Tape and reel
UMW BST23C362V	DB2	SOD-323	3000	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.