




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	3	REVISED PER ECO-16-004800	07SEP2016	NK	MZ
AG		REVISED PER ECO-17-004657	05APR2017	RS	MZ
AH		REVISED PER ECO-19-011232	08AUG2019	RS	MZ



- 1 HOUSING: THERMOPLASTIC, COLOR: BLACK.
- 2 PERIPHERAL SEAL: ELASTOMER, COLOR: BLACK.
- 3 CONTACT:
BODY - BRASS, .000030 MIN GOLD FOR A LENGTH OF .200 MIN FROM MATING END, GOLD FLASH ON REMAINDER, BOTH OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN-LEAD OVER .000100 MIN COPPER.
- 4 CONTACT:
BODY - BRASS, .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN-LEAD OVER .000100 MIN COPPER.
- 5 CONTACT:
BODY - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
- 6 .009 MAXIMUM CONTACT LEAD-IN SEAM GAP PERMISSIBLE ON MATING FACE END.
- 7 CONTACT:
BODY - BRASS, .000030 MIN GOLD FOR A LENGTH OF .200 MIN FROM MATING END, GOLD FLASH ON REMAINDER, BOTH OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN OVER .000100 MIN COPPER.
- 8 CONTACT:
BODY - BRASS, .000100 MIN TIN OVER .000050 MIN NICKEL.
POST - BRASS, .000100 MIN TIN OVER .000100 MIN COPPER.
- 9 FLANGE SEAL: ELASTOMER, COLOR: BLACK.

OBSOLETE	NO	NO	.547	7	ALL	2-208224-9
	NO	NO	.490	7	ALL	2-208224-8
	YES	YES	.368	7	1-17, 19-37	2-208224-5
	NO	NO	.557	3	1-9, 11-31, 33-37	2-208224-4
	NO	YES	.557	3	ALL	2-208224-3
	NO	NO	.368	7	ALL	2-208224-2
OBSOLETE	NO	YES	.368	8	1-10, 12-29, 31-37	1-208224-8
	NO	YES	.368	8	4,8,10,23,31,34-36	1-208224-7
	NO	YES	.368	8	1-10, 12-29, 31-37	1-208224-6
	NO	YES	.368	5	1-22, 24-37	1-208224-5
	NO	NO	.368	5	ALL	1-208224-3
	NO	YES	.368	5	1-10, 12-29, 31-37	1-208224-2
OBSOLETE	NO	YES	.368	4	1-10, 12-29, 31-37	1-208224-0
	NO	NO	.368	3	ALL	208224-9
OBSOLETE	NO	YES	.368	4	1-22, 24-37	208224-5
	NO	YES	.368	4	4,8,10,23,31,34-36	208224-4
	NO	YES	.368	4	1-10, 12-29, 31-37	208224-3
	NO	NO	.368	4	ALL	208224-2
OBSOLETE	NO	NO	.557	3	ALL	208224-1
	FLANGE SEAL	PERIPHERAL SEAL	L	CONTACT FINISH	SELECT LOADED IN POSITIONS	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN S. WELDON 26FEB2003	TE Connectivity		
DIMENSIONS:			CHK S. HEADER 26FEB2003	NAME RECEPTACLE ASSEMBLY, POSTED, REVERSE SEX, SERIES 1, 23-37, CPC		
INCHES			APVD S. HEADER 26FEB2003	SIZE CAGE CODE DRAWING NO		
TOLERANCES UNLESS OTHERWISE SPECIFIED:			PRODUCT SPEC	RESTRICTED TO		
0 PLC ±.0			APPLICATION SPEC	A100779C=208224		
1 PLC ±.0			WEIGHT	SCALE 3:1		
2 PLC ±.0			CUSTOMER DRAWING	SHEET 1 OF 1		
3 PLC ±.0				REV AH		
4 PLC ±.0000						
ANGLES ±.0000						
FINISH						