

1.Description

- Low $R_{DS(ON)}$ to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- Optimized Gate Charge to Minimize Switching Losses

2.1Features

- $V_{DS(V)}=30V$
- $I_D=73A(V_{GS}=10V)$
- $R_{DS(ON)}<6.2m\Omega(V_{GS}=10V)$
- $R_{DS(ON)}<9.3m\Omega(V_{GS}=4.5V)$


2.2Features

- VCore Applications
- DC-DC Converters
- High/Low Side Switching

3.Pinning information

Pin	Symbol	Description
1	G	GATE
2	D	DRAIN
3	S	SOURCE

TO-252(DPAK)
top view



4.Absolute Maximum Ratings $T_J=25^{\circ}C$

Parameter			Symbol	Value	Units
Drain-to-Source Voltage			V _{DSS}	30	V
Gate-to-Source Voltage			V _{GS}	±20	V
Continuous Drain Current (R _{θJA}) (Note 1)	Steady State	T _A =25°C	I _D	14	A
		T _A =85°C		10.9	A
Power Dissipation (R _{θJA}) (Note 1)		T _A =25°C	P _D	2	W
Continuous Drain Current (R _{θJA}) (Note 2)		T _A =25°C	I _D	11.2	A
		T _A =85°C		8.7	A
Power Dissipation (R _{θJA}) (Note 2)		T _A =25°C	P _D	1.3	W



Continuous Drain Current ($R_{\theta JC}$) (Note 1)	Steady State	$T_C=25^{\circ}\text{C}$	I_D	73	A
		$T_C=85^{\circ}\text{C}$		56	A
Power Dissipation ($R_{\theta JC}$) (Note 1)		$T_C=25^{\circ}\text{C}$	P_D	54.5	W
Pulsed Drain Current	$t_p=10\mu\text{s}$	$T_C=25^{\circ}\text{C}$	I_{DM}	146	A
Current Limited by Package		$T_A=25^{\circ}\text{C}$	$I_{DmaxPkg}$	45	A
Junction and Storage Temperature		$T_A=25^{\circ}\text{C}$	T_J, T_{STG}	-55 to 175	$^{\circ}\text{C}$
Source Current (Body Diode)			I_S	45	A
Drain to Source dv/dt			dv/dt	6	V/ns
Single Pulse Drain-to-Source Avalanche Energy ($T_J=25^{\circ}\text{C}$, $V_{DD}=50\text{V}$, $V_{GS}=10\text{V}$, $I_L=15\text{A}_{pk}$, $L=1\text{mH}$, $R_G=25\Omega$)			E_{AS}	112.5	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			T_L	260	$^{\circ}\text{C}$

5. Thermal resistance rating

Parameter	Symbol	Value	Units
Junction-to-Case (Drain)	$R_{\theta JC}$	1.9	$^{\circ}\text{C/W}$
Junction-to-TAB (Drain)	$R_{\theta JC-TAB}$	3.5	$^{\circ}\text{C/W}$
Junction-to-Ambient-Steady State (Note 1)	$R_{\theta JA}$	56.6	$^{\circ}\text{C/W}$
Junction-to-Ambient-Steady State (Note 2)	$R_{\theta JA}$	106.6	$^{\circ}\text{C/W}$



6. Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS}=0V, I_D=250\mu A$	30			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V_{(BR)DSS}/T_J$			22		mV/ $^\circ\text{C}$
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=0V$	$T_J=25^\circ\text{C}$		1	μA
		$V_{DS}=20V$	$T_J=125^\circ\text{C}$		10	μA
Gate-to-Source Leakage Current	I_{GSS}	$V_{DS}=0V, V_{GS}=\pm 20V$			± 100	nA
ON CHARACTERISTICS						
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	1.45		2.5	V
Negative Temperature Coefficient	$V_{GS(th)}/T_J$			5.3		mV/ $^\circ\text{C}$
Drain-to-Source On Resistance	$R_{DS(on)}$	$V_{GS}=10V$	$I_D=30A$	5.2	6.2	m Ω
		$V_{GS}=4.5V$	$I_D=30A$	7.3	9.3	m Ω
Forward Transconductance	g_{FS}	$V_{DS}=1.5V, I_D=15A$		55		S
CHARGES AND CAPACITANCES						
Input Capacitance	C_{iss}	$V_{GS}=0V, V_{DS}=12V, f=1\text{MHz}$		1563		pF
Output Capacitance	C_{oss}			405		pF
Reverse Transfer Capacitance	C_{rss}			200		pF
Total Gate Charge	$Q_{G(TOT)}$	$V_{GS}=4.5V, V_{DS}=15V, I_D=30A$		12.8	19.2	nC
Threshold Gate Charge	$Q_{G(TH)}$			1.3		nC
Gate-to-Source Charge	Q_{GS}			4.7		nC
Gate-to-Drain Charge	Q_{GD}			5.2		nC
Total Gate Charge	$Q_{G(TOT)}$	$V_{GS}=10V, V_{DS}=15V, I_D=30A$		25.7		nC

1. Surface-mounted on FR4 board using 1 sq-in pad, 1 oz Cu.
2. Surface-mounted on FR4 board using the minimum recommended pad size.




SWITCHING CHARACTERISTICS (Note 4)							
Turn-On Delay Time	t _{D(on)}	V _{GS} =4.5V, V _{DS} =15V I _D =15A, R _G =3Ω			12.6		ns
Rise Time	t _r				20.2		ns
Turn-Off Delay Time	t _{D(off)}				16.4		ns
Fall Time	t _f				5.1		ns
Turn-On Delay Time	t _{D(on)}	V _{GS} =11.5V, V _{DS} =15V I _D =15A, R _G =3Ω			7.7		ns
Rise Time	t _r				17.3		ns
Turn-Off Delay Time	t _{D(off)}				23.8		ns
Fall Time	t _f				2.8		ns
DRAIN-SOURCE DIODE CHARACTERISTICS							
Forward Diode Voltage	V _{SD}	V _{GS} =0V	T _J =25°C		0.87	1.2	V
		I _D =30A	T _J =125°C		0.73		V
Reverse Recovery Time	t _{rr}	V _{GS} =0V, dI _S /dt=100A/μs I _S =30A			11.6		ns
Charge Time	t _a				7.8		ns
Discharge Time	t _b				3.7		ns
Reverse Recovery Time	Q _{rr}				3		nC
PACKAGE PARASITIC VALUES							
Source Inductance	L _S	T _A =25°C			2.49		nH
Drain inductance, DPAK	L _D				0.0164		nH
Drain Inductance, IPAK	L _D				1.88		nH
Gate Inductance	L _G				3.46		nH
Gate Resistance	R _G				0.7		Ω

3. Pulse Test: pulse width $\leq 300 \mu s$, duty cycle $\leq 2\%$.

4. Switching characteristics are independent of operating junction temperatures.



7.1Typical Characteristics





7.2 Typical Characteristics




Figure 7: Capacitance Variation




Figure 8: Gate-To-Source and Drain-To-Source Voltage vs. Total Charge




Figure 9: Resistive Switching Time Variation vs. Gate Resistance




Figure 10: On-Resistance versus Drain Current and Gate Voltage




Figure 11: Maximum Rated Forward Biased Safe Operating Area





Figure 12: Maximum Avalanche Energy vs. Starting Junction Temperature




7.3Typical Characteristics





7.TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A1	A2	A3	b	c	D	D1	D2	E	E1	E2	e	L1	L2	L3	θ
Min	0.00	2.18	0.90	0.65	0.46	6.35	4.95	4.32	9.40	5.97	5.21	2.286 BSC	0.89	1.70	0.60	0.00
Max	0.13	2.39	1.10	0.85	0.61	6.73	5.46	4.90	10.41	6.22	5.38		1.27	1.90	1.00	8.00



8.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW NTD4858NT4G	TO-252	2500	Tape and reel



9.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.