




LOC	DIST	REVISIONS				
CG	00	P	LTR	DESCRIPTION	DATE	APVD
			A	RELEASED	04AUG2011	BC AS




- 1 MATERIAL: ZINC ALLOY
- 2 KEY HOLE ORIENTATION (DIM A) PER MATING GUIDE MODULE PART NUMBER TABLE (ORIENTATION SHOWN ON PCB LAYOUT IS FOR 1-1410353-2)
- 3 ANNULAR RING PLATED AROUND GUIDE PIN MOUNTING HOLE ON TOP AND BOTTOM SIDE OF BOARD
- 4 FINISH:
3.81µm MINIMUM SILVER IN CONTACT AREA
OVER NICKEL OVER COPPER ALL OVER




4	5.70	1-1410354-4
4	4.20	1-1410354-3
4	2.60	1-1410354-2
FINISH	DIM "G"	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO 04AUG2011		 TE Connectivity		
		CHK A. SHARPE 04AUG2011				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME KEYED GUIDE PIN, DIE CAST, BACKPLANE CONNECTOR, MULTIGIG, THREADED POST		
		0 PLC ±. 1 PLC ±0.5 2 PLC ±.13 3 PLC ±0.013 4 PLC ±. ANGLES ±.				
MATERIAL 		FINISH		PRODUCT SPEC 108-2072		RESTRICTED TO -
SEE TABLE				APPLICATION SPEC 114-13056		
		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C-1410354
		CUSTOMER DRAWING		SCALE 8:1	SHEET 1	OF 2
				REV A		

LOC	DIST	REVISIONS					
CG	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-



TIER 2
GUIDE PIN FOOTPRINT
(20.3mm SIGNAL MODULES)
SCALE 4:1



ALTERNATE PCB LAYOUT
FOR GUIDE POST
SCALE 4:1

4	-	1-1410353-9
4	315°	1-1410353-8
4	270°	1-1410353-7
4	90°	1-1410353-3
4	45°	1-1410353-2
4	0°	1-1410353-1
FINISH	DIM "A"	20.3mm GUIDE MODULE
		MATING GUIDE MODULE 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO	04AUG2011	 TE Connectivity		
DIMENSIONS:		CHK A. SHARPE	04AUG2011			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. SHARPE	04AUG2011	NAME KEYED GUIDE PIN, DIE CAST, BACKPLANE CONNECTOR, MULTIGIG, THREADED POST		
mm		PRODUCT SPEC	108-2072			
0 PLC ±		APPLICATION SPEC	114-13056	SIZE	CAGE CODE	DRAWING NO
1 PLC ±0.5		WEIGHT	-	A2	00779	C-1410354
2 PLC ±.13		CUSTOMER DRAWING				RESTRICTED TO
3 PLC ±0.013		SCALE 8:1				-
4 PLC ±		SHEET 2 OF 2				REV A
ANGLES ±						
FINISH						
SEE TABLE						